




SIM pin assignment	
PIN#	Name
C1	VCC 供电电压
C2	RST 重置
C3	CLK 时钟
C5	GND 接地
C6	VPP 程序电压
C7	I/O 输入输出



PCB 焊盘区  
 下沉避让区  
 RECOMMENDED PCB LAYOUT  
 GENERAL TOLERANCE ±0.05

### Specification

#### MATERIAL:


Insulator: High Temperature Thermoplastic, UL 94V-0.  
 Contact: Copper Alloy  
 SHELL: SUS

#### PLATING:

Contact: Plated 50u'' Ni Overall Contact Au 1U  
 Shell: Plated 50u'' Ni Overall  
 Plated 1u''Au Selective Contact Area

#### Electrical:

Current Rating :0.5mA AC/DC max.  
 Voltage Rating :125V AC/DC  
 Ambient Temperature Range :-20° C~+60° C  
 Storage Temperature Range :-40° C~+70° C  
 Ambient Humidity Range :95% R.H. Max.  
 Contact Resistance:100m Ω  
 Insulation Resistance:1000M min./500VDC  
 产品耐温温度: 260  
 Mating Cycles:3000Min Insertions



TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY :	DATE :	PART NAME: 自弹式 MicroSIM 卡卡座 7P
	CHECKED BY:	DATE :	PART NO. ZX-MSIM-481.35J-7
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY:	DATE :	MOLD NO.
			DRAW NO.
			SHEET NO. 1 OF 1