

# TMP2060D

## P -Channel Enhancement Mosfet

### General Description

- Low  $R_{DS(ON)}$
- RoHS and Halogen-Free Compliant

### Applications

- Load switch
- PWM


### General Features

$V_{DS} = -20V$   $I_D = -60A$



$R_{DS(ON)} = 9m\Omega$  (typ.) @  $V_{GS} = -4.5V$

100% UIS Tested

100%  $R_g$  Tested



D:TO-252-3L



Marking: 60P02

### Absolute Maximum Ratings (Tc=25°C Unless otherwise noted)

| Symbol               | Parameter                                    | Rating     | Units |
|----------------------|----------------------------------------------|------------|-------|
| $V_{DS}$             | Drain-Source Voltage                         | -20        | V     |
| $V_{GS}$             | Gate-Source Voltage                          | $\pm 12$   | V     |
| $I_D@T_C=25^\circ C$ | Continuous Drain Current, $V_{GS} @ -4.5V^1$ | -60        | A     |
| $I_D@T_C=70^\circ C$ | Continuous Drain Current, $V_{GS} @ -4.5V^1$ | -25        | A     |
| $I_{DM}$             | Pulsed Drain Current <sup>2</sup>            | -68        | A     |
| $P_D@T_C=25^\circ C$ | Total Power Dissipation <sup>3</sup>         | 38         | W     |
| $P_D@T_C=70^\circ C$ | Total Power Dissipation <sup>3</sup>         | 18         | W     |
| $T_{STG}$            | Storage Temperature Range                    | -55 to 150 | °C    |
| $T_J$                | Operating Junction Temperature Range         | -55 to 150 | °C    |

### Thermal Data

| Symbol          | Parameter                                                  | Max. | Unit |
|-----------------|------------------------------------------------------------|------|------|
| $R_{\theta JA}$ | Thermal Resistance Junction-Ambient <sup>1</sup>           | 75   | °C/W |
| $R_{\theta JA}$ | Thermal Resistance Junction-Ambient <sup>1</sup> (t ≤ 10s) | 40   | °C/W |
| $R_{\theta JC}$ | Thermal Resistance Junction-Case <sup>1</sup>              | 4.2  | °C/W |



# TMP2060D

## P -Channel Enhancement Mosfet







### Electrical Characteristics (T<sub>J</sub>=25 °C, unless otherwise noted)

| Symbol                              | Parameter                                      | Conditions                                                                                      | Min. | Typ.   | Max.  | Unit  |
|-------------------------------------|------------------------------------------------|-------------------------------------------------------------------------------------------------|------|--------|-------|-------|
| BV <sub>DSS</sub>                   | Drain-Source Breakdown Voltage                 | V <sub>GS</sub> =0V , I <sub>D</sub> =-250uA                                                    | -20  | ---    | ---   | V     |
| ΔBV <sub>DSS</sub> /ΔT <sub>J</sub> | BV <sub>DSS</sub> Temperature Coefficient      | Reference to 25°C , I <sub>D</sub> =-1mA                                                        | ---  | -0.012 | ---   | V/°C  |
| R <sub>DS(ON)</sub>                 | Static Drain-Source On-Resistance <sup>2</sup> | V <sub>GS</sub> =-4.5V , I <sub>D</sub> =-10A                                                   | ---  | 9      | 13    | mΩ    |
|                                     |                                                | V <sub>GS</sub> =-2.5V , I <sub>D</sub> =-8A                                                    | ---  | 12     | 18    |       |
|                                     |                                                |                                                                                                 |      |        |       |       |
| V <sub>GS(th)</sub>                 | Gate Threshold Voltage                         | V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> =-250uA                                       | -0.5 | -0.7   | -1.0  | V     |
| ΔV <sub>GS(th)</sub>                | V <sub>GS(th)</sub> Temperature Coefficient    |                                                                                                 | ---  | 2.94   | ---   | mV/°C |
| I <sub>DSS</sub>                    | Drain-Source Leakage Current                   | V <sub>DS</sub> =-15V , V <sub>GS</sub> =0V , T <sub>J</sub> =25°C                              | ---  | ---    | 1     | uA    |
| I <sub>GSS</sub>                    | Gate-Source Leakage Current                    | V <sub>GS</sub> = ± 12 V , V <sub>DS</sub> =0V                                                  | ---  | ---    | ± 100 | nA    |
| g <sub>fs</sub>                     | Forward Transconductance                       | V <sub>DS</sub> =-5V , I <sub>D</sub> =-10A                                                     | ---  | 43     | ---   | S     |
| Q <sub>g</sub>                      | Total Gate Charge (-4.5V)                      | V <sub>DS</sub> =-10V , V <sub>GS</sub> =-4.5V , I <sub>D</sub> =-10A                           | ---  | 35     | ---   | nC    |
| Q <sub>gs</sub>                     | Gate-Source Charge                             |                                                                                                 | ---  | 5.0    | ---   |       |
| Q <sub>gd</sub>                     | Gate-Drain Charge                              |                                                                                                 | ---  | 10     | ---   |       |
| T <sub>d(on)</sub>                  | Turn-On Delay Time                             | V <sub>DD</sub> =-10V , V <sub>GS</sub> =-4.5V ,<br>R <sub>G</sub> =3.3Ω , I <sub>D</sub> =-10A | ---  | 12.0   | ---   | ns    |
| T <sub>r</sub>                      | Rise Time                                      |                                                                                                 | ---  | 40.0   | ---   |       |
| T <sub>d(off)</sub>                 | Turn-Off Delay Time                            |                                                                                                 | ---  | 30     | ---   |       |
| T <sub>f</sub>                      | Fall Time                                      |                                                                                                 | ---  | 10     | ---   |       |
| C <sub>iss</sub>                    | Input Capacitance                              | V <sub>DS</sub> =-15V , V <sub>GS</sub> =0V , f=1MHz                                            | ---  | 2800   | ---   | pF    |
| C <sub>oss</sub>                    | Output Capacitance                             |                                                                                                 | ---  | 690    | ---   |       |
| C <sub>rss</sub>                    | Reverse Transfer Capacitance                   |                                                                                                 | ---  | 590    | ---   |       |
| I <sub>S</sub>                      | Continuous Source Current <sup>1,4</sup>       | V <sub>G</sub> =V <sub>D</sub> =0V , Force Current                                              | ---  | ---    | -60.0 | A     |
| I <sub>SM</sub>                     | Pulsed Source Current <sup>2,4</sup>           |                                                                                                 | ---  | ---    | ---   | A     |
| V <sub>SD</sub>                     | Diode Forward Voltage <sup>2</sup>             | V <sub>GS</sub> =0V , I <sub>S</sub> =-1A , T <sub>J</sub> =25°C                                | ---  | ---    | -1.2  | V     |
| t <sub>rr</sub>                     | Reverse Recovery Time                          | I <sub>F</sub> =-10A , dI/dt=100A/μs ,                                                          | ---  | 27     | ---   | nS    |
| Q <sub>rr</sub>                     | Reverse Recovery Charge                        | T <sub>J</sub> =25°C                                                                            | ---  | 17.8   | ---   | nC    |

Note :


1. The data tested by surface mounted on a 1 inch<sup>2</sup> FR-4 board with 20Z copper.
2. The data tested by pulsed , pulse width ≤ 300us , duty cycle ≤ 2%
3. The power dissipation is limited by 150°C junction temperature
4. The data is theoretically the same as I<sub>D</sub> and I<sub>DM</sub> , in real applications , should be limited by total power dissipation.

## Typical Characteristics




**TMP2060D**


**P-Channel Enhancement Mosfet**




**Fig.7 Capacitance**




**Fig.8 Safe Operating Area**



**Fig.9 Normalized Maximum Transient Thermal Impedance**




**Fig.10 Switching Time Waveform**



**Fig.11 Gate Charge Waveform**



## Package Mechanical Data: TO-252-3L



| Symbol | Dimensions In Millimeters |        | Dimensions In Inches |       |
|--------|---------------------------|--------|----------------------|-------|
|        | Min.                      | Max.   | Min.                 | Max.  |
| A      | 2.200                     | 2.400  | 0.087                | 0.094 |
| A1     | 0.000                     | 0.127  | 0.000                | 0.005 |
| b      | 0.660                     | 0.860  | 0.026                | 0.034 |
| c      | 0.460                     | 0.580  | 0.018                | 0.023 |
| D      | 6.500                     | 6.700  | 0.256                | 0.264 |
| D1     | 5.100                     | 5.460  | 0.201                | 0.215 |
| D2     | 4.830 TYP.                |        | 0.190 TYP.           |       |
| E      | 6.000                     | 6.200  | 0.236                | 0.244 |
| e      | 2.186                     | 2.386  | 0.086                | 0.094 |
| L      | 9.800                     | 10.400 | 0.386                | 0.409 |
| L1     | 2.900 TYP.                |        | 0.114 TYP.           |       |
| L2     | 1.400                     | 1.700  | 0.055                | 0.067 |
| L3     | 1.600 TYP.                |        | 0.063 TYP.           |       |
| L4     | 0.600                     | 1.000  | 0.024                | 0.039 |
| Φ      | 1.100                     | 1.300  | 0.043                | 0.051 |
| θ      | 0°                        | 8°     | 0°                   | 8°    |
| h      | 0.000                     | 0.300  | 0.000                | 0.012 |
| V      | 5.350 TYP.                |        | 0.211 TYP.           |       |