




3D VIEWS



Mating PCB detail



Assembly Layout



X9396WVS-02

X9396WVS-03

■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 7A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ

X9396 W V S-XXC- 9T SN



- ① Series No.
- ② Category : W-WAFER
- ③ Wedging Board Angle : V-Stright 90°
- ④ Welding Way:S-SMT
- ⑤ Row No.Pin No.XX-Single row
- ⑥ C:Cap
- ⑦ Material:9T-PA9T 94V-0
- ⑧ Planting Category:SN-Bright tin plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	3.96	11.88	8.60	093	1.68	39.60	36.32
03	7.92	15.84	12.56	103	5.64	43.56	
04	11.88	19.80	16.52	11	39.60	47.52	44.24
05	15.84	23.76	20.48	12	43.56	51.48	48.20
06	19.80	27.72	24.44	13	47.52	55.44	
07	23.76	31.68	28.40	14	51.48	59.40	
08	27.72	35.64	32.36	15	55.44	63.36	60.08

X9396WVS-XXC-9TSN	PA9T UL 94V-0	Brass	Tin-Plated	X9396H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XK B Terminal

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.96mm Crimp Style Connectors																																
DWN		DATE		VIEW:	PART NO.: X9396WVS-XXC-9TSN																																
CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9396WVS-XXC-9TSN																																
APPD		DATE		SIZE: A4																																	
<table border="1"> <thead> <tr> <th>REVISIONS</th> <th>DATE</th> <th>REVISED</th> <th>APPROVED</th> <th>UNSPECIFIED TOLERANCES</th> </tr> </thead> <tbody> <tr> <td>ΔX</td> <td></td> <td></td> <td></td> <td>ANGLAR ±5°</td> </tr> <tr> <td>ΔX</td> <td></td> <td></td> <td></td> <td>L ≤ 4 ±0.2</td> </tr> <tr> <td>ΔX</td> <td></td> <td></td> <td></td> <td>4 < L ≤ 16 ±0.3</td> </tr> <tr> <td>MARK</td> <td></td> <td></td> <td></td> <td>16 < L ≤ 63 ±0.4</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td>L > 63 ±0.5</td> </tr> </tbody> </table>					REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	ΔX				ANGLAR ±5°	ΔX				L ≤ 4 ±0.2	ΔX				4 < L ≤ 16 ±0.3	MARK				16 < L ≤ 63 ±0.4					L > 63 ±0.5	WEIGHT 1.0g	SHEET 1/1	REVISION A0
REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES																																	
ΔX				ANGLAR ±5°																																	
ΔX				L ≤ 4 ±0.2																																	
ΔX				4 < L ≤ 16 ±0.3																																	
MARK				16 < L ≤ 63 ±0.4																																	
				L > 63 ±0.5																																	
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					XKB INDUSTRIAL PRECISION CO., LIMITED																																