




precidip

## DIL SOCKETS

### SERIES 114

**114-PP-XXX-41-134161**  
2.54 mm, Surface mount pick and place

Specially designed for reflow soldering including vapor phase. With unique self-aligning floating contacts



### TECHNICAL SPECS.:

|                              |                                            |
|------------------------------|--------------------------------------------|
| Insulator                    | Black glass filled polyester PCT-GF30-FR   |
| Flammability                 | UL 94V-O                                   |
| Sleeve                       | Brass CuZn36Pb3 (C36000)                   |
| Contact                      | Clip (4 finger): Beryllium copper (C17200) |
| Accepted pin Ø               | 0.40 to 0.56 mm                            |
| Insertion force              | 2 N typ.                                   |
| Withdrawal force             | 1 N typ. (polished steel gauge Ø 0.43 mm)  |
| Mechanical life              | Min. 100 cycles                            |
| Rated current                | 1 A                                        |
| Contact resistance           | Max. 10 m                                  |
| Dielectric strength          | Min. 1000 V RMS                            |
| Coplanarity SMD terminations | Max. 0.10 mm                               |

### ORDERING INFORMATION:

|                 |        |              |
|-----------------|--------|--------------|
| PP Plating code | Sleeve | Clip         |
| 87              | Tin    | Gold flash   |
| 83              | Tin    | Gold 0.75 µm |

Tape & Reel packaging: replace 161 by suffix 191 to part number Other pin counts please consult

### ADVANCED INFORMATION:

| Order Codes          | Poles | A    | B    | C    | D    | E | See |
|----------------------|-------|------|------|------|------|---|-----|
| 114-PP-306-41-134161 | 6     | 7.6  | 7.62 | 10.1 | 7.6  |   |     |
| 114-PP-308-41-134161 | 8     | 10.1 | 7.62 | 10.1 | 10.1 |   |     |

|                      |    |      |       |      |      |
|----------------------|----|------|-------|------|------|
| 114-PP-310-41-134161 | 10 | 12.6 | 7.62  | 10.1 | 12.6 |
| 114-PP-314-41-134161 | 14 | 17.8 | 7.62  | 10.1 | 5.3  |
| 114-PP-316-41-134161 | 16 | 20.3 | 7.62  | 10.1 | 5.3  |
| 114-PP-318-41-134161 | 18 | 22.9 | 7.62  | 10.1 | 5.3  |
| 114-PP-320-41-134161 | 20 | 25.4 | 7.62  | 10.1 | 8.3  |
| 114-PP-324-41-134161 | 24 | 30.4 | 7.62  | 10.1 | 8.3  |
| 114-PP-328-41-134161 | 28 | 35.6 | 7.62  | 10.1 | 8.3  |
| 114-PP-628-41-134161 | 28 | 35.5 | 15.24 | 17.7 | 10.0 |
| 114-PP-632-41-134161 | 32 | 40.6 | 15.24 | 17.7 | 10.0 |
| 114-PP-640-41-134161 | 40 | 50.8 | 15.24 | 17.7 | 10.0 |
| 114-PP-642-41-134161 | 42 | 53.4 | 15.24 | 17.7 | 10.0 |

# TECHNICAL ASSISTANCE

## GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP DIL sockets. Please see individual catalog page for additional and product specific technical data.

|                             |                  |
|-----------------------------|------------------|
| Operating temperature range | -55 ... +125 °C  |
| Climatic category (IEC)     | 55/125/21        |
| Operating humidity range    | annual mean 75 % |
| Max working voltage         | 100 VRMS/150 VDC |

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442.

## MECHANICAL CHARACTERISTICS:

|                                   |                                                       |
|-----------------------------------|-------------------------------------------------------|
| Clip retention                    | Min. 40 N (no displacement under axial force applied) |
| Contact (sleeve / clip) retention | Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2          |

## ELECTRICAL CHARACTERISTICS:

|                                                              |                                                  |
|--------------------------------------------------------------|--------------------------------------------------|
| Insulation resistance between any two adjacent contacts      | Min. 10'000 M at 500 V AC                        |
| Capacitance between any two adjacent contacts                | Max. 1 pF                                        |
| Air and creepage distances between any two adjacent contacts | Min. 0.6 mm (Min. 0.2 mm FOR SHRINK-DIP SOCKETS) |

## ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
  - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
  - 2) Sulfur dioxide (SO<sub>2</sub>) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO<sub>2</sub>, 25 °C, 75 %rH
  - 3) Hydrogen sulfide (H<sub>2</sub>S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H<sub>2</sub>S, 25 °C, 75 %rH

## SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

### PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

### PCB HOLE DIMENSIONS

- 2.54 mm grid: Finished hole Ø: 1 + 0.09/-0.06 mm | Drilled hole Ø: 1.15 ± 0.02 mm

## **PCB HOLE PLATING**

- PCB surface finish: Hole plating
- Tin: 5-15  $\mu\text{m}$  tin over min. 25  $\mu\text{m}$  copper
- Copper: min. 25  $\mu\text{m}$  copper
- Gold over nickel: 0.05-0.2  $\mu\text{m}$  gold over 2.5-5  $\mu\text{m}$  nickel over min. 25  $\mu\text{m}$  copper