



APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-55°C TO +85°C	STORAGE TEMPERATURE RANGE	-10°C TO +50°C(PACKED CONDITION)			
	VOLTAGE	40V AC/DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90%MAX(NOT DEWED)			
	CURRENT	0.25A (note1)	APPLICABLE CABLE	t=0.2±0.03mm, GOLD PLATING			
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS	QT AT		
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	×	×	
MARKING		CONFIRMED VISUALLY.			×	×	
ELECTRIC CHARACTERISTICS							
VOLTAGE PROOF		120V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	×	×	
INSULATION RESISTANCE		100V DC.		500MΩ MIN.	×	×	
CONTACT RESISTANCE		AC 20mV MAX (1KHz), 1mA.		100mΩ MAX. INCLUDING FPC BULK RESISTANCE (L=8mm)	×	×	
MECHANICAL CHARACTERISTICS							
VIBRATION		FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μ s. ② CONTACT RESISTANCE: 100mΩ MAX.	×	—	
SHOCK		981 m/s ² , DURATION OF PULSE 6ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.			×	—	
MECHANICAL OPERATION		20 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 100mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—	
FPC RETENTION FORCE		MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.20mm AT INITIAL CONDITION.)		① DIRECTION OF INSERTION: 0.15 N × n MIN. ② VERTICAL DIRECTION OF INSERTION: 0.1 N × n MIN. (note 2)	×	—	
ENVIRONMENTAL CHARACTERISTICS							
CORROSION SALT MIST		EXPOSED AT 35±2°C, 5% SALT WATER SPRAY FOR 96h.		① CONTACT RESISTANCE: 100mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS. ③ NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	×	—	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→+15 TO +35→+85→+15 TO +35 °C TIME 30 → 2 TO 3 → 30 → 2 TO 3 min UNDER 5 CYCLES.			① CONTACT RESISTANCE: 100mΩ MAX. ② INSULATION RESISTANCE: 50MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2°C. RELATIVE HUMIDITY 90 TO 95%, 96h.				×	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
△							
REMARK Unless otherwise specified, refer to JIS C 5402.				APPROVED	MO.ISHIDA	13.11.13	
				CHECKED	HS.SAKAMOTO	13.11.13	
				DESIGNED	YH.KOTANI	13.11.13	
				DRAWN	YH.KOTANI	13.11.13	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-355229-01		
HRS	SPECIFICATION SHEET		PART NO.	FH29DJ-*S-0.2SHW(05)			
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL580	△	1/2	

SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
DAMP HEAT, CYCLIC	EXPOSED AT -10 TO +65 °C RELATIVE HUMIDITY 90 TO 96 % 10 CYCLES, TOTAL 240h.	① CONTACT RESISTANCE: 100mΩ MAX. ② INSULATION RESISTANCE: 1MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—	
DRY HEAT	EXPOSED AT 85±2°C, 96h.	① CONTACT RESISTANCE: 100mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—	
COLD	EXPOSED AT -55±3°C, 96h.		×	—	
SULPHUR DIOXIDE [JIS C 60068-2-42]	EXPOSED AT 40±2°C, RELATIVE HUMIDITY 80±5 %, 25±5 ppm FOR 96h.	① CONTACT RESISTANCE: 100mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS. ③ NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	×	—	
HYDROGEN SULPHIDE [JIS C 60068-2-43]	EXPOSED AT 40±2°C, RELATIVE HUMIDITY 80±5 %, 10 TO 15 ppm FOR 96h.		×	—	
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245±3°C FOR IMMERSION DURATION, 3±0.3 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	—	
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING: PEAK TMP. 250°C MAX. REFLOW TMP. OVER 230°C WITHIN 60 sec. 2) SOLDERING IRONS: TMP. 350±10°C FOR 5±1 sec.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS. (note 3)	×	—	
<p>(note 1)</p> <p>WHEN THE SAME VALUE OF CURRENT ARE APPLIED TO ALL CONTACTS AT THE SAME TIME IN ONCE, SET THE CURRENT TO THE 70 % OF THE RATED CURRENT VALUE.</p> <p>(note 2)</p> <p>THIS PRODUCT HAS FLIP-LOCK CONSTRUCTION. FASTEN FPC ON PCB OR SOMETHING FIXED IF FORCE IN VERTICAL DIRECTION SHALL BE PREDICTED.</p> <p>(note 3)</p> <p>BLISTERS WHICH MAY OCCUR IN HOUSING DO NOT AFFECT PRODUCT PERFORMANCE.</p>					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-355229-01		
	SPECIFICATION SHEET	PART NO.	FH29DJ-*S-0.2SHW(05)		
	HIROSE ELECTRIC CO., LTD.	CODE NO	CL580		2/2