


Specifications:

- 规格:
- Voltage rating:250VAC/DC
额定电压: 250V AC/DC
 - Current rating:3A AC/DC
额定电流: 3A AC/DC
 - Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
 - Temperature range: -55°C~+105°C
温度范围: -55°C~+105°C
 - Insulation resistance:1000MΩ MIN
绝缘电阻:1000MΩ MIN
 - Contact resistance:30mΩ Max
接触电阻: 30mΩ Max
- Material:
- 材料:
- Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
 - The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC-SD,镀镍/镀锡/镀金
 - Terminal:Copper alloy
端子: 铜合金

X01 XX W X X X X
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09;15;25;37
- ③ Welding Board Angle :W-Male
- ④ T: Tradutional C: Car-pin
- ⑤ Plating Catogoty: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn
- ⑥ Color:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	18.00	24.99	30.80	19.28
15	26.50	33.32	39.20	27.51
25	40.00	47.04	53.05	41.28
37	56.60	63.50	69.40	57.71



广东星坤科技股份有限公司

姓名	日期
数量	日期
MARK	DESCRIPTION
文件工程章	

DATE	REVISED	APPROVED	ANGLAR	±5°
			L ≤ 4	±0.2
			4 < L ≤ 16	±0.3
			16 < L ≤ 63	±0.4
			L > 63	±0.5
UNSPECIFIED TOLERANCES				



DSND	SCALE: N/A	MODEL TYPE: D-SUB
DWN	VIEW:	PART NO.: X01XXWXXXX
CHKD	UNIT: mm/in	DWG NO.: X-X01XXWXXXX
APPD	SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO.,LIMITED		1/1 A0