



Miniature circuit breaker 240 V 14kA, 3-pole, D, 4A, D=70 mm according to UL 489

Model	
product brand name	SENTRON
product designation	Miniature circuit breakers
design of the product	Miniature circuit-breaker 5SJ4
General technical data	
number of poles	3
tripping characteristic class	D
mechanical service life (switching cycles) / typical	10 000
installation environment regarding EMC	Suitable for environment B (immunity to interference not applicable)
reference code / according to DIN 40719 extended according to IEC 204-2 / according to IEC 750	F
overvoltage category	3
degree of pollution	3
Voltage	
type of voltage / of the operating voltage	AC/DC
insulation voltage (Ui) / at AC / rated value	440 V
Supply voltage	
supply voltage / at AC / rated value	400 V
operating voltage	
• at AC / according to UL 489 and CSA C22.2 No. 5-02 / maximum	240 V
• at DC / rated value / maximum	60 V
• at DC / single channel / according to UL 489 and CSA C22.2 No. 5-02 / maximum	60 V
• at DC / 2-channel / according to UL 489 and CSA C22.2 No. 5-02 / maximum	125 V
supply voltage frequency / rated value	50 Hz
Protection class	
protection class IP	IP20, with connected conductors, IP 40 in the handle range
Switching capacity	
switching capacity current	
• according to EN 60898 / rated value	10 kA
• according to IEC 60947-2 / rated value	15 kA
Dissipation	
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.6 W
Current	
operational current	
• at 30 °C / rated value	4 A
• at 40 °C / rated value	4 A

<ul style="list-style-type: none"> <li>• at 45 °C / rated value</li> <li>• at 50 °C / rated value</li> <li>• at 55 °C / rated value</li> <li>• at 60 °C / rated value</li> <li>• at AC / rated value</li> </ul>	3.9 A 3.8 A 3.7 A 3.6 A 4 A
<b>Main circuit</b>	
type of voltage supply / at AC / according to UL 489 and CSA C22.2 No. 5-02	240
suitability for operation	Mechanical engineering / industry
<b>Product details</b>	
product component / neutral conductor switching	No
product feature / touch protection	Yes
product component	
<ul style="list-style-type: none"> <li>• tunnel terminals top</li> <li>• tunnel terminals bottom</li> <li>• combined terminal top</li> <li>• combined terminal bottom</li> </ul>	No No Yes Yes
product feature	
<ul style="list-style-type: none"> <li>• halogen-free</li> <li>• sealable</li> <li>• silicon-free</li> </ul>	Yes Yes Yes
product extension / installable / supplementary devices	Yes
<b>Product function</b>	
product function / note	Terminal tightening torque for Cu, 60/75°C; 3.5Nm/31lb.in
<b>Short circuit</b>	
breaking capacity short-circuit current (I <sub>cn</sub> ) / at AC / according to UL 1077 and CSA C22.2 No.235	14 kA
<b>Connections</b>	
connectable conductor cross-section / finely stranded / with core end processing	
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	0.75 mm <sup>2</sup> 25 mm <sup>2</sup>
tightening torque / with screw-type terminals / maximum	3.5 N·m
position / of power supply cord	Any
<b>Mechanical Design</b>	
height	110 mm
width	54 mm
depth	70 mm
installation depth	70 mm
number of modular width units	3
fastening method	on standard mounting rail
mounting position	any
net weight	482 g
<b>Environmental conditions</b>	
vibration resistance	50 m/s <sup>2</sup> at 25 to 150Hz and 60m/s <sup>2</sup> at 35Hz (4sec)
ambient temperature / during operation	
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	55 °C -25 °C
ambient temperature / during storage	
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	-40 °C 75 °C
<b>Certificates</b>	
reference code	
<ul style="list-style-type: none"> <li>• according to EN 61346-2</li> <li>• according to IEC 81346-2</li> </ul>	F F
<b>General Product Approval</b>	
Declaration of Conformity	

[Confirmation](#)



Declaration of Conformity	Test Certificates	other
---------------------------	-------------------	-------



EG-Konf.

[Miscellaneous](#)

[Special Test Certificate](#)

[Miscellaneous](#)

#### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SJ4304-8HG41>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SJ4304-8HG41>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SJ4304-8HG41](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SJ4304-8HG41)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



