



Circuit breaker size S2 for motor protection, CLASS 10 A-release 54...65 A  
N-release 845 A screw terminal increased switching capacity

|   |                      |
|---|----------------------|
| product brand name  | SIRIUS               |
| product designation   | Circuit breaker      |
| design of the product   | For motor protection |
| product type designation  | 3RV2                 |
| <b>General technical data</b>   |                      |
| size of the circuit-breaker   | S2                   |
| size of contactor can be combined company-specific                                  | S2                   |
| product extension auxiliary switch  | Yes                  |
| power loss [W] for rated value of the current                                       |                      |
| • at AC in hot operating state  | 26 W                 |
| • at AC in hot operating state per pole   | 8.7 W                |
| insulation voltage with degree of pollution 3 at AC rated value                     | 690 V                |
| surge voltage resistance rated value  | 6 kV                 |
| shock resistance according to IEC 60068-2-27  | 25g / 11 ms Sinus    |
| mechanical service life (switching cycles)  |                      |
| • of the main contacts typical  | 20 000               |
| • of auxiliary contacts typical   | 20 000               |
| electrical endurance (switching cycles) typical                                     | 20 000               |
| type of protection according to ATEX directive 2014/34/EU                           | Ex II (2) GD         |
| certificate of suitability according to ATEX directive 2014/34/EU                   | DMT 02 ATEX F 001    |
| reference code according to IEC 81346-2   | Q                    |
| Substance Prohibitance (Date)   | 03/01/2017           |
| <b>Ambient conditions</b>   |                      |
| installation altitude at height above sea level maximum                             | 2 000 m              |
| ambient temperature   |                      |
| • during operation  | -20 ... +60 °C       |
| • during storage  | -50 ... +80 °C       |
| • during transport  | -50 ... +80 °C       |
| relative humidity during operation  | 10 ... 95 %          |
| <b>Main circuit</b>   |                      |
| number of poles for main current circuit  | 3                    |
| adjustable current response value current of the current-dependent overload release | 54 ... 65 A          |
| operating voltage   |                      |
| • rated value   | 20 ... 690 V         |
| • at AC-3 rated value maximum   | 690 V                |
| • at AC-3e rated value maximum  | 690 V                |

|  |  |
|--|--|
| <b>operating frequency rated value</b>   | 50 ... 60 Hz   |
| <b>operational current rated value</b>   | 65 A   |
| <b>operational current</b>   |  |
| • at AC-3 at 400 V rated value   | 65 A   |
| • at AC-3e at 400 V rated value  | 65 A   |
| <b>operating power</b>   |  |
| • at AC-3  |  |
| — at 230 V rated value   | 18.5 kW  |
| — at 400 V rated value   | 30 kW  |
| — at 500 V rated value   | 45 kW  |
| — at 690 V rated value   | 55 kW  |
| • at AC-3e   |  |
| — at 230 V rated value   | 18.5 kW  |
| — at 400 V rated value   | 30 kW  |
| — at 500 V rated value   | 45 kW  |
| — at 690 V rated value   | 55 kW  |
| <b>operating frequency</b>   |  |
| • at AC-3 maximum  | 15 1/h   |
| • at AC-3e maximum   | 15 1/h   |
| <b>Protective and monitoring functions</b>   |  |
| <b>product function</b>  |  |
| • ground fault detection   | No   |
| • phase failure detection  | Yes  |
| <b>trip class</b>  | CLASS 10   |
| <b>design of the overload release</b>  | thermal  |
| <b>breaking capacity maximum short-circuit current (Icu)</b>                                   |  |
| • at AC at 240 V rated value   | 100 kA   |
| • at AC at 400 V rated value   | 100 kA   |
| • at AC at 500 V rated value   | 10 kA  |
| • at AC at 690 V rated value   | 6 kA   |
| <b>breaking capacity operating short-circuit current (Ics) at AC</b>                           |  |
| • at 240 V rated value   | 100 kA   |
| • at 400 V rated value   | 50 kA  |
| • at 500 V rated value   | 8 kA   |
| • at 690 V rated value   | 4 kA   |
| response value current of instantaneous short-circuit trip unit                                | 845 A  |
| <b>UL/CSA ratings</b>  |  |
| <b>full-load current (FLA) for 3-phase AC motor</b>  |  |
| • at 480 V rated value   | 65 A   |
| • at 600 V rated value   | 62 A   |
| <b>yielded mechanical performance [hp]</b>   |  |
| • for 3-phase AC motor   |  |
| — at 200/208 V rated value   | 20 hp  |
| — at 220/230 V rated value   | 25 hp  |
| — at 460/480 V rated value   | 50 hp  |
| — at 575/600 V rated value   | 60 hp  |
| <b>Short-circuit protection</b>  |  |
| <b>product function short circuit protection</b>   | Yes  |
| <b>design of the short-circuit trip</b>  | magnetic   |
| <b>design of the fuse link for IT network for short-circuit protection of the main circuit</b> |  |
| • at 240 V   | none required  |
| • at 400 V   | 160  |
| • at 500 V   | 125  |
| • at 690 V   | 100  |
| <b>Installation/ mounting/ dimensions</b>  |  |
| <b>mounting position</b>   | any  |
| <b>fastening method</b>  | screw and snap-on mounting onto 35 mm standard mounting rail |

|                               |                           |
|-------------------------------|---------------------------|
|                               | according to DIN EN 60715 |
| <b>height</b>                 | 140 mm                    |
| <b>width</b>                  | 55 mm                     |
| <b>depth</b>                  | 149 mm                    |
| <b>required spacing</b>       |                           |
| • for grounded parts at 400 V |                           |
| — downwards                   | 50 mm                     |
| — upwards                     | 50 mm                     |
| — at the side                 | 10 mm                     |
| • for live parts at 400 V     |                           |
| — downwards                   | 50 mm                     |
| — upwards                     | 50 mm                     |
| — at the side                 | 10 mm                     |
| • for grounded parts at 500 V |                           |
| — downwards                   | 50 mm                     |
| — upwards                     | 50 mm                     |
| — at the side                 | 10 mm                     |
| • for live parts at 500 V     |                           |
| — downwards                   | 50 mm                     |
| — upwards                     | 50 mm                     |
| — at the side                 | 10 mm                     |
| • for grounded parts at 690 V |                           |
| — downwards                   | 50 mm                     |
| — upwards                     | 50 mm                     |
| — at the side                 | 10 mm                     |
| • for live parts at 690 V     |                           |
| — downwards                   | 50 mm                     |
| — upwards                     | 50 mm                     |
| — at the side                 | 10 mm                     |

| <b>Connections/ Terminals</b>  |  |
|--|--|
| <b>type of electrical connection</b>                                 |  |
| • for main current circuit   | screw-type terminals   |
| <b>arrangement of electrical connectors for main current circuit</b> | Top and bottom   |
| <b>type of connectable conductor cross-sections</b>                  |  |
| • for main contacts  |  |
| — solid or stranded  | 2x (1 ... 35 mm <sup>2</sup> ), 1x (1 ... 50 mm <sup>2</sup> ) |
| — finely stranded with core end processing                           | 2x (1 ... 25 mm <sup>2</sup> ), 1x (1 ... 35 mm <sup>2</sup> ) |
| • at AWG cables for main contacts                                    | 2x (18 ... 2), 1x (18 ... 1)                                   |
| <b>tightening torque</b>   |  |
| • for main contacts with screw-type terminals                        | 3 ... 4.5 N·m  |
| <b>design of screwdriver shaft</b>                                   | Diameter 5 to 6 mm   |
| <b>size of the screwdriver tip</b>                                   | Pozidriv size 2  |
| <b>design of the thread of the connection screw</b>                  |  |
| • for main contacts  | M6   |

| <b>Safety related data</b>   |  |
|--|--|
| <b>B10 value</b>   |  |
| • with high demand rate according to SN 31920                                  | 5 000  |
| <b>proportion of dangerous failures</b>  |  |
| • with low demand rate according to SN 31920                                   | 50 %   |
| • with high demand rate according to SN 31920                                  | 50 %   |
| <b>failure rate [FIT]</b>  |  |
| • with low demand rate according to SN 31920                                   | 50 FIT   |
| <b>T1 value for proof test interval or service life according to IEC 61508</b> | 10 y   |
| <b>protection class IP on the front according to IEC 60529</b>                 | IP20   |
| <b>touch protection on the front according to IEC 60529</b>                    | finger-safe, for vertical contact from the front |
| display version for switching status   | Handle   |
| <b>Certificates/ approvals</b>   |  |

## General Product Approval



[Confirmation](#)



CCC



UL

KC



For use in hazardous locations

Declaration of Conformity

Test Certificates



IECEx



ATEX



EG-Konf.

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

## Marine / Shipping



ABS



BUREAU  
VERITAS



DNV



LRS



PRIS



RINA

Marine / Shipping

other

Railway



RMRS

[Confirmation](#)



VDE

[Vibration and Shock](#)

[Confirmation](#)

## Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2032-4JA10>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2032-4JA10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2032-4JA10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RV2032-4JA10&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2032-4JA10&lang=en)

Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2032-4JA10/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2032-4JA10&objecttype=14&gridview=view1>

last modified:

6/25/2022