


Features

- Complementary to MMBT3906

Maximum ratings (AT $T_A=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	60	V
V_{CEO}	Collector-Emitter Voltage	40	V
V_{EBO}	Emitter-Base Voltage	6	V
I_C	Collector Current	200	mA
P_C	Collector Power Dissipation	200	mW
$R_{\theta JA}$	Thermal Resistance From Junction To Ambient	625	$^{\circ}\text{C/W}$
T_J	Junction Temperature	150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature	-55~+150	$^{\circ}\text{C}$

SOT- 23



Dimensions in inches and (millimeters)









Electrical characteristics (AT $T_A=25^{\circ}\text{C}$ unless otherwise noted)

Off characteristics



Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=10\mu\text{A}$, $I_E=0$	60			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=1\text{mA}$, $I_B=0$	40			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=10\mu\text{A}$, $I_C=0$	6			V
Collector cut-off current	I_{CEX}	$V_{CE}=30\text{V}$, $V_{EB(off)}=3\text{V}$			50	nA
Collector cut-off current	I_{CBO}	$V_{CB}=60\text{V}$, $I_E=0$			100	nA
Emitter cut-off current	I_{EBO}	$V_{EB}=5\text{V}$, $I_C=0$			100	nA
DC current gain	$h_{FE(1)}$	$V_{CE}=1\text{V}$, $I_C=10\text{mA}$	100		300	
	$h_{FE(2)}$	$V_{CE}=1\text{V}$, $I_C=50\text{mA}$	60			
	$h_{FE(3)}$	$V_{CE}=1\text{V}$, $I_C=100\text{mA}$	30			
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C=50\text{mA}$, $I_B=5\text{mA}$			0.3	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C=50\text{mA}$, $I_B=5\text{mA}$			0.95	V
Transition frequency	f_T	$V_{CE}=20\text{V}$, $I_C=10\text{mA}$, $f=100\text{MHz}$	300			MHz
Delay time	t_d	$V_{CC}=3\text{V}$, $V_{BE(off)}=-0.5\text{V}$, $I_C=10\text{mA}$, $I_{B1}=1\text{mA}$			35	ns
Rise time	t_r	$V_{CC}=3\text{V}$, $V_{BE(off)}=-0.5\text{V}$, $I_C=10\text{mA}$, $I_{B1}=1\text{mA}$			35	ns
Storage time	t_s	$V_{CC}=3\text{V}$, $I_C=10\text{mA}$, $I_{B1}=I_{B2}=1\text{mA}$			200	ns
Fall time	t_f	$V_{CC}=3\text{V}$, $I_C=10\text{mA}$, $I_{B1}=I_{B2}=1\text{mA}$			50	ns

CLASSIFICATION OF $h_{FE(1)}$

HFE	100-300	
RANK	L	H
RANGE	100 - 200	200 - 300

Typical Characteristics


Pinning information

Pin	Simplified outline	Symbol
PinB Base PinC Collector PinE Emitter		

Marking

Type number	Marking code
MMBT3904	1AM

Suggested solder pad layout

SOT-23

