


Features

- Ultra low quiescent current: $4\mu A$ (typ.)
- High input voltage (up to 12V)
- Output voltage:
1.8V, 2.5V, 2.7V, 3.0V, 3.3V, 3.5V, 5.0V
- Output voltage accuracy: tolerance $\pm 3\%$
- Maximum output current: 250mA
- Low dropout voltage
- Low temperature coefficient
-

SOT-89

RoHS
COMPLIANT

Pb
Pb-Free



Applications

- Battery-powered equipment
- Voltage regulator for microprocessor
- Voltage regulator for LAN cards
- Wireless Communication equipment
- Audio/Video equipment




Dimensions in millimeters

General Description

The SY73XX series is a set of three-terminal, low power, high voltage regulators implemented in CMOS technology. The series features extremely low quiescent current which is typically $4\mu A$. They allow input voltages as high as 12V. The device provides large current with a significantly small dropout voltage.

The SY73XX consists of a high-precision voltage reference, an error correction circuit, and a current limited output driver. They are available with several fixed output voltages ranging from 1.8V to 5.0V. CMOS technology ensures low dropout voltage and low current consumption. Although designed primarily as fixed voltage regulators, these devices can be used with external components to generate variable voltages and currents.



Selection Table

Part No.	Output Voltage	Tolerance	Package	Marking
SY7318	1.8V	$\pm 3\%$	SOT-89	73XX OR 73XX-A
SY7325	2.5V	$\pm 3\%$		
SY7327	2.7V	$\pm 3\%$		OR 73XX-1
SY7330	3.0V	$\pm 3\%$		
SY7333	3.3V	$\pm 3\%$		
SY7335	3.5V	$\pm 3\%$		
SY7350	5.0V	$\pm 3\%$		

Note: "XX" stands for output voltages

Absolute Maximum Ratings

Supply Voltage $V_{SS} - 0.3V$ to $V_{SS} + 14V$ Storage Temperature $-50^\circ C$ to $125^\circ C$

Power Consumption (*1) 500mW Operating Temperature $-40^\circ C$ to $85^\circ C$

Power Consumption (*2) 500mW

Note: These are stress ratings only. Stresses exceeding the range specified under "Absolute Maximum Ratings" may cause substantial damage to the device. Functional operation of this device at other conditions beyond those listed in the specification is not implied and prolonged exposure to extreme conditions may affect device reliability.

Electrical Characteristics
SY7318 +1.8V Output Type
T_a=25°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V_{IN}	Conditions				
V _{OUT}	Output Voltage	2.8V	I _{OUT} =40mA	1.746	1.8	1.854	V
I _{OUT(MAX)}	Maximum Output Current	2.8V	V _{OUT} ≥1.62V	150	—	—	mA
ΔV _{OUT} *	Load Regulation	2.8V	1mA≤I _{OUT} ≤60mA	—	45	90	mV
V _{DROP} **	Dropout Voltage	—	I _{OUT} =40mA	—	170	—	mV
I _{SS}	Quiescent Current	2.8V	No load	—	4	8	μA
ΔV _{OUT} ΔV _{IN} × V _{OUT}	Line Regulation	—	I _{OUT} =40mA 2.8V≤V _{IN} ≤12V	—	0.2	0.3	%/V
V _{IN}	Input Voltage	—	—	—	—	12	V
ΔV _{OUT} ΔT _a	Temperature Coefficient	2.8V	I _{OUT} =40mA −40°C<T _a <85°C	—	±0.7	—	ppm/°C

SY7325 +2.5V Output Type
T_a=25°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V_{IN}	Conditions				
V _{OUT}	Output Voltage	3.5V	I _{OUT} =40mA	2.425	2.5	2.575	V
I _{OUT(MAX)}	Maximum Output Current	3.5V	V _{OUT} ≥2.25V	180	—	—	mA
ΔV _{OUT} *	Load Regulation	3.5V	1mA≤I _{OUT} ≤60mA	—	45	90	mV
V _{DROP} **	Dropout Voltage	—	I _{OUT} =40mA	—	110	—	mV
I _{SS}	Quiescent Current	3.5V	No load	—	4	8	μA
ΔV _{OUT} ΔV _{IN} × V _{OUT}	Line Regulation	—	I _{OUT} =40mA 3.5V≤V _{IN} ≤12V	—	0.2	0.3	%/V
V _{IN}	Input Voltage	—	—	—	—	12	V
ΔV _{OUT} ΔT _a	Temperature Coefficient	3.5V	I _{OUT} =40mA −40°C<T _a <85°C	—	±0.7	—	ppm/°C

SY7327 +2.7V Output Type
T_a=25°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V_{IN}	Conditions				
V _{OUT}	Output Voltage	3.7V	I _{OUT} =40mA	2.619	2.7	2.781	V
I _{OUT(MAX)}	Maximum Output Current	3.7V	V _{OUT} ≥2.43V	200	—	—	mA
ΔV _{OUT} *	Load Regulation	3.7V	1mA≤I _{OUT} ≤80mA	—	45	90	mV
V _{DROP} **	Dropout Voltage	—	I _{OUT} =40mA	—	100	—	mV
I _{SS}	Quiescent Current	3.7V	No load	—	4	8	μA
ΔV _{OUT} ΔV _{IN} × V _{OUT}	Line Regulation	—	I _{OUT} =40mA 3.7V≤V _{IN} ≤12V	—	0.2	0.3	%/V
V _{IN}	Input Voltage	—	—	—	—	12	V
ΔV _{OUT} ΔT _a	Temperature Coefficient	3.7V	I _{OUT} =40mA −40°C<T _a <85°C	—	±0.7	—	ppm/°C



SY73XX

Low Power Consumption LDO

SY7330 +3.0V Output Type

Ta=25°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V _{IN}	Conditions				
V _{OUT}	Output Voltage	4V	I _{OUT} =40mA	2.91	3	3.09	V
I _{OUT(MAX)}	Maximum Output Current	4V	V _{OUT} ≥2.7V	250	—	—	mA
ΔV _{OUT} *	Load Regulation	4V	1mA≤I _{OUT} ≤80mA	—	45	90	mV
V _{DROP} **	Dropout Voltage	—	I _{OUT} =40mA	—	95	—	mV
I _{SS}	Quiescent Current	4V	No load	—	4	8	μA
ΔV _{OUT} ΔV _{IN} × V _{OUT}	Line Regulation	—	I _{OUT} =40mA 4V≤V _{IN} ≤12V	—	0.2	0.3	%/V
V _{IN}	Input Voltage	—	—	—	—	12	V
ΔV _{OUT} ΔT _a	Temperature Coefficient	4V	I _{OUT} =40mA −40°C<Ta<85°C	—	±0.7	—	ppm/°C

SY7333 +3.3V Output Type

Ta=25°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V _{IN}	Conditions				
V _{OUT}	Output Voltage	4.3V	I _{OUT} =40mA	3.201	3.3	3.399	V
I _{OUT(MAX)}	Maximum Output Current	4.3V	V _{OUT} ≥2.97V	250	—	—	mA
ΔV _{OUT} *	Load Regulation	4.3V	1mA≤I _{OUT} ≤80mA	—	45	90	mV
V _{DROP} **	Dropout Voltage	—	I _{OUT} =40mA	—	90	—	mV
I _{SS}	Quiescent Current	4.3V	No load	—	4	8	μA
ΔV _{OUT} ΔV _{IN} × V _{OUT}	Line Regulation	—	I _{OUT} =40mA 4.3V≤V _{IN} ≤12V	—	0.2	0.3	%/V
V _{IN}	Input Voltage	—	—	—	—	12	V
ΔV _{OUT} ΔT _a	Temperature Coefficient	4.3V	I _{OUT} =40mA −40°C<Ta<85°C	—	±0.7	—	ppm/°C

SY7335 +3.5V Output Type

Ta=25°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V _{IN}	Conditions				
V _{OUT}	Output Voltage	4.5V	I _{OUT} =40mA	3.395	3.5	3.605	V
I _{OUT(MAX)}	Maximum Output Current	4.5V	V _{OUT} ≥3.15V	250	—	—	mA
ΔV _{OUT} *	Load Regulation	4.5V	1mA≤I _{OUT} ≤80mA	—	45	90	mV
V _{DROP} **	Dropout Voltage	—	I _{OUT} =40mA	—	80	—	mV
I _{SS}	Quiescent Current	4.5V	No load	—	4	8	μA
ΔV _{OUT} ΔV _{IN} × V _{OUT}	Line Regulation	—	I _{OUT} =40mA 4.5V≤V _{IN} ≤12V	—	0.2	0.3	%/V
V _{IN}	Input Voltage	—	—	—	—	12	V
ΔV _{OUT} ΔT _a	Temperature Coefficient	4.5V	I _{OUT} =80mA −40°C<Ta<85°C	—	±0.7	—	ppm/°C

SY7350 +5.0V Output Type

Ta=25°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V _{IN}	Conditions				
V _{OUT}	Output Voltage	6V	I _{OUT} =40mA	4.85	5	5.15	V
I _{OUT(MAX)}	Maximum Output Current	6V	V _{OUT} ≥4.5V	250	—	—	mA
ΔV _{OUT} *	Load Regulation	6V	1mA≤I _{OUT} ≤100mA	—	45	90	mV
V _{DROP} **	Dropout Voltage	—	I _{OUT} =40mA	—	60	—	mV
I _{SS}	Quiescent Current	6V	No load	—	4	8	μA
ΔV _{OUT} ΔV _{IN} × V _{OUT}	Line Regulation	—	I _{OUT} =40mA 6V≤V _{IN} ≤12V	—	0.2	0.3	%/V
V _{IN}	Input Voltage	—	—	—	—	12	V
ΔV _{OUT} ΔT _a	Temperature Coefficient	6V	I _{OUT} =80mA −40°C<Ta<85°C	—	±0.7	—	ppm/°C

Note: ** Regulation is measured at constant junction temperature, using pulsed ON time.

*** Dropout is measured at constant junction temperature, using pulsed ON time, and the criterion is V_{OUT} inside target value ±2%.

Application Circuits
