





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2016.03.14	胡金花



Specifications
 Current Rating:2.0Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Phosphor Bronze
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon (Halogen Free) or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.

Recommended P.C.B. Layout
 (Tolerance:0.05mm)



Ordering Information

C SFD218 - XX XX A 002 R 1 A X

No. of Pins per Row 02~40
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin 05=Gold Flash/Tin
 Color 1=Black
 Standard Packing C=Tube
 Selective Packing A=Box
 D=Tape&Reel

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE		DESIGNED: 胡金花	DATE: 2016.03.14	DWG. NO.	TITLE. 2.00 FEMALE HEADER DUAL ROWS SMT TYPE CONNECTOR
X.*±5.0°	X.±0.30	CHECKED:	DATE:	CSFD218-CA2RA	
.X*±3.0°	.X±0.25	CO SIGNED: 劉北平	DATE: 2016.03.14	PART NO.	
.XX*±2.0°	.XX±0.15	APPROVED:	DATE:	CSFD218-XXXX A002R1AX	
.XXX*±1.0°	.XXX±0.10				

REV.	UNIT.	SCALE.	PAGE.
01	mm	3:1	1/1