

F

E

D

C

B

A

F

E




D

C

B

A

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2012.06.16	黃小燕
02		因客訴下板困難，增加端子間距尺寸中心	2015.02.14	邱國強



Specifications
Current Rating:2Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:500VAC
Contact Resistance:20mΩMax.
Operating Temperature:−40°C to +105°C
Materials
Contact Material:Phosphor Bronze
Insulator Material:High Temperature Thermoplastic, UL 94V−0 Nylon 6T (Halogen Free) or the equivalent material
All materials must meet Greenconn hazardous substances control standards.

Ordering Information

C SFB203 - XX XX A 001 R 1 A X


No. of Pins per Row
02~40


Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
C=Tube
Selective Packing
A=Box

Recommended P.C.Board Layout
(Tolerance:±0.05)



格稜股份有限公司 Greenconn Corporation					GENERAL TOLERANCE		DESIGNED: 邱國強	DATE: 2015.02.14	DWG. NO. CSFB203—CA1RA	TITLE. 2.00 FEMALE HEADER DUAL ROW (R/A) TYPE SIDE ENTRY
					X.°±5.0°	X.±0.30	CHECKED:	DATE:		
					.X°±3.0°	.X±0.25	CO SIGNED: 劉北平	DATE: 2015.02.14	PART NO. CSFB203—XXXX A001R1AX	
					.XX°±2.0°	.XX±0.15	APPROVED:	DATE:		
REV. 02	UNIT. mm	SCALE. 4:1	PAGE. 1/1		.XXX°±1.0°	.XXX±0.10				