

[illegible]



深圳市韩下电子有限公司

Shenzhen Hanxia Electronic Co., Ltd

Tel: 0755-33819206 Fax: 0755-27597491

## 承 认 书

### SPECIFICATION FOR APPROVAL

客 户 Customer:

产品名称 Project:

针座

规格型号 Part No:

HX VH3.96-5P WZ

贵公司承认印 Approval signatures

| 料 号/Part No. | 签 章/Signatures |
|--------------|----------------|
|              |                |

日期 Date:

|             |     |                                                                                      |
|-------------|-----|--------------------------------------------------------------------------------------|
| 拟制/Drawn    | 黄彬  |  |
| 审核/Check    | 张伟  |                                                                                      |
| 批准/Approved | 罗小春 |                                                                                      |

**1、SCOPE: (适用范围)**

1.1 This specification covers production and inspection of Connector.

本规范内容适用于本公司普通系列型条形连接器（针座）产品的生产与检验.

**2、USE CONDITION: (使用条件)**

**2.1 Ambient temperature Range:-40℃~+105℃**

环境温度: -40℃~+105℃

**2.2 Applicable Wire Sizes:AWG#18~#26**

适用线规: AWG#18~#26

**2.3 Applicable PC board thickness:1.2~1.6mm**

适用 PC 板厚度: 1.2~1.6 mm

**3、Appearance and Dimension: (外观及尺寸)**

**3.1 Appearance:Product surface without defect、dirt、crack、and mechanical damang, Contact without rust,plating not oxidized and not peeled.**

产品表面不应有对制品有害的缺陷、污垢、裂痕及机械损伤; 接触件无锈蚀、镀层氧化、脱落等现象.

**3.2 Dimension:According to drawings**

外形尺寸: 依照附图

**3.3 Exchangable:Exchangable with same specification products.**

互换性: 相同规格应能互换

**4、Material:**

材 料 (以图纸为准)

| P/N<br>零件名称                   | Type<br>类 型        | Material<br>材 料                  | Finish<br>表面处理                          | Expiain<br>说 明     |
|-------------------------------|--------------------|----------------------------------|-----------------------------------------|--------------------|
| Terminal<br>端子                | Contact<br>插 簧     | Phosphor bronze<br>锡青磷铜 厚 0.15mm | Tin Plating:3~4 μ m<br>镀锡: 3~4 μ m      | RoHS<br>Comp liant |
| Housing<br>孔 座                | Plastic<br>塑 壳     | Nylon66 UL94V-0                  | Color:White<br>颜色: 白色                   |                    |
| Opening Wafer<br>开口针座         | Contact<br>插 针     | Phosphor bronze<br>锡青磷铜 厚 0.30mm | Tin Plating:3~4 μ m<br>镀锡: 3~4 μ m      |                    |
|                               | Plastic<br>塑 壳     | Nylon46 UL94V-0                  | Color: Beige<br>颜色: 米色                  |                    |
| Lips Wafer<br>闭口针座            | Contact<br>插 针     | Phosphor bronze<br>锡青磷铜 厚 0.30mm | Gold Plating:3~4 μ " m<br>镀金: 3~4 μ " m |                    |
|                               | Plastic<br>塑 壳     | PBT UL94V-0                      | Color: White<br>颜色: 白色                  |                    |
| Tiepian Wafer<br>卧贴针座<br>立贴针座 | Contact<br>插 针     | Phosphor bronze<br>锡青磷铜 厚 0.30mm | Tin Plating:3~4 μ m<br>镀锡: 3~4 μ m      |                    |
|                               | Solder tabs<br>焊护耳 | Phosphor bronze<br>锡青磷铜 厚 0.25mm | Tin Plating:3~4 μ m<br>镀锡: 3~4 μ m      |                    |
|                               | Plastic<br>塑 壳     | Nylon46 UL94V-0                  | Color: Beige<br>颜色: 米色                  |                    |

## 5、Electrical Performance:

## 电气性能

| N0.<br>序号 | Ltem<br>项 目                   | Requirement<br>技术要求    |
|-----------|-------------------------------|------------------------|
| 5.1       | Voltage Rated<br>额定电压         | 250V AC DC             |
| 5.2       | Current Rated<br>额定电流         | 7A AC DC               |
| 5.3       | Contact Resistance<br>接触电阻    | $\leq 0.01 \Omega$     |
| 5.4       | Insulation Resistance<br>绝缘电阻 | $\geq 1000 M \Omega$   |
| 5.5       | Dielectric Strength<br>耐 压    | $\geq 1500V$ AC/minute |

## 6、Mechanical Performance:

## 机械性能

| N0.<br>序号 | Ltem<br>项 目                              | Requirement<br>技术要求 |
|-----------|------------------------------------------|---------------------|
| 6.1       | Male contact Retention force<br>PIN 针固定力 | $\geq 15N$ per pin  |
| 6.2       | Female contact Retention force<br>端子固定力  | $\geq 15N$ per pin  |
| 6.3       | Plug-in force<br>插入力                     | $\leq 3N$ per pin   |
| 6.4       | Plug-out force<br>拔出力                    | $\geq 0.5N$ per pin |

## 7、Endurance Characteristics:

## 环境性能

| N0.<br>序号 | Ltem<br>项 目           | Requirement<br>技术要求                                                                                                                                                        |
|-----------|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 7.1       | Soldering rest<br>可焊性 | Time: $2.5 \pm 0.5S$<br>时间: $2.5 \pm 0.5S$<br><br>Temperature: $260 \pm 5^{\circ}C$<br>温度: $260 \pm 5^{\circ}C$<br><br>Area of Soldering: $\geq 95\%$<br>焊锡面积: $\geq 95\%$ |

|     |                                      |                                                                                                                                                                                                                                                                                                                                                                        |
|-----|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 7.2 | Resistance to soldering Heat<br>耐焊接热 | Time: $5 \pm 1S$<br>时间: $5 \pm 1S$<br><br>Temperature: $260 \pm 5^{\circ}C$<br>温度: $260 \pm 5^{\circ}C$<br><br>Appearance: NO Damage<br>外观: 无损坏                                                                                                                                                                                                                        |
| 7.3 | Heat test<br>耐热性                     | Time: 96h<br>时间: 96 小时<br><br>Temperature: $+85 \pm 3^{\circ}C$<br>温度: $+85 \pm 3^{\circ}C$<br><br>Appearance: NO Damage<br>外观: 无损坏<br><br>Contact resistance: $\leq 20 m\Omega$<br>接触电阻: $\leq 20 m\Omega$                                                                                                                                                            |
| 7.4 | Cold test<br>耐冷性                     | Time: 48h<br>时间: 48 小时<br><br>Temperature: $-25 \pm 3^{\circ}C$<br>温度: $-25 \pm 3^{\circ}C$<br><br>Appearance: NO Damage<br>外观: 无损坏<br><br>Contact resistance: $\leq 20 m\Omega$<br>接触电阻: $\leq 20 m\Omega$                                                                                                                                                            |
| 7.5 | Temperature Cycling<br>温度循环          | Low temperature: $-25 \pm 3^{\circ}C$<br>低温: $-25 \pm 3^{\circ}C$<br><br>High temperature: $85 \pm 3^{\circ}C$<br>高温: $85 \pm 3^{\circ}C$<br><br>For 5 cycles. test after keeping in Normal Condition for 30 min.<br><br>5 次循环后, 放置在正常环境中 30 分钟, 在进行测试<br><br>Appearance: NO Damage<br>外观: 无损坏<br><br>Contact resistance: $\leq 20 m\Omega$<br>接触电阻: $\leq 20 m\Omega$ |

|     |                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|-----|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 7.6 | Invariab lenes humidity<br>恒定湿热 | <p>Temperature: <math>60 \pm 2^{\circ}\text{C}</math><br/>温度: <math>60 \pm 2^{\circ}\text{C}</math></p> <p>Relative humidity: 90%–96% RH<br/>相对湿度: 90%–96% RH</p> <p>Tim: 96h<br/>时间: 96 小时</p> <p>Appearance: NO Damage<br/>外观: 无损坏</p> <p>Contact resistance: <math>\leq 20\text{ m}\Omega</math><br/>接触电阻: <math>\leq 20\text{ m}\Omega</math></p> <p>Insulation Resistance: <math>\geq 100\text{ M}\Omega</math><br/>绝缘电阻: <math>\geq 100\text{ M}\Omega</math></p>                                                                                                                                                           |
| 7.7 | Salt Spray<br>盐雾试验              | <p>Salt concentration: <math>5 \pm 1\%</math><br/>浓度: <math>5 \pm 1\%</math></p> <p>Temperature: <math>35 \pm 2^{\circ}\text{C}</math><br/>温度: <math>35 \pm 2^{\circ}\text{C}</math></p> <p>Tim: <math>16 \pm 2\text{ h}</math><br/>时间: <math>16 \pm 2</math> 小时</p> <p>After salt is removed by running wafer and A drop is removed ,it is measured.</p> <p>把试验样品从试验箱顶悬挂下来,采用浓度 (<math>5 \pm 1</math>) %的氯化钠溶液,连续雾化 16 小时,试验后用流动的蒸馏水轻轻洗去表面沉积物,在常温常驻湿条件下恢复 1-2 小时,外观无损伤</p> <p>Appearance: NO Damage<br/>外观: 无损坏</p> <p>Contact resistance: <math>\leq 20\text{ m}\Omega</math><br/>接触电阻: <math>\leq 20\text{ m}\Omega</math></p> |



## 8、Packaging Transportation Storage

包装、运输、贮存

### 8.1 Packaging

包装

- (1) **The packing of plastic inner is the plastic bag,the packing of inner terminal is panel mounting attach material packing, marked with product name, specification model, quantity, date in produced.**

塑件内包装为塑料袋，端子内包装为盘装带料包装，装（贴）入合格证，注明产品名称、规格型号、数量生产日期

- (2) **Exterior package is carton, facing the packing list, the packing list marked with product name, specificcation model, quantity, date of dispatch.**

外包装为纸箱，贴装箱单、装箱单上注明产品名称、规格型号、数量、出货日期

- (3) **The product in the box must not rock.**

产品在箱内不晃动

### 8.2 Transportation

运输

**Allow for any way transportation, can't get wet and mechanical in jury.**

允许用任何方式运输，勿淋湿及机械性损伤

### 8.3 Storage

贮存

**The connector of packing finished should be in the ambient temperature between-10℃ to+40℃, Relative humidity≤80%. To store in storehouse does not have acidic, alkaline air and other corrosive gas in the ambient air.**

包装完毕的连接器应在环境温度为-10℃~+40℃，相对湿度≤80%，周围空气没有酸性，碱性及其它腐蚀性气体的库房中贮存