



RECOMMEND P C B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard:
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 200° C for 30-60 seconds
(220° C for 5 seconds)

Code Description

HJ-254-PH-1-XX-25-S-115-2-G0-B
(1) (2) (3) (4) (5) (6) (7) (8) (9) (10)

- (1) Pin Spacing: 254=2.54mm
(2) Product Name: PH=Pin Header
(3) No. of Rows: 1=Single Row; 2=Dual Row
(4) No. of Pins Per Row: 1~40
(5) Insulator Material Height: 15=1.5mm; 20=2.0mm; 25=2.5mm
(6) Connector Type: S=Straight; R=Right; Angle M=SMT
(7) Contact Material Length: 115=11.5mm 130=13.0mm
(8) No. of Insulator Material: 1=1PCS; 2=2PCS; 3=3PCS
(9) Contact Plating.

SN=Tin; G0=Gold Flash; S0=Gold Flash/Tin; AU08=Au 0.8u"
(10) Insulator Material Option.

A=BK-PBT; B=BK-PA6T; C=BK-PA46; D=KB-LCP; S=Special

17-0045-001

HJ-Tech 东莞市皇捷通讯科技有限公司
DONGGUAN HUANGJIE COMMUNICATION TECHNOLOGY CO., LTD.

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.3 X° : ±5°
X.X : ±0.2 X.X° : ±1°
X.XX : ±0.1 X.XX° : ±0.5°

DRAWN NAME.

2.54PH 1x4PIN 2.5塑高 180° DIP L11.5 双塑 镀金 PA6T

SIZE

A4

SCALE

N:1

PRODUCT NO.

17-0045-001

REV

A

UNIT

mm

PROJECT

APPROVED:

PAGE 1/1

CHECKED: LU JING NUAN 2020/11/24 CHECKED: / / APPROVED: / /

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.54	11	25.40	27.94	21	50.80	53.34	31	76.20	78.74
2	2.54	5.08	12	27.94	30.48	22	53.34	55.88	32	78.74	81.28
3	5.08	7.62	13	30.48	33.02	23	55.88	58.42	33	81.28	83.82
4	7.62	10.16	14	33.02	35.56	24	58.42	60.96	34	83.82	86.36
5	10.16	12.70	15	35.56	38.10	25	60.96	63.50	35	86.36	88.90
6	12.70	15.24	16	38.10	40.64	26	63.50	66.04	36	88.90	91.44
7	15.24	17.78	17	40.64	43.18	27	66.04	68.58	37	91.44	93.98
8	17.78	20.32	18	43.18	45.72	28	68.58	71.12	38	93.98	96.52
9	20.32	22.86	19	45.72	48.26	29	71.12	73.66	39	96.52	99.06
10	22.86	25.40	20	48.26	50.80	30	73.66	76.20	40	99.06	101.60