




## Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Idea for printed circuit board
- ◆ Glass passivated Junction chip
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed 250°C/10 seconds at terminals

**SMAF**

Dimensions in inches and (millimeters)

## Mechanical Data

**Case** : Molded plastic body**Terminals** : Solder plated, solderable per MIL-STD-750, Method 2026**Polarity** : Polarity symbol marking on body**Mounting Position** : Any**Weight** : 0.0014 ounce, 0.038 grams

## Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

| Parameter                                                                                                 | SYMBOLS                          | US2A        | US2B | US2D | US2G | US2J | US2K | US2M | UNITS |
|-----------------------------------------------------------------------------------------------------------|----------------------------------|-------------|------|------|------|------|------|------|-------|
| Maximum repetitive peak reverse voltage                                                                   | V <sub>RRM</sub>                 | 50          | 100  | 200  | 400  | 600  | 800  | 1000 | V     |
| Maximum RMS voltage                                                                                       | V <sub>RMS</sub>                 | 35          | 70   | 140  | 280  | 420  | 560  | 700  | V     |
| Maximum DC blocking voltage                                                                               | V <sub>DC</sub>                  | 50          | 100  | 200  | 400  | 600  | 800  | 1000 | V     |
| Maximum average forward rectified current at T <sub>L</sub> =100°C                                        | I <sub>(AV)</sub>                | 2.0         |      |      |      |      |      |      | A     |
| Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load                        | I <sub>FSM</sub>                 | 50.0        |      |      |      |      |      |      | A     |
| Maximum instantaneous forward voltage at 2.0A                                                             | V <sub>F</sub>                   | 1.0         |      |      | 1.4  | 1.7  |      |      | V     |
| Maximum DC reverse current   T <sub>A</sub> =25°C<br>at rated DC blocking voltage   T <sub>A</sub> =125°C | I <sub>R</sub>                   | 5.0<br>500  |      |      |      |      |      |      | uA    |
| Maxinum reverse recovery time(Note 1)                                                                     | T <sub>rr</sub>                  | 50          |      |      |      | 75   |      |      | ns    |
| Typical junction capacitance (Note2)                                                                      | C <sub>J</sub>                   | 50.0        |      |      |      |      |      |      | pF    |
| Typical thermal resistance                                                                                | R <sub>qJA</sub>                 | 70.0        |      |      |      |      |      |      | °C/W  |
| Operating junction and storage temperature range                                                          | T <sub>J</sub> ,T <sub>STG</sub> | -55 to +150 |      |      |      |      |      |      | °C    |

**Note:** 1.Reverse recovery time test condition:  $I_F=0.5\text{A}$   $I_R=1.0\text{A}$   $I_{rr}=0.25\text{A}$

2.Measured at 1MHz and applied reverse voltage of 4.0V D.C.



## Ratings And Characteristic Curves

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS






FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS



## Suggested Pad Layout



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| A      | 1.68      | 0.066       |
| B      | 1.52      | 0.060       |
| C      | 3.90      | 0.154       |
| D      | 2.00      | 0.078       |
| E      | 5.10      | 0.200       |