

Features

- ★ Green Device Available
- ★ Super Low Gate Charge
- ★ Excellent CdV/dt effect decline
- ★ Advanced high cell density Trench technology
- ★ 100% EAS Guaranteed

Description

THE 4606A is the highest performance trench N-ch and P-ch MOSFETs with extreme high cell density , which provide excellent RDSON and gate charge for most of the synchronous buck converter applications .

THE 4606A meet the RoHS and Green Product requirement , 100% EAS guaranteed with full function reliability approved.



Product Summary

| BVDSS | RDSON | ID |
|-------|-------|-----|
| 30V | 18mΩ | 7A |
| -30V | 35mΩ | -6A |

Applications

- ★ Power management in half bridge and inverters
- ★ DC-DC Converter
- ★ Load Switch

SOP8 Pin Configuration



Absolute Maximum Ratings

| Symbol | Parameter | Rating | | Units |
|-----------------------|--|------------|------------|------------|
| | | N-Channel | P-Channel | |
| V_{DS} | Drain-Source Voltage | 30 | -30 | V |
| V_{GS} | Gate-Source Voltage | ± 20 | ± 20 | V |
| $I_D@T_C=25^\circ C$ | Continuous Drain Current, $V_{GS} @ 10V^1$ | 7 | -6 | A |
| $I_D@T_C=100^\circ C$ | Continuous Drain Current, $V_{GS} @ 10V^1$ | 6 | -4 | |
| I_{DM} | Pulsed Drain Current ² | 20 | -12 | |
| E_{AS} | Single Pulse Avalanche Energy ³ | 72 | 59 | mJ |
| I_{AS} | Avalanche Current | 21 | -19 | A |
| $P_D@T_C=25^\circ C$ | Total Power Dissipation ⁴ | 2.5 | 2.08 | W |
| T_{STG} | Storage Temperature Range | -55 to 150 | -55 to 150 | $^\circ C$ |
| T_J | Operating Junction Temperature Range | -55 to 150 | -55 to 150 | |

Thermal Data

| Symbol | Parameter | Typ. | Max. | Unit |
|-----------------|--|------|------|--------------|
| $R_{\theta JA}$ | Thermal Resistance Junction-Ambient ¹ | - | 85 | $^\circ C/W$ |
| $R_{\theta JC}$ | Thermal Resistance Junction-Case ¹ | - | 50 | $^\circ C/W$ |

Electrical Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise specified)

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|------------------------------|--|--|------|-------|-----------|----------------------|
| BV_{DSS} | Drain-Source Breakdown Voltage | $V_{GS}=0V, I_D=250\mu A$ | 30 | - | - | V |
| $\Delta BV_{DSS}/\Delta T_J$ | BVDSS Temperature Coefficient | Reference to 25°C , $I_D=1\text{mA}$ | - | 0.034 | - | V/ $^\circ\text{C}$ |
| $R_{DS(on)}$ | Static Drain-Source On-Resistance ² | $V_{GS}=10V, I_D=6A$ | - | 18 | 25 | m Ω |
| | | $V_{GS}=4.5V, I_D=5A$ | - | 25 | 31 | |
| $V_{GS(th)}$ | Gate Threshold Voltage | $V_{GS}=V_{DS}, I_D=250\mu A$ | 1 | 1.5 | 2.5 | V |
| $\Delta V_{GS(th)}$ | $V_{GS(th)}$ Temperature Coefficient | | - | -5.8 | - | mV/ $^\circ\text{C}$ |
| I_{DSS} | Drain-Source Leakage Current | $V_{DS}=30V, V_{GS}=0V, T_J=25^\circ\text{C}$ | - | - | 1 | uA |
| | | $V_{DS}=30V, V_{GS}=0V, T_J=55^\circ\text{C}$ | - | - | 5 | |
| I_{GSS} | Gate-Source Leakage Current | $V_{GS}=\pm 20V, V_{DS}=0V$ | - | - | ± 100 | nA |
| g_{fs} | Forward Transconductance | $V_{DS}=15V, I_D=5A$ | - | 10 | - | S |
| R_g | Gate Resistance | $V_{DS}=24V, V_{GS}=0V, f=1\text{MHz}$ | - | 2.5 | - | Ω |
| Q_g | Total Gate Charge (4.5V) | | - | 7.2 | - | nC |
| Q_{gs} | Gate-Source Charge | $V_{DS}=20V, V_{GS}=4.5V, I_D=6A$ | - | 1.4 | - | |
| Q_{gd} | Gate-Drain Charge | | - | 2.2 | - | |
| $T_{d(on)}$ | Turn-On Delay Time | $V_{DD}=12V, V_{GS}=10V, R_G=3.3\Omega, I_D=5A$ | - | 3.9 | - | ns |
| T_r | Rise Time | | - | 9.2 | - | |
| $T_{d(off)}$ | Turn-Off Delay Time | | - | 14.5 | - | |
| T_f | Fall Time | | - | 6 | - | |
| C_{iss} | Input Capacitance | $V_{DS}=25V, V_{GS}=0V, f=1\text{MHz}$ | - | 370 | - | pF |
| C_{oss} | Output Capacitance | | - | 54 | - | |
| C_{rss} | Reverse Transfer Capacitance | | - | 40 | - | |

Guaranteed Avalanche Characteristics

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|--------|--|--|------|------|------|------|
| EAS | Single Pulse Avalanche Energy ⁵ | $V_{DD}=25V, L=0.1\text{mH}, I_{AS}=10A$ | 16 | --- | --- | mJ |

Diode Characteristics

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|----------|--|---|------|------|------|------|
| I_S | Continuous Source Current ^{1,6} | $V_G=V_D=0V$, Force Current | --- | --- | 7 | A |
| I_{SM} | Pulsed Source Current ^{2,6} | | --- | --- | 20 | A |
| V_{SD} | Diode Forward Voltage ² | $V_{GS}=0V, I_S=5A, T_J=25^\circ\text{C}$ | --- | --- | 1.2 | V |

Note :

- The data tested by surface mounted on a 1 inch² FR-4 board with 20Z copper, $t < 10\text{sec}$.
- The data tested by pulsed, pulse width $\leq 300\mu\text{s}$, duty cycle $\leq 2\%$
- The EAS data shows Max. rating. The test condition is $V_{DD}=25V, V_{GS}=10V, L=0.1\text{mH}, I_{AS}=10A$.
- The power dissipation is limited by 150°C junction temperature.
- The Min. value is 100% EAS tested guarantee.
- The data is theoretically the same as I_D and I_{DM} , in real applications, should be limited by total power dissipation.

Electrical Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise specified)

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|--|---|---|------|------|-----------|------------|
| Static Characteristics | | | | | | |
| $V_{(BR)DSS}$ | Drain-Source Breakdown Voltage | $V_{GS} = 0V, I_D = -250\mu A$ | -30 | - | - | V |
| I_{DSS} | Zero Gate Voltage Drain Current | $V_{DS} = -30V, V_{GS} = 0V$ | - | - | -1 | μA |
| I_{GSS} | Gate-Source Leakage | $V_{DS} = 0V, V_{GS} = \pm 20V$ | - | - | ± 100 | nA |
| $V_{GS(th)}$ | Gate-Source Threshold voltage | $V_{DS} = V_{GS}, I_D = -250\mu A$ | -1 | -1.5 | -2.5 | V |
| $R_{DS(on)}$ | Drain-Source on-State Resistance ³ | $V_{GS} = -10V, I_D = -4.1A$ | - | 36 | 60 | m Ω |
| | | $V_{GS} = -4.5V, I_D = -3A$ | - | 50 | 85 | |
| Dynamic Characteristics⁴ | | | | | | |
| C_{iss} | Input Capacitance | $V_{GS} = 0V, V_{DS} = -15V, f = 1.0MHz$ | - | 530 | - | pF |
| C_{oss} | Output Capacitance | | 70 | - | | |
| C_{rss} | Reverse Transfer Capacitance | | 56 | - | | |
| Switching Characteristics⁴ | | | | | | |
| Q_g | Total Gate Charge | $V_{GS} = -10V, V_{DS} = -15V, I_D = -4.1A$ | - | 6.8 | - | nC |
| Q_{gs} | Gate-Source Charge | | - | 1 | - | |
| Q_{gd} | Gate-Drain Charge | | - | 1.4 | - | |
| $t_{d(on)}$ | Turn-on Delay Time | $V_{GS} = -10V, V_{DS} = -15V, R_L = 15\Omega, R_{GEN} = 2.5\Omega$ | - | 14 | - | ns |
| t_r | Rise Time | | - | 61 | - | |
| $t_{d(off)}$ | Turn-off Delay time | | - | 19 | - | |
| t_f | Fall Time | | - | 10 | - | |
| Source-Drain Body Diode Characteristics | | | | | | |
| V_{SD} | Diode Forward Voltage ³ | $I_S = -4.1A, V_{GS} = 0V$ | - | - | -1.2 | V |
| I_S | Continuous Source Current | | - | - | -56 | A |

Notes:

- 1.Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)} = 150^\circ\text{C}$.
- 2.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper, The value in any given application depends on the user's specific board design.
- 3.Pulse Test: Pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.
- 4.This value is guaranteed by design hence it is not included in the production test.

N-Channel Typical Performance Characteristics

Figure 1: Typical Output Characteristics




Figure 2: On-Resistance vs. G-S Voltage




Figure 3: Forward Characteristics of Reverse




Figure 4: Gate-charge Characteristics




Figure 5: VGS(th) vs. TJ





Figure 6: Normalized RDS(on) vs. TJ



N-Channel Typical Performance Characteristics

Figure 7: Capacitance




Figure 8: Safe Operating Area




Figure 9: Normalized Maximum Transient




Figure 10: Switching Time Waveform





Figure 11: Unclamped Inductive Waveform



P-Channel Typical Performance Characteristics

Figure 1: Typical Output Characteristics




Figure 2: On-Resistance vs. G-S Voltage




Figure 3: Forward Characteristics of Reverse




Figure 4: Gate-charge Characteristics




Figure 5: $V_{GS(th)}$ vs. T_J





Figure 6: Normalized $R_{DS(on)}$ vs. T_J



P-Channel Typical Performance Characteristics

Figure7:Capacitance




Figure 8: Safe Operating Area




Figure9:Normalized Maximum Transient Thermal Response




Figure10:Switching Time Waveform




Figure 11: Unclamped Inductive Waveform

