

Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40°C-+125°C


温度范围: -40°C-+125°C

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance: 20mΩ Max

接触电阻: 20mΩ Max



X1011 W V S-2xXX S-9T XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2.Category:W-Wafer

3. Welding Board Angle: V-Stright 180°


4.Welding Way:S-SMT

5. Row.no.Pin no: 2xXX-2x02~2x25 Pin

6.Special No:S-Positioning column

7. Material: 9T-PA9T UL94V-0

8.Plating:V01-Gold Flash ; SM



Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
2x02	1.00	4.30	2.50	麦拉	2x11	10.00	13.30	11.50	7.00
2x03	2.00	5.30	3.50		2x12	11.00	14.30	12.50	
2x04	3.00	6.30	4.50		2x14	13.00	16.30	14.50	
2x05	4.00	7.30	5.50		2x15	14.00	17.30	15.50	
2x06	5.00	8.30	6.50	4.00	2x16	15.00	18.30	16.50	
2x07	6.00	9.30	7.50		2x18	17.00	20.30	18.50	
2x08	7.00	10.30	8.50	7.00	2x20	19.00	22.30	20.50	
2x09	8.00	11.30	9.50		2x25	24.00	27.30	25.50	
2x10	9.00	12.30	10.50			/			

X1011WVS-2xXS-9TXX	PA9T	Phosphor Bronze	X1011H
PART NO	Material	Material(Pin)	Suitable XKE Housing

DSND		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X1011WVS-2xXXS-9TXX
CHKD		UNIT: mm/in	DWG NO.: X-X1011WVS-2xXXS-9TXX
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKIE

XKB INDUSTRIAL PRECISION CO.,LIMITED