


Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	5000
2.Working Temperature (温度)	-55~+150 ℃
3.IP Rating (防护级别)	IP 50
4.Diameter of socket end(插合端直径)	φ2.0
5.Testing Voltage (测试电压)	1450V
6.Working Voltage (工作电压)	1250V
7.Rated Current (额定电流)	19A
8.Shell material(壳体材质)	Brass (chromium plating) shell and chuck nut/(nickel plating) pin sleeve and middleware/黄铜（镀铬）外壳和夹头螺母/（镀镍）插销套和中间件
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)
10. Insulator material(绝缘体材质)	L:PPS P:PEEK


Sum up(总结)	
Series(系列)	B
Shell style/model（外壳样式/型号）	TGG: Straight plug, cable collet and nut for fitting a bend relief直塞、电缆夹头和螺母，用于安装弯曲凸起
Button（按键）	A button(一个按键)
Termination type（终止类型）	Male solder(公焊锡)
Line diameter awg(线材直径)	22-14 AWG
Cable diameterφ（电缆直径）	φ8.3-9.2MM
Matching parts(配件)	ZGG.3B.P04.CXL

Location pin combination (定位销组合)			
(编号) Nunder	Number of positioning pins(定位销数量)	Angle(角度)	Series(系列)---3B
G	One(1)		(Zero degrees)0°
A	Two(2)	A	Thirty degrees(30°)
B	Two(2)		Forty-five degrees(45°)
C	Two(2)		Sixty degrees(60°)
D	Two(2)	γ	95 degrees（95°）
E	Two(2)	β	120 degrees(120°)
F	Two(2)		145 degrees(145°)
J	Two(2)	A	37.5degrees(37.5°)
K	Two(2)		52.5degrees(52.5°)
L	Two(2)	γ	Seventy degrees(70°)


	A	B	C√	ANGLE	
5-10	±0.02	±0.05	±0.1	0°-30°	±0.1°
50-100	±0.1	±0.15	±0.2	61°-90°	±0.5°
50-100	±0.15	±0.2	±0.25		
100-	±0.15%	±0.20%	±0.25%		




	A	L	M	S1	S2
MM	φ18	57	41.5	16.0	15
in	0.7087	2.2441	1.6339	0.6299	0.5906



Welded surface
(焊接面)



Solder core
(焊接型公胶芯)



Positive view
(正视图)

TG G. 3B. P04.C X A D 92 H

Model(型号)	TG
Positioning pin(定位销)	G.
Series(系列)	3B.
Needle core configuration(针芯配置)	P04.C
Outer casing(外壳)	X
Insulator(绝缘体)	A
Needle core(针芯)	D
Type of CXamp(线夹类型)	92
Cable diameter(电缆直径)	H

SH means a sheath type, not a cover type.
(H表示护套型，不表示为不带护套型)

DESIGNED (设计)		DATE(日期)		SCALE(比例)	N/A(不适用)	MODEL TYPE 型号类型: TGG.3B.P04.CXAD92H
CHECKED (校对)		DATE(日期)		VIEW(视图)		PART NO. 3B4-core plug
APPROVED (审核)		DATE(日期)		UNIT(单位)	MM	名称: 3B4芯插头
REVISIONS				MATERIAL (材料)		DWG NO.:
www.helloxkb.com www.helloxkb.cn			XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT(重量)
						SHEET(表)
						REVISION(修订)
						1/1
						A0