



# MMBT7002BK

## N-Channel Enhancement Mode MOSFET

### Features

- Very fast switching
- Built-in G-S Protection Diode
- Typical ESD Protection HBM Class 2

Classification	Voltage Range(V)
0A	< 125
0B	125 to < 250
1A	250 to < 500
1B	500 to < 1000
1C	1000 to < 2000
2	2000 to < 4000
3A	4000 to < 8000
3B	$\geq 8000$



1. Gate 2. Source 3. Drain  
SOT-23 Plastic Package

### Application

- Portable appliances
- Battery management

### Absolute Maximum Ratings(at $T_a = 25^\circ\text{C}$ unless otherwise specified)


Parameter	Symbol	Value	Unit
Drain-Source Voltage	$V_{DS}$	60	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current	$I_D$	350	mA
Pulsed Drain Current <sup>1)</sup>	$I_{DM}$	2	A
Power Dissipation <sup>2)</sup>	$P_D$	370	mW
Operating Junction Temperature	$T_j$	150	$^\circ\text{C}$
Storage Temperature Range	$T_{stg}$	- 65 to + 150	$^\circ\text{C}$

### Thermal Resistance Ratings

Parameter	Symbol	Max.	Unit
Thermal Resistance from Junction to Ambient <sup>2)</sup>	$R_{\theta JA}$	340	$^\circ\text{C/W}$

<sup>1)</sup> Pulse Test: Pulse Width  $\leq 100 \mu\text{s}$ , Duty Cycle  $\leq 2\%$ , Repetitive rating, pulse width limited by junction temperature  $T_{J(MAX)} = 150^\circ\text{C}$ .


<sup>2)</sup> Device mounted on FR-4 substrate PC board, with minimum recommended pad layout.



# MMBT7002BK

Characteristics at  $T_a = 25^\circ\text{C}$  unless otherwise specified

Parameter	Symbol	Min.	Typ.	Max.	Unit
<b>STATIC PARAMETERS</b>					
Drain-Source Breakdown Voltage at $I_D = 10 \mu\text{A}$	$V_{(\text{BR})\text{DSS}}$	60	-	-	V
Zero Gate Voltage Drain Current at $V_{DS} = 60 \text{ V}$	$I_{DSS}$	-	-	1	$\mu\text{A}$
Gate-Source Leakage at $V_{GS} = 20 \text{ V}$	$I_{GSS}$	-	-	10	$\mu\text{A}$
Gate-Source Threshold Voltage at $V_{DS} = V_{GS}$ , $I_D = 250 \mu\text{A}$	$V_{GS(\text{th})}$	1.1	-	2.1	V
Drain-Source On-State Resistance at $V_{GS} = 10 \text{ V}$ , $I_D = 500 \text{ mA}$ at $V_{GS} = 5 \text{ V}$ , $I_D = 50 \text{ mA}$	$R_{DS(\text{on})}$	-	-	1.6 2	$\Omega$
<b>DYNAMIC PARAMETERS</b>					
Gate resistance at $V_{DS} = 0 \text{ V}$ , $f = 1 \text{ MHz}$	$R_g$	-	37	-	$\Omega$
Forward Transconductance at $V_{DS} = 10 \text{ V}$ , $I_D = 200 \text{ mA}$	$g_{fs}$	-	307	-	$\text{mS}$
Input Capacitance at $V_{DS} = 10 \text{ V}$ , $V_{GS} = 0 \text{ V}$ , $f = 1 \text{ MHz}$	$C_{iss}$	-	31	-	$\text{pF}$
Output Capacitance at $V_{DS} = 10 \text{ V}$ , $V_{GS} = 0 \text{ V}$ , $f = 1 \text{ MHz}$	$C_{oss}$	-	11	-	$\text{pF}$
Reverse Transfer Capacitance at $V_{DS} = 10 \text{ V}$ , $V_{GS} = 0 \text{ V}$ , $f = 1 \text{ MHz}$	$C_{rss}$	-	8	-	$\text{pF}$
Total Gate Charge at $V_{DS} = 30 \text{ V}$ , $I_D = 1 \text{ A}$ , $V_{GS} = 10 \text{ V}$ at $V_{DS} = 30 \text{ V}$ , $I_D = 1 \text{ A}$ , $V_{GS} = 4.5 \text{ V}$	$Q_g$	- -	1.1 0.4	-	$\text{nC}$
Gate to Source Charge at $V_{DS} = 30 \text{ V}$ , $I_D = 1 \text{ A}$ , $V_{GS} = 10 \text{ V}$	$Q_{gs}$	-	0.5	-	$\text{nC}$
Gate to Drain Charge at $V_{DS} = 30 \text{ V}$ , $I_D = 1 \text{ A}$ , $V_{GS} = 10 \text{ V}$	$Q_{gd}$	-	0.2	-	$\text{nC}$
Turn-On Delay Time at $V_{DD} = 30 \text{ V}$ , $V_{GS} = 10 \text{ V}$ , $I_D = 1 \text{ A}$ , $R_g = 6.8 \Omega$	$t_{d(\text{on})}$	-	4.8	-	ns
Turn-On Rise Time at $V_{DD} = 30 \text{ V}$ , $V_{GS} = 10 \text{ V}$ , $I_D = 1 \text{ A}$ , $R_g = 6.8 \Omega$	$t_r$	-	3	-	ns
Turn-Off Delay Time at $V_{DD} = 30 \text{ V}$ , $V_{GS} = 10 \text{ V}$ , $I_D = 1 \text{ A}$ , $R_g = 6.8 \Omega$	$t_{d(\text{off})}$	-	4.4	-	ns
Turn-Off Fall Time at $V_{DD} = 30 \text{ V}$ , $V_{GS} = 10 \text{ V}$ , $I_D = 1 \text{ A}$ , $R_g = 6.8 \Omega$	$t_f$	-	15	-	ns
<b>Body-Diode PARAMETERS</b>					
Drain-Source Diode Forward Voltage at $I_s = 115 \text{ mA}$	$V_{SD}$	-	-	1.1	V
Body-Diode Continuous Current	$I_s$	-	-	350	$\text{mA}$
Body Diode Reverse Recovery Time at $I_s = 1 \text{ A}$ , $di/dt = 100 \text{ A} / \mu\text{s}$	$t_{rr}$	-	8.4	-	ns
Body Diode Reverse Recovery Charge at $I_s = 1 \text{ A}$ , $di/dt = 100 \text{ A} / \mu\text{s}$	$Q_{rr}$	-	3.6	-	$\text{nC}$



# MMBT7002BK

## Electrical Characteristics Curves

Fig. 1 Typical Output Characteristics




Fig. 2 Typical Transfer Characteristics




Fig. 3 on-Resistance vs. Drain Current




Fig. 4 on-Resistance vs. Gate-Source Voltage




Fig. 5 on-Resistance vs.  $T_j$






Fig. 6 Typical Forward Characteristics



# MMBT7002BK

## Electrical Characteristics Curves

Fig. 7 Typical Junction Capacitance




Fig. 8 Drain-Source Leakage Current vs.  $T_j$




Fig. 9  $V_{(BR)DSS}$  vs. Junction Temperature




Fig. 10 Gate Threshold Variation vs.  $T_j$






Fig. 11 Gate Charge



# MMBT7002BK

## Test Circuits

Fig.1-1 Switching times test circuit




Fig.1-2 Switching Waveform




Fig.2-1 Gate charge test circuit







Fig.2-2 Gate charge waveform



# MMBT7002BK


## Package Outline (Dimensions in mm)

SOT-23



Unit	A	A1	B	C	D	E	F	G	L	L1
mm	1.20	0.100	1.40	0.19	3.04	2.6	1.02	2.04	0.51	0.2
	0.89	0.013	1.20	0.08	2.80	2.2	0.89	1.78	0.37	MIN

## Recommended Soldering Footprint



## Packing information

Package	Tape Width (mm)	Pitch		Reel Size		Per Reel Packing Quantity
		mm	inch	mm	inch	
SOT-23	8	4 ± 0.1	0.157 ± 0.004	178	7	3,000

## Marking information

" K1 " = Part No.

" YM " = Date Code Marking

" Y " = Year

" M " = Month

Font type: Arial

