

## 79LXX

## LINEAR INTEGRATED CIRCUIT


## 3-Terminal 0.1A NEGATIVE VOLTAGE REGULATOR

## ■ DESCRIPTION

The UTC **79LXX** family is monolithic fixed voltage regulator integrated circuit. They are suitable for applications that required supply current up to 100mA.

## ■ FEATURES

- \* Output current up to 100mA.
- \* Fixed output voltage of -5V, -6V, -8V, -9V, -10V, -12V, -15V, -18V and -24V available.
- \* Thermal overload shutdown protection.
- \* Short circuit current limiting.




## ■ ORDERING INFORMATION




Ordering Number		Package	Pin Assignment								Packing
Lead Free	Halogen Free		1	2	3	4	5	6	7	8	
79LXXL-AB3-R	79LXXG-AB3-R	SOT-89	G	I	O	-	-	-	-	-	Tape Reel
79LXXL-S08-R	79LXXG-S08-R	SOP-8	O	I	I	N	G	I	I	N	Tape Reel
79LXXL-T92-B	79LXXG-T92-B	TO-92	G	I	O	-	-	-	-	-	Tape Box
79LXXL-T92-K	79LXXG-T92-K	TO-92	G	I	O	-	-	-	-	-	Bulk

Notes: 1. XX: Output Voltage, refer to Marking Information


2. Note: Pin Assignment: I:V<sub>IN</sub> O:V<sub>OUT</sub> G:GND

 79LXXG-AB3-R	(1)Packing Type (2)Package Type (3)Green Package (4)Output Voltage Code	(1) R: Tape Reel, B: Tape Box, K: Bulk (2) AB3: SOT-89, S08: SOP-8, T92: TO-92 (3) G: Halogen Free and Lead Free, L: Lead Free (4) XX: refer to Marking Information
---	--	--

#### ■ MARKING INFORMATION

PACKAGE	VOLTAGE CODE	MARKING
SOT-89		 <p>Date Code Voltage Code</p> <p>L: Lead Free G: Halogen Free</p>
TO-92	05:-5.0V 06:-6.0V 08:-8.0V 09:-9.0V 10:-10V 12:-12V 15:-15V 18:-18V 24:-24V	 <p>G: Halogen Free L: Lead Free Voltage Code Date Code</p>
SOP-8		 <p>L: Lead Free G: Halogen Free</p> <p>Date Code Voltage Code Lot Code</p>

## ■ BLOCK DIAGRAM



### ■ ABSOLUTE MAXIMUM RATINGS

PARAMETER		SYMBOL	VALUE	UNIT
Input Voltage	$V_{OUT} = -5 \sim -9V$	$V_{IN}$	-30	V
	$V_{OUT} = -12 \sim -15V$		-35	V
	$V_{OUT} = -18 \sim -24V$		-35	V
Power Dissipation	SOT-89	$P_D$	350	mW
	SOP-8		300	mW
	TO-92		625	mW
Operating Temperature	$T_{OPR}$		-40 ~ +125	°C
Storage Temperature	$T_{STG}$		-40 ~ +150	°C

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

### ■ ELECTRICAL CHARACTERISTICS

**79L05**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{OUT}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output Voltage	$V_{OUT}$	$V_{IN}=-10V$ , $I_{OUT}=40\text{mA}$	-4.8	-5.0	-5.2	V
Line Regulation	$\frac{\Delta V_{OUT}}{\Delta V_{IN} \times V_{OUT}}$	$V_{IN}=-7 \sim -20V$ , $I_{OUT}=40\text{mA}$		15	150	mV
Load Regulation	$\frac{\Delta V_{OUT}}{\Delta I_{OUT} \times V_{OUT}}$	$V_{IN}=-10V$ , $I_{OUT}=1 \sim 100\text{mA}$		7	60	mV
Quiescent current	$I_Q$	$V_{IN}=-10V$ , $I_{OUT}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{IN}=-8 \sim -18V$ , $I_{OUT}=40\text{mA}$ , $e_{IN}=1V_{P-P}$ , $f=120\text{Hz}$	41	71		dB
Output Voltage Noise	$e_N$	$V_{IN}=-10V$ , $I_{OUT}=40\text{mA}$ $BW=10\text{Hz} \sim 100\text{kHz}$		120		$\mu\text{V}$

**79L06**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{OUT}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output Voltage	$V_{OUT}$	$V_{IN}=-12V$ , $I_{OUT}=40\text{mA}$	-5.76	-6.0	-6.24	V
Line Regulation	$\frac{\Delta V_{OUT}}{\Delta V_{IN} \times V_{OUT}}$	$V_{IN}=-8.5 \sim -20V$ , $I_{OUT}=40\text{mA}$		15	150	mV
Load Regulation	$\frac{\Delta V_{OUT}}{\Delta I_{OUT} \times V_{OUT}}$	$V_{IN}=-12V$ , $I_{OUT}=1 \sim 100\text{mA}$		7	60	mV
Quiescent current	$I_Q$	$V_{IN}=-12V$ , $I_{OUT}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{IN}=-9 \sim -19V$ , $I_{OUT}=40\text{mA}$ $e_{IN}=1V_{P-P}$ , $f=120\text{Hz}$	41	71		dB
Output Voltage Noise	$e_N$	$V_{IN}=-12V$ , $I_{OUT}=40\text{mA}$ $BW=10\text{Hz} \sim 100\text{kHz}$		120		$\mu\text{V}$

**79L08**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{OUT}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	Test conditions	MIN	TYP	MAX	UNIT
Output Voltage	$V_{OUT}$	$V_{IN}=-14V$ , $I_{OUT}=40\text{mA}$	-7.68	-8.0	-8.32	V
Line Regulation	$\frac{\Delta V_{OUT}}{\Delta V_{IN} \times V_{OUT}}$	$V_{IN}=-10.5 \sim -23V$ , $I_{OUT}=40\text{mA}$		24	175	mV
Load Regulation	$\frac{\Delta V_{OUT}}{\Delta I_{OUT} \times V_{OUT}}$	$V_{IN}=-14V$ , $I_{OUT}=1 \sim 100\text{mA}$		10	80	mV
Quiescent current	$I_Q$	$V_{IN}=-14V$ , $I_{OUT}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{IN}=-11 \sim -21V$ , $I_{OUT}=40\text{mA}$ $e_{IN}=1V_{P-P}$ , $f=140\text{Hz}$	39	68		dB
Output Voltage Noise	$e_N$	$V_{IN}=-14V$ , $I_{OUT}=40\text{mA}$ $BW=10\text{Hz} \sim 100\text{kHz}$		190		$\mu\text{V}$

## ■ ELECTRICAL CHARACTERISTICS(Cont.)

**79L09**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{\text{OUT}}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output Voltage	$V_{\text{OUT}}$	$V_{\text{IN}}=-15\text{V}$ , $I_{\text{OUT}}=40\text{mA}$	-8.64	-9.0	-9.36	V
Line Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta V_{\text{IN}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-12.5\sim-24\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		27	200	mV
Load Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta I_{\text{OUT}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-15\text{V}$ , $I_{\text{OUT}}=1\sim100\text{mA}$		12	90	mV
Quiescent current	$I_Q$	$V_{\text{IN}}=-15\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{\text{IN}}=-12\sim-22\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ $e_{\text{IN}}=1\text{V}_{\text{P-P}}, f=150\text{Hz}$	37	64		dB
Output Voltage Noise	eN	$V_{\text{IN}}=-15\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ BW=10Hz~100kHz		210		$\mu\text{V}$

**79L10**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{\text{OUT}}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output Voltage	$V_{\text{OUT}}$	$V_{\text{IN}}=-16\text{V}$ , $I_{\text{OUT}}=40\text{mA}$	-9.6	-10	-10.4	V
Line Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta V_{\text{IN}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-13\sim-24\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		30	220	mV
Load Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta I_{\text{OUT}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-16\text{V}$ , $I_{\text{OUT}}=1\sim100\text{mA}$		15	95	mV
Quiescent current	$I_Q$	$V_{\text{IN}}=-16\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{\text{IN}}=-13\sim-23\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ $e_{\text{IN}}=1\text{V}_{\text{P-P}}, f=150\text{Hz}$	37	64		dB
Output Voltage Noise	eN	$V_{\text{IN}}=-16\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ BW=10Hz~100kHz		210		$\mu\text{V}$

**79L12**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{\text{OUT}}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output Voltage	$V_{\text{OUT}}$	$V_{\text{IN}}=-19\text{V}$ , $I_{\text{OUT}}=40\text{mA}$	-11.52	-12.0	-12.48	V
Line Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta V_{\text{IN}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-14.5\sim-27\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		36	250	mV
Load Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta I_{\text{OUT}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-19\text{V}$ , $I_{\text{OUT}}=1\sim100\text{mA}$		16	100	mV
Quiescent current	$I_Q$	$V_{\text{IN}}=-19\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{\text{IN}}=-15\sim-25\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ $e_{\text{IN}}=1\text{V}_{\text{P-P}}, f=190\text{Hz}$	37	64		dB
Output Voltage Noise	eN	$V_{\text{IN}}=-19\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ BW=10Hz~100kHz		210		$\mu\text{V}$

**79L15**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{\text{OUT}}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output Voltage	$V_{\text{OUT}}$	$V_{\text{IN}}=-23\text{V}$ , $I_{\text{OUT}}=40\text{mA}$	-14.4	-15.0	-15.6	V
Line Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta V_{\text{IN}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-17.5\sim-30\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		45	300	mV
Load Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta I_{\text{OUT}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-23\text{V}$ , $I_{\text{OUT}}=1\sim100\text{mA}$		20	150	mV
Quiescent current	$I_Q$	$V_{\text{IN}}=-23\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{\text{IN}}=-18.5\sim-28.5\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ $e_{\text{IN}}=1\text{V}_{\text{P-P}}, f=230\text{Hz}$	34	63		dB
Output Voltage Noise	eN	$V_{\text{IN}}=-23\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ BW=10Hz~100kHz		340		$\mu\text{V}$

## ■ ELECTRICAL CHARACTERISTICS(Cont.)


**79L18**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{\text{OUT}}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output Voltage	$V_{\text{OUT}}$	$V_{\text{IN}}=-27\text{V}$ , $I_{\text{OUT}}=40\text{mA}$	-17.28	-18.0	-18.72	V
Line Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta V_{\text{IN}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-20.5\text{~}33\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		54	300	mV
Load Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta I_{\text{OUT}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-27\text{V}$ , $I_{\text{OUT}}=1\text{~}100\text{mA}$		23	170	mV
Quiescent current	$I_Q$	$V_{\text{IN}}=-27\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{\text{IN}}=-23\text{~}33\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ $e_{\text{IN}}=1\text{V}_{\text{P-P}}$ , $f=270\text{Hz}$	33	60		dB
Output Voltage Noise	$e_N$	$V_{\text{IN}}=-27\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ BW=10Hz~100kH		410		$\mu\text{V}$







**79L24**( $T_J=25^\circ\text{C}$ ,  $C_1=0.33\mu\text{F}$ ,  $C_{\text{OUT}}=1\mu\text{F}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output Voltage	$V_{\text{OUT}}$	$V_{\text{IN}}=-33\text{V}$ , $I_{\text{OUT}}=40\text{mA}$	-23.04	-24.0	-24.96	V
Line Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta V_{\text{IN}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-27\text{~}38\text{V}$ , $I_{\text{O}}=40\text{mA}$		72	350	mV
Load Regulation	$\frac{\Delta V_{\text{OUT}}}{\Delta I_{\text{OUT}} \times V_{\text{OUT}}}$	$V_{\text{IN}}=-33\text{V}$ , $I_{\text{OUT}}=1\text{~}100\text{mA}$		30	200	mV
Quiescent current	$I_Q$	$V_{\text{IN}}=-33\text{V}$ , $I_{\text{OUT}}=40\text{mA}$		3.5	6.0	mA
Ripple Rejection	RR	$V_{\text{IN}}=-29\text{~}35\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ $e_{\text{IN}}=1\text{V}_{\text{P-P}}$ , $f=330\text{Hz}$	31	55		dB
Output Voltage Noise	$e_N$	$V_{\text{IN}}=-33\text{V}$ , $I_{\text{OUT}}=40\text{mA}$ BW=10Hz~100kH		550		$\mu\text{V}$




### ■ APPLICATION CIRCUIT



■ TYPICAL CHARACTERISTICS



■ TYPICAL CHARACTERISTICS(Cont.)



UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. UTC reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.