






Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+120℃

温度范围: -40℃-+120℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2007 W R S - XX -LP SN

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:R-Stright 90°

4.Welding Way:S-SMT

5.Row No.Pin No:XX-02~08P

6.Material:LP-LCP UL94V-0 Beige

7.Plating:SN-Tin Plated

Poles	Dimensions(mm)		
	A	B	C
02	2.00	6.80	8.30
03	4.00	8.80	10.30
04	6.00	10.80	12.30
05	8.00	12.80	14.30
06	10.00	14.80	16.30
07	12.00	16.80	18.30
08	14.00	18.80	20.30

SUGGESTED PCB LAYOUT

Assembly Layout

X2007WRS-XX-LPSN	LCP	Phosphor Bronze	X2007HM
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X2007WRS-XX-LPSN		
CHKD		UNIT: mm/in	DWG NO.: X-X2007WRS-XX-LPSN		
APPD		SIZE: A4	WEIGHT		
L PRECISION CO., LIMITED			SHEET		REVISION
			1/1		A0

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

广东星坤科技股份有限公司

生效 MARK

文件工程章

DESCRIPTION

REVISIONS

DATE

REVISED

APPROVED

ANGULAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5
UNSPECIFIED TOLERANCES	

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn