




Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:7A AC/DC

额定电流: 7A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25°C-+85°C


温度范围: -25℃-+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max



X9396	W	V - XX	S-	N0	SN
①	②	③	④	⑤	⑥

1.Series No

2. Category: W-Wafer

3. Welding Board Angle: V-Stright 180°


4.Row No.Pin No:XX-02~15P

5. Category: S-With positioning column

6Material:N0-PA66 UL94V-0

7. Plating: SN-Tin Plated

PCB LAYOUT



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.9600	9.8000	09	31.6800	37.5200
03	7.9200	13.7600	10	35.6400	41.4800
04	11.8800	17.7200	11	39.6000	45.4400
05	15.8400	21.6800	12	43.5600	49.4000
06	19.8000	25.6400	13	47.5200	53.3600
07	23.7600	29.6000	14	51.4800	57.3200
08	27.7200	33.5600	15	55.4400	61.2800

X9396WV-XXS-N0SN	PA66	Brass	X9396H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 3.96mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X9396VW-XXS-N0SN		
CHKD		UNIT: mm/in			
APPD		SIZE: A4	DWG NO.: X-X9396VW-XXS-N0SN		
PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

广东星坤科技股份有限公司							ANGLAR	±5°
Δx							L ≤ 4	±0.2
Δx		日期					4 < L ≤ 16	±0.3
Δx		期					16 < L ≤ 63	±0.4
MARK		DESCRIPTION		DATE	REVISED	APPROVED	L > 63	±0.5
零件工程图							UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn								

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED