


**SPECIFICATIONS**

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer LCP UL94-V0  
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-VH-2AWT-X	3.96	9.90	11.88
3	HC-VH-3AWT-X	7.92	13.86	15.84
4	HC-VH-4AWT-X	11.88	17.82	19.80
5	HC-VH-5AWT-X	15.84	21.78	23.76
6	HC-VH-6AWT-X	19.80	25.74	27.72
7	HC-VH-7AWT-X	23.76	29.70	31.68
8	HC-VH-8AWT-X	27.72	33.66	35.64
9	HC-VH-9AWT-X	31.68	37.62	39.60
10	HC-VH-10AWT-X	35.64	41.58	43.56
11	HC-VH-11AWT-X	39.60	45.54	47.52
12	HC-VH-12AWT-X	43.56	49.50	51.48

**Ordering Information**



			GENERAL TOLERANCE		制图 DRAWING		<b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	VH (3.96)卧贴	版本 REV.	A
			X.XX	±0.20	比例 SCALE		产品料号 PART NO.	HC-VH-NAWT-X	单位 UNITS	mm
			X.XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°							