



■ 规格表 SPECIFICATIONS



■ 外形图 DIMENSIONS (mm)



ΦD	5	6.3	8	10	13	16	18
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5
Φd	0.5	0.5	0.5	0.6	0.6	0.8	0.8

α	$(L < 20) 1.0$
	$(L \geq 20) 2.0$

● 频率系数 Frequency Multipliers

Rated Voltage(V)	Frequency(Hz)	120	1K	10K	100K
	Case code				
6.3 10	Φ5 (~ 47μF)	0.40	0.75	0.93	1.00
	Φ5 (100μF),Φ6.3,Φ8	0.70	0.86	0.96	1.00
	Φ10 ~ Φ18	0.85	0.95	0.98	1.00
16 ~ 35	Φ5 (to 22μF)	0.30	0.68	0.91	1.00
	Φ5 (33μF ~),Φ6.3,Φ8	0.50	0.80	0.94	1.00
	Φ10 ~ Φ18	0.70	0.88	0.97	1.00
50 63	Φ5 (~ 3.3μF)	0.20	0.66	0.90	1.00
	Φ5 (4.7μF ~),Φ6.3,Φ8	0.40	0.76	0.93	1.00
	Φ10 ~ Φ18	0.60	0.84	0.96	1.00
100	Φ5 (~ 1μF)	0.20	0.60	0.88	1.00
	Φ5 (2.2μF ~),Φ6.3,Φ8	0.30	0.65	0.90	1.00
	Φ10 ~ Φ18	0.40	0.75	0.93	1.00
160 ~ 450	Φ10	0.25	0.61	0.88	1.00
	Φ12.5 ~ Φ18	0.35	0.66	0.89	1.00

■ 尺寸与最大纹波电流一览表 STANDARD RATINGS

WV(V) cap(μF)	6.3(0J)				10(1A)				16(1C)				25(1E)			
4.7													5×11	3.0	9.0	104
10									5×11	2.0	6.0	126	5×11	2.0	6.0	126
22					5×11	1.3	3.9	156	5×11	1.3	3.9	158	5×11	1.3	3.9	158
33	5×11	1.3	3.9	158	5×11	1.3	3.9	158	5×11	1.3	3.9	158	5×11	1.3	3.9	158
47	5×11	1.3	3.9	158	5×11	1.3	3.9	158	5×11	1.3	3.9	158	5×11	1.3	3.9	158
100	5×11	1.3	3.9	158	5×11	1.3	3.9	158	6.3×11	0.60	1.8	264	6.3×11	0.60	1.8	264
220	6.3×11	0.60	1.8	264	6.3×11	0.60	1.8	264	8×12	0.33	0.99	405	8×12	0.3	1.0	405
330	6.3×11	0.60	1.8	264	8×12	0.33	0.99	405	8×12	0.33	0.99	405	10×13	0.3	0.8	512
470	8×12	0.33	0.99	404	8×12	0.33	0.99	405	10×13	0.25	0.75	514	10×16	0.2	0.57	638
1,000	10×13	0.25	0.75	514	10×16	0.19	0.57	638	10×20	0.14	0.42	864	13×20	0.085	0.26	1125
2,200	13×20	0.085	0.26	1125	13×20	0.085	0.26	1124	13×25	0.070	0.21	1325	16×25	0.060	0.18	1578
3,300	13×20	0.085	0.26	1,125	13×25	0.070	0.21	1,325	16×25	0.060	0.18	1,578	16×31.5	0.048	0.14	1,814
4,700	16×25	0.060	0.18	1,578	16×25	0.060	0.18	1,576	16×31.5	0.048	0.14	1,814	18×35.5	0.037	0.11	2,245
6,800	16×25	0.060	0.18	1,578	16×31.5	0.048	0.14	1,814	18×35.5	0.037	0.11	2,240	18×40	0.034	0.10	2,465
10,000	16×31.5	0.048	0.14	1,815	18×35.5	0.037	0.11	2,245	18×40	0.034	0.10	2,465				
15,000	18×35.5	0.037	0.11	2,245												

WV(V) cap(μF)	35(1V)				50(1H)				63(1J)				100(2A)			
0.47					5×11	7.0	21.0	68					5×11	10.0	35.0	58
1.0					5×11	5.0	15.0	79					5×11	7.0	25.0	69
2.2					5×11	4.0	12.0	89					5×11	6.0	21.0	78
3.3					5×11	3.5	11.0	95					5×11	5.0	18.0	80
4.7	5×11	3.0	9.0	104	5×11	3.0	9.0	104	5×11	4.0	14.0	89	5×11	4.0	14.0	89
10	5×11	2.0	6.0	128	5×11	0.0	6.0	128	5×11	2.5	8.8	125	6.3×11	1.2	4.2	184
22	5×11	1.3	3.9	156	5×11	1.3	3.9	158	6.3×11	1.2	4.2	184	8×12	0.66	2.3	286
33	5×11	1.3	3.9	158	6.3×11	0.60	1.8	264	6.3×11	1.2	4.2	184	10×13	0.50	1.8	385
47	6.3×11	0.60	1.8	264	6.3×11	0.60	1.8	264	8×12	0.56	2.0	306	10×16	0.32	1.1	504
100	8×12	0.33	1.0	405	8×12	0.33	0.99	405	10×13	0.50	1.8	384	13×20	0.16	0.56	895
220	10×13	0.25	0.75	514	10×16	0.19	0.57	638	10×20	0.27	0.95	624	16×25	0.090	0.32	1,445
330	10×16	0.19	0.57	635	10×20	0.14	0.42	864	13×20	0.16	0.56	892	16×25	0.090	0.32	1,445
470	10×20	0.14	0.42	864	13×20	0.085	0.26	1,124	13×20	0.14	0.49	1,045	16×31.5	0.060	0.21	1,795
1,000	13×25	0.070	0.21	1,324	16×25	0.060	0.18	1,578	16×31.5	0.060	0.21	1,795				
2,200	16×31.5	0.048	0.14	1,814	18×35.5	0.037	0.11	2,245								
3,300	18×35.5	0.037	0.11	2,245												
4,700	18×40	0.034	0.10	2,465												
6,800																

WV(V) cap(μF)	160(2C)			200(2D)			250(2E)		
4.7							10×16	3.5	164
10	10×16	1.5	254	10×16	1.5	254	10×20	2.8	234
22	10×20	1.1	354	10×20	1.1	352	13×25	1.2	368
33	13×20	0.71	445	13×20	0.71	448	13×25	1.2	368
47	13×25	0.46	604	13×25	0.46	605	16×25	0.60	578
100	16×25	0.24	912	16×31.5	0.17	1,168	18×35.5	0.30	938
220	18×35.5	0.14	1,375	18×35.5	0.14	1,378	18×40	0.27	1,004

WV(V) cap(μF)	400(2G)			450(2W)		
2.2				10×16	7.9	114
3.3	10×20	2.9	198	10×20	6.2	138
4.7	10×25	2.3	224	13×20	3.7	195
10	13×25	1.2	364	13×25	2.6	256
22	16×25	0.61	573	16×31.5	1.0	484
33	16×31.5	0.46	706	18×35.5	0.62	658
47	18×31.5	0.33	868			

↑ ripple current : (mA rms / 105 °C, 100KHz)
 ↑ Impedance : (Ω max / 20 °C, 100KHz)
 ↑ Impedance : ΦD × L (mm)