



Recommended
P.C. Board Hole Layout



Specifications

- Current Rating : 2 Amps
- Insulator Resistance : 1000 Megohms min.
- Contact Resistance : 20 m ohms max.
- Dielectric Withstanding : AC 500V
- Operating Temperature : -40°C ~ +105°C
- Contact Material : Brass
- Insulator Material : Polyester, UL 94V-0-PA6T
- Contact Plated : See Option / Standard: Full Gold Flash

Cir- cuits	Dimension (mm)	
	L1	L2
1x02	2.00	4.00
1x03	4.00	6.00
1x04	6.00	8.00
1x05	8.00	10.00
1x06	10.00	12.00
1x07	12.00	14.00
1x08	14.00	16.00
1x09	16.00	18.00
1x10	18.00	20.00
1x11	20.00	22.00
1x12	22.00	24.00
1x13	24.00	26.00
1x14	26.00	28.00
1x15	28.00	30.00
1x16	30.00	32.00
1x17	32.00	34.00
1x18	34.00	36.00
1x19	36.00	38.00
1x20	38.00	40.00
1x21	40.00	42.00
1x22	42.00	44.00
1x23	44.00	46.00
1x24	46.00	48.00
1x25	48.00	50.00
1x26	50.00	52.00
1x27	52.00	54.00
1x28	54.00	56.00
1x29	56.00	58.00
1x30	58.00	60.00
1x31	60.00	62.00
1x32	62.00	64.00
1x33	64.00	66.00
1x34	66.00	68.00
1x35	68.00	70.00
1x36	70.00	72.00
1x37	72.00	74.00
1x38	74.00	76.00
1x39	76.00	78.00
1x40	78.00	80.00

—		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	2005WV-XXP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X.	±0.25		
			MODEL NAME	2005WV-XXP		X.x	±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	±0.15		
							ANGULAR	±3'	
								FILE. NO.	