




**TMN3006MI**
**N-Channel Enhancement Mosfet**

<b>General Description</b> <ul style="list-style-type: none"> <li>• Low <math>R_{DS(ON)}</math></li> <li>• RoHS and Halogen-Free Compliant</li> </ul> <b>Applications</b> <ul style="list-style-type: none"> <li>• Load switch</li> <li>• PWM</li> </ul>	<b>General Features</b> <p><math>V_{DS} = 30V</math> <math>I_D = 6.0A</math>  <math>R_{DS(ON)} = 24m\Omega</math>(typ.)@ <math>V_{GS}=10V</math></p> <p>100% UIS Tested      100% <math>R_g</math> Tested</p> 
----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

 Marking: XO	<b>MI:SOT-23-3L</b> 	
---------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------	--------------------------------------------------------------------------------------

<b>Absolute Maximum Ratings (<math>T_c=25^\circ C</math>unless otherwise noted)</b>			
<b>Symbol</b>	<b>Parameter</b>	<b>Rating</b>	<b>Units</b>
$V_{DS}$	Drain-Source Voltage	30	V
$V_{GS}$	Gate-Source Voltage	$\pm 12$	V
$I_D @ T_A=25^\circ C$	Continuous Drain Current	6.0	A
$I_D @ T_A=70^\circ C$	Continuous Drain Current	4.9	A
$I_{DM}$	Pulsed Drain Current <sup>2</sup>	20	A
$P_D @ T_A=25^\circ C$	Total Power Dissipation <sup>3</sup>	1	W
$T_{STG}$	Storage Temperature Range	-55 to 150	$^\circ C$
$T_J$	Operating Junction Temperature Range	-55 to 150	$^\circ C$
$R_{\theta JA}$	Thermal Resistance Junction-ambient <sup>1</sup>	125	$^\circ C/W$
$R_{\theta JA}$	Thermal Resistance Junction-Ambient <sup>1</sup> ( $t \leq 10s$ )	85	$^\circ C/W$


**TMN3006MI**
**N-Channel Enhancement Mosfet**
**Electrical Characteristics ( $T_J=25^{\circ}\text{C}$ , unless otherwise noted)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$\text{BV}_{\text{DSS}}$	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}$ , $I_D=250\mu\text{A}$	30	---	---	V
$\Delta \text{BV}_{\text{DSS}}/\Delta T_J$	BVDSS Temperature Coefficient	Reference to $25^{\circ}\text{C}$ , $I_D=1\text{mA}$	---	0.029	---	$\text{V}/^{\circ}\text{C}$
$R_{\text{DS}(\text{ON})}$	Static Drain-Source On-Resistance <sup>2</sup>	$V_{\text{GS}}=10\text{V}$ , $I_D=5\text{A}$	---	24	26	$\text{m}\Omega$
		$V_{\text{GS}}=4.5\text{V}$ , $I_D=3\text{A}$	---	27	29	
		$V_{\text{GS}}=2.5\text{V}$ , $I_D=1\text{A}$	---	30	49	
$V_{\text{GS}(\text{th})}$	Gate Threshold Voltage	$V_{\text{GS}}=V_{\text{DS}}$ , $I_D=250\mu\text{A}$	0.5	0.9	1.2	V
$\Delta V_{\text{GS}(\text{th})}$	$V_{\text{GS}(\text{th})}$ Temperature Coefficient		---	-2.82	---	$\text{mV}/^{\circ}\text{C}$
$I_{\text{DS}}$	Drain-Source Leakage Current	$V_{\text{DS}}=24\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $T_J=25^{\circ}\text{C}$	---	---	1	$\text{uA}$
		$V_{\text{DS}}=24\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $T_J=55^{\circ}\text{C}$	---	---	5	
$I_{\text{GSS}}$	Gate-Source Leakage Current	$V_{\text{GS}}=\pm 12\text{V}$ , $V_{\text{DS}}=0\text{V}$	---	---	$\pm 100$	nA
$g_{\text{fs}}$	Forward Transconductance	$V_{\text{DS}}=5\text{V}$ , $I_D=5\text{A}$	---	25	---	S
$R_g$	Gate Resistance	$V_{\text{DS}}=0\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $f=1\text{MHz}$	---	1.5	---	$\Omega$
$Q_g$	Total Gate Charge (4.5V)	$V_{\text{DS}}=15\text{V}$ , $V_{\text{GS}}=4.5\text{V}$ , $I_D=5.8\text{A}$	---	11.5	---	$\text{nC}$
$Q_{\text{gs}}$	Gate-Source Charge		---	1.6	---	
$Q_{\text{gd}}$	Gate-Drain Charge		---	2.9	---	
$T_{\text{d}(\text{on})}$	Turn-On Delay Time	$V_{\text{DD}}=15\text{V}$ , $V_{\text{GS}}=10\text{V}$ , $R_g=3\Omega$ $I_D=5\text{A}$	---	5	---	$\text{ns}$
$T_r$	Rise Time		---	47	---	
$T_{\text{d}(\text{off})}$	Turn-Off Delay Time		---	26	---	
$T_f$	Fall Time		---	8	---	
$C_{\text{iss}}$	Input Capacitance	$V_{\text{DS}}=15\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $f=1\text{MHz}$	---	530	---	$\text{pF}$
$C_{\text{oss}}$	Output Capacitance		---	130	---	
$C_{\text{rss}}$	Reverse Transfer Capacitance		---	36	---	
$I_s$	Continuous Source Current <sup>1,4</sup>	$V_G=V_D=0\text{V}$ , Force Current	---	---	6.0	A
$V_{\text{SD}}$	Diode Forward Voltage <sup>2</sup>	$V_{\text{GS}}=0\text{V}$ , $I_s=1\text{A}$ , $T_J=25^{\circ}\text{C}$	---	---	1.2	V


**Note :**

- 1、The data tested by surface mounted on a 1 inch<sup>2</sup> FR-4 board with 2OZ copper.
- 2、The data tested by pulsed , pulse width  $\leq 300\mu\text{s}$  , duty cycle  $\leq 2\%$
- 3、The power dissipation is limited by  $150^{\circ}\text{C}$  junction temperature
- 4、The data is theoretically the same as  $I_D$  and  $I_{\text{DM}}$  , in real applications , should be limited by total power dissipation.


**Typical Characteristics**




**Fig.1 Typical Output Characteristics**




**Fig.2 On-Resistance vs. Gate-Source**




**Fig.3 Forward Characteristics Of Reverse**



**Fig.4 Gate-Charge Characteristics**



**Fig.5 Normalized  $V_{GS(th)}$  vs.  $T_J$**



**Fig.6 Normalized  $R_{DS(on)}$  vs.  $T_J$**

## TMN3006MI

## N-Channel Enhancement Mosfet




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Gate Charge Waveform

## Package Mechanical Data: SOT-23-3L



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°