


东莞市祥如电子有限公司

产品规格书


S P E C I F I C A T I O N

CUSTOMER		CUSTOMER'S P/S	
TSSUE DATE		OUR P/N	XRCD75-3R3M

1. 外观尺寸图 DIMENSIO S



2. 接线图 CONNECTION (BOTTOM VIEW)



A=7.8±0.3 B=7.0±0.3 C=5.0±0.3
D=2.5TYP. E=7.5±0.3 F=3.05 G=1.9

3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.4	8.5	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 100KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XRCD75-3R3M	3.3uH±20%	0.06 Ω	3.8A	3R3(黑色)	—

备注:

OPERATING TEMP. : -40℃~+85℃

INDUCTANCE DROP=10% TYP. AT IDC.

制作DRW	审核 CHK	确认 APPD	
-------	--------	---------	--

彭丽粉	梁何娟	黄振伟
2022.03.05	2022.03.05	2022.03.05

东莞市祥如电子有限公司

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:XRCD75-3R3M					EVALUATED Q' TY: 试样数:10PCS				
WATERIAL CODE: 磁材型号规格:DR7850					TESTED DATE: 试制日期:				
(DATA) 试样情况记录	SPC 规格 LOTS 序号	LOA (S-F) uH 3.3uH±20%	DCR Ω MAX 0.06	L3. 3A/LOA uH					
	1	3.15	0.029	3.11					
	2	3.22	0.030	3.15					
	3	3.18	0.028	3.09					
	4	3.35	0.029	3.20					
	5	3.42	0.030	3.28					
	6	3.36	0.029	3.21					
	7	3.27	0.028	3.16					
	8	3.45	0.029	3.30					
	9	3.32	0.030	3.19					
	10	3.14	0.029	3.07					
	REMARK: HK1062A, HK5028C. VR-114, VR-115 备注: 100KHZ 0.1V 外观: OK								
RESULTS: 判定: ☒ 合格 (PASSED) ☒ ROHS ☐ 非ROHS ☐ 不合格, 改良后 (FAILED) 参照 (REF)_____					制样员DRW 彭丽粉		东莞市祥如电子有限公司		