

### FEATURES

- USB Type-C 2.1 and USB PD 3.1 Compliant
  - USB-IF Certified. TID: 8655
  - Support SOP' Communication
  - Integrated Transceiver (BMC PHY)
  - Support Both Structured VDM Version 1.0 and 2.0
- High Integration
  - Embedded Both Side Ra Resistors
  - Embedded Both Side VCONN Diodes
- Package Options:
  - DFN2×2-6L
- Support 4 Times Programming
- Compatible with CC Wire Programming Tools
- Support 2.7 V ~ 5.75 V operation on VCONN1 and VCONN2 Pins
- 36 V High Voltage Tolerance on CC, VCONN1 and VCONN2 Pins
- Support USB 2.0 Data Communication
- Encryption Commands Supported for Vendor Identification
- Integrated Over-temperature Protection

- CC Over-voltage Protection at BMC transmission function
- 0.6 mA Ultra-Low Power Consumption
- ±8000 V HBM ESD Rating for all pins

### APPLICATIONS

- USB Type-C Cable ID
- USB 2.0 Passive Cable

### GENERAL DESCRIPTION

**HUSB332C** is a USB Type-C eMarker for Cable ID applications. It is compliant with USB Type-C Specification Revision 2.1. It is also compliant to USB Power Delivery 3.1 Specification.

Powered from VCONN1 or VCONN2, **HUSB332C** can determine to act as SOP'. The built-in OTP can be programmed through CC line or I<sup>2</sup>C bus so that it will be flexible for in-system programming.

The enhanced system ESD protection on the exposed pins can improve the system reliability significantly. The **HUSB332C** operates over a wide supply range of 2.7 V to 5.75 V. It is available in DFN2×2-6L package. It is rated over the -40°C to +85°C temperature range.

### TYPICAL APPLICATION CIRCUIT




Figure 1. HUSB332C\_B44DA Typical Application Circuit

**TABLE OF CONTENTS**

Features ..... 1

Applications ..... 1

General Description ..... 1

Typical Application Circuit ..... 1

Table of Contents ..... 2

Revision History ..... 2

Pin Configuration and Function Descriptions ..... 3

Recommended Operating Conditions ..... 4

Specifications ..... 5

Absolute Maximum Ratings ..... 6

    Thermal Resistance ..... 6

    ESD Caution ..... 6

Functional Block Diagram ..... 7

Theory of Operation ..... 8

    Power Cable Termination ..... 8

    High Voltage Tolerance ..... 8

    PD Message Information ..... 8

Typical Application Circuits ..... 10

Package Outline Dimensions ..... 11

Ordering Guide ..... 12

Tape and Reel Information ..... 13

Important Notice ..... 14

**REVISION HISTORY**

Version	Date	Descriptions
Rev. 1.0	12/2022	Initial version
Rev. 1.1	01/2023	Add the information about TID. Add Tape and Reel Information.
Rev. 1.2	03/2023	Modify the value of High Voltage Tolerance on CC, VCONN1 and VCONN2 Pins Modify the Functional Block Diagram
Rev. 1.3	07/2023	Delete one eMarker Solution Modify the ESD level

## PIN CONFIGURATION AND FUNCTION DESCRIPTIONS




Figure 2. HUSB332C\_B44DA Pin Assignment

**Table 1. HUSB332C\_XXXDA Pin Function Descriptions**

Pin No.	Pin Name	Type	Description
1	VCONN1	P	The input pin supplied from VCONN.
2	CC	D	USB Type-C CC line input and output.
3	VCONN2	P	The input pin supplied from the other side VCONN.
4	GND	A	Ground.
5	SDA	D	This pin is only used for debug. Please connect it to ground.
6	SCL	D	This pin is only used for debug. Please connect it to ground.

---

**RECOMMENDED OPERATING CONDITIONS**

Table 2.

<b>Parameter</b>	<b>Rating</b>
VCONN1 Input Voltage	2.7 V to 5.75 V
VCONN2 Input Voltage	2.7 V to 5.75 V
Operating Temperature Range (Junction)	-40°C to +125°C
Ambient Temperature Range	-40°C to 85°C

## SPECIFICATIONS

$V_{CONN1}$  or  $V_{CONN2} = 5\text{ V}$  and  $T_A = 25^\circ\text{C}$  for typical specifications, unless otherwise noted.

**Table 3. Electrical Specification**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
<b>GENERAL PARAMETERS</b>						
$V_{CONN1}/V_{CONN2}$ Voltage	$V_{CONN}$		2.7	5	5.75	V
Under-voltage Lockout	$V_{UVLO}$	Rising edge		2.6		V
		Falling edge		2.35		V
Standby Current	$I_{DD\_STANDBY}$	$V_{CONN1}$ or $V_{CONN2} > V_{CONN}$ , BMC is Idle		0.6		mA
CC Over-voltage Protection Threshold	VOV	Enabled to disable BMC transmission	6.3			V
Over-temperature Protection Threshold	$T_{OT\_DEF}$	Default trimmed	80	90	100	$^\circ\text{C}$
Operating Ambient Temperature	$T_A$		-40		85	$^\circ\text{C}$
<b>BMC COMMON PARAMETERS</b>						
Bit Rate	$f_{BitRate}$		270	300	330	kbps
<b>BMC TX PARAMETERS</b>						
Maximum Difference between the Bit-rate during the Part of the Packet Following the Preamble and the Reference Bit-rate.	$\rho_{BitRate}$				0.25	%
Time to Cease Driving the Line after the End of the Last bit of the Frame.	$t_{EndDriveBMC}$				23	$\mu\text{s}$
Fall Time	$t_{Fall}$	From 90% to 10% amplitude	300			ns
Time to Cease Driving the Line after the Final High-to-Low Transition.	$t_{HoldLowBMC}$		1			$\mu\text{s}$
Time from the End of Last Bit of a Frame until the Start of the First bit of the Next Preamble.	$t_{InterFrameGap}$		25			$\mu\text{s}$
Rise Time	$t_{Rise}$	From 10% to 90% amplitude	300			ns
Time Before the Start of the First Bit of the Preamble when the Transmitter shall Start Driving the Line.	$t_{StartDrive}$		-1		1	$\mu\text{s}$
Voltage Swing	$V_{Swing}$		1.05	1.125	1.2	V
Transmit Low Voltage			-75		75	mV
Transmitter Output Impedance	$Z_{Driver}$		33	54	75	$\Omega$
<b>BMC RX PARAMETERS</b>						
Power Cable Termination	$R_a$	$V_{CONN1}$ and $V_{CONN2} < V_{UVLO}$	800		1200	$\Omega$
Time Window for Detecting Bus Non-idle	$t_{TransitionWindow}$		12		20	$\mu\text{s}$
Number to Count to Detect Bus Non-idle	$n_{Count}$		3			
Time Constant of a Single Pole Filter to Limit Broad-band Noise Ingression	$t_{RxFilter}$		100			ns
Receiver Input Impedance	$Z_{BmcRx}$		1			$M\Omega$

## ABSOLUTE MAXIMUM RATINGS

Table 4. Absolute Maximum Ratings<sup>(a)</sup>

Parameter	Rating
VCONN1, VCONN2 and CC to GND	-0.5 V to +36 V
Storage Temperature Range	-65°C to +150°C
Operating Temperature Range (Junction)	-40°C to +125°C
Soldering Conditions	JEDEC J-STD-020 (T <sub>p</sub> : 260°C)
Electrostatic Discharge (ESD)	
Human Body Model (CC, VCONN1, VCONN2)	±8000 V
Human Body Model (SCL, SDA)	±8000 V
Charged Device Model	±2000 V

Note:

- a. Stresses at or above those listed under Absolute Maximum Ratings may cause permanent damage to the product. This is a stress rating only; functional operation of the product at these or any other conditions above those indicated in the operational section of this specification is not implied. Operation beyond the maximum operating conditions for extended periods may affect product reliability.

## THERMAL RESISTANCE

Thermal performance is directly linked to printed circuit board (PCB) design and operating environment. Close attention to PCB thermal design is required.

$\theta_{JA}$  is the natural convection junction to ambient thermal resistance measured in a one cubic foot sealed enclosure.

$\theta_{JC}$  is the junction to case thermal resistance.

Table 5. Thermal Resistance

Package Type	$\theta_{JA}$	$\theta_{JC}$	Unit
DFN2x2-6L	102.4	74.5	°C/W

## ESD CAUTION



### Electrostatic Discharge Sensitive Device.

Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

### FUNCTIONAL BLOCK DIAGRAM




Figure 3. HUSB332C Functional Block Diagram

## THEORY OF OPERATION

The HUSB332C is a USB eMarker Chip. It is usually applied in a USB Type-C cable plug. The HUSB332C employs two communication protocols, one is I<sup>2</sup>C communication protocol and the other is USB PD protocol. With both communication protocols, some customized information can be stored in the internal EPROM of the HUSB332C. And this information can be ready by the external devices via USB PD protocol.

### POWER CABLE TERMINATION

VCONN1 and VCONN2 pins are independent power input pin for the HUSB332C. When it is powered up ( $V_{CONN1}$  or  $V_{CONN2} > V_{UVLO}$ ), the HUSB332C starts up. If ( $V_{CONN1}$  or  $V_{CONN2} < V_{UVLO}$ ), the pins ( $V_{CONN1}$  and  $V_{CONN2}$ ) perform as a resistance characteristic. The equivalent resistance is Ra.

### HIGH VOLTAGE TOLERANCE

The VCONN1, VCONN2 and CC pins are all high voltage tolerance. They can be survived from a high voltage of up to 36 V to withstand in some accidental faults, such as a short fault between CC pin and VBUS pin whose voltage could be up to 36 V.

### PD MESSAGE INFORMATION

The HUSB332C supports several extended messages for some customization information. It is able to respond the correct message once there is an inquiry message received.

#### DISCOVER IDENTITY

The Discover Identity Command is provided to enable an Initiator (DFP) to identify its Port Partner and for an Initiator (VCONN Source) to identify the Responder (Cable Plug). The Discovery Identity Command is also used to determine whether a Cable Plug is PD-Capable by looking for a GoodCRC Message Response.

The Discover Identity Command shall be used to determine whether a given Cable Plug is PD Capable. In this case a Discover Identity Command request sent to SOP' shall not cause a Soft Reset if a GoodCRC Message response is not returned since this can indicate a non-PD Capable cable. Note that a Cable Plug will not be ready for PD Communication until 50 ms after VCONN has been applied. During Cable Plug discovery, when there is an Explicit Contract, Discover Identity Commands are sent at a rate defined by the DiscoverIdentityTimer up to a maximum of nDiscoverIdentityCount times. See USB Power Delivery Specification Revision 3.1, Version 1.0 for details.

A PD-Capable Cable Plug shall return a Discover Identity Command ACK in response to a Discover Identity Command request sent to SOP'.

The Number of Data Objects field in the Message Header in the Discover Identity Command request shall be set to 1 since the Discover Identity Command request shall not contain any VDOs.

The Discover Identity Command ACK sent back by the HUSB332C shall contain an ID Header VDO, a Cert Stat VDO, a Product VDO and the Product Type VDOs defined by the Product Type as shown in Figure 4.



Figure 4. Discover Identity Command Response

### MANUFACTURER INFORMATION

The Manufacturer Information Message Shall be sent in response to a Get\_Manufacturer\_Info Message. The Manufacturer\_Info Message contains the USB VID and the Vendor's PID to identify the device and the device's manufacturer byte array in a variable length Data Block of up to 26 bytes.

The Manufacturer\_Info Message format is shown in Figure 5.



Figure 5. Manufacturer Information Message

For the MIDB, it consists of VID, PID and Manufacture String. They can be sent with a pre-determined offset.

Offset	Field	Description
0	VID	Vendor ID (assigned by the USB-IF)
2	PID	Product ID (assigned by the manufacturer)
4	Manufacturer String	Vendor defined null terminated string of 0...21 characters. If the Manufacturer Info Target field or Manufacturer Info Ref field in the <i>Get_Manufacturer_Info</i> Message is unrecognized the field Shall return a null terminated ascii text string "Not Supported".

Figure 6. Manufacturer Information MIDB

The VID, PID information can be programmed. Please be noted that, if the received Get\_Manufacturer\_Info Message contains the information which the HUSB332C does not support, such as the Manufacturer Information Target field in the Get\_Manufacturer\_Info Message equals Battery (01b) and the Manufacturer Information Ref field is Invalid, the HUSB332C responds Manufacturer Information with VID=0xFFFF, PID=0x0000.

Offset	Field	Description
0	<i>Manufacturer Info Target</i>	0: Port/Cable Plug 1: Battery 255...2: <b>Reserved, Shall Not</b> be used.
1	<i>Manufacturer Info Ref</i>	If <i>Manufacturer Info Target</i> subfield is Battery (01b) the <i>Manufacturer Info Ref</i> field Shall contain the Battery number reference which is the number of the Battery indexed from zero: <ul style="list-style-type: none"> <li>Values 0...3 represent the Fixed Batteries.</li> <li>Values 4...7 represent the Hot Swappable Batteries.</li> </ul> Otherwise, this field is <b>Reserved</b> and <b>Shall</b> be set to zero.

Figure 7. Get\_Manufacturer\_Info MIDB

The HUSB332C does not support any Manufacturer String. A "Not Supported" string is filled in this field.

### DISCOVER RESPONSE

The HUSB332C supports Structured VDMs. Therefore, the Discover Identity, Discover SVIDs, the Discover Modes, the Enter Mode and Exit Mode Commands are all supported by the HUSB332C. The HUSB332C does not initial any Structure VDMs. It can only respond a received Structure VDM REQ. Discover Identity is a MUST supported command for the HUSB332C. For the other Structured VDMs, it is impacted by the modal operation field in the Discover Identity.

TYPICAL APPLICATION CIRCUITS




Figure 8. Two eMarkers Solution without VCONN Connected Through the Cable

**PACKAGE OUTLINE DIMENSIONS**






Figure 9. DFN2x2-6L Package, 2 mm x 2 mm Body

## ORDERING GUIDE

Order Model	Description	Application	Package	Ta Range	Package Option
HUSB332C_B44DA	Default USB2.0, ERP Mode Capable, 1m cable	Two eMarkers Solution without VCONN Connected Through the Cable	DFN2×2-6L	-40°C to +85°C	Tape & Reel, 4000

# TAPE AND REEL INFORMATION



**DIMENSIONS AND PIN1 ORIENTATION**

D0 (mm)	W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	P2 (mm)	W (mm)	Pin1 Quadrant
178.00	9.50	2.30	2.30	1.10	4.00	4.00	8.00	Q2

All dimensions are nominal

Figure 10. Tape and Reel Information

## IMPORTANT NOTICE

Hynetek Semiconductor Co., Ltd. and its subsidiaries (Hynetek) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as “components”) are sold subject to Hynetek’s terms and conditions of sale supplied at the time of order acknowledgment.

Hynetek warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in Hynetek’s terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent Hynetek deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

Hynetek assumes no liability for applications assistance or the design of Buyers’ products. Buyers are responsible for their products and applications using Hynetek components. To minimize the risks associated with Buyers’ products and applications, Buyers should provide adequate design and operating safeguards.

Hynetek does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which Hynetek components or services are used. Information published by Hynetek regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from Hynetek under the patents or other intellectual property of Hynetek.

Reproduction of significant portions of Hynetek information in Hynetek data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Hynetek is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of Hynetek components or services with statements different from or beyond the parameters stated by Hynetek for that component or service voids all express and any implied warranties for the associated Hynetek component or service and is an unfair and deceptive business practice.

Hynetek is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of Hynetek components in its applications, notwithstanding any applications-related information or support that may be provided by Hynetek. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify Hynetek and its representatives against any damages arising out of the use of any Hynetek components in safety-critical applications.

In some cases, Hynetek components may be promoted specifically to facilitate safety-related applications. With such components, Hynetek’s goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No Hynetek components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those Hynetek components which Hynetek has specifically designated as military grade or “enhanced plastic” are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of Hynetek components which have not been so designated is solely at the Buyer’s risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

Hynetek has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, Hynetek will not be responsible for any failure to meet ISO/TS16949.

Please refer to below URL for other products and solutions of Hynetek Semiconductor Co., Ltd.