

# USB Type-C™ Compatible DX07 SMT Contact Receptacle

CONNECTOR  
MB-0297-6  
October 2018

**RoHS Compliant**



On-board Type



Mid-mount Type

The DX07 Series are connectors compatible with the next-generation USB specification “USB Type-C™” and they are expected to become popular as a standard interface for various devices, such as PCs, smartphones, hand-held devices, audio-visual equipment, and gaming devices.

Note) USB Type-C™ is a trademark of USB Implementers Forum, Inc.

## Applicable Markets

Smartphones, tablets, PCs, digital still cameras, headphones, and others

## Features

- Compliant with Universal Serial Bus Type-C™ Specification Release 1.3.
- Compatible with 10Gbps x2 (20Gbps) Super Speed communication.
- Supports 5A max. power supply. (Compatible with USB Power Delivery)
- Reversible plug orientation makes possible to insert both ways up.
- Lock structure with superior durability.
- Large selection of connector variations  
(Please refer to the below chart below for Brochures)

Brochure Number	Brochure Name
MB-0335-2	DX07 Hybrid Contact Receptacle
MB-0336-2	DX07 Vertical Receptacle
MB-0333-1	DX07 Waterproof Receptacle
MB-0301-3	DX07 Plug Series
MB-0322-1	DX07 Vertical Plug
MB-0324-4	DX07 Harness

**General Specifications**

Number of Contacts	24 Position	Rated Current	V <sub>BUS</sub> (Terminal No. A4, A9, B4, B9) DC 5A (Total)
Contact Resistance	40mΩ max. (initial)		GND (Terminal No. A1, A12, B1, B12) DC 6.25A (Total)
Withstanding Dielectric Withstanding Voltage	100Vrms / 1minute		V <sub>CONN</sub> (Terminal No. B5) DC 1.25A
Insulation Resistance	100MΩ (initial)		Others DC 0.25A / pin
Durability	10,000 times	Rated Voltage	20Vrms
Operating Temperature Range	-30°C ~ +80°C		

**Ordering Information**

[Receptacle Side]

**DX07 \* 0 24 J \* \* R\*\*\*\***

Series  
DX07: USB Type C

Reeled pcs. / reel

S: On-board, B: Mid-mount

Modification Code #2

Modification Code #1

Plating Specification

J: Contact area:

Au flash over Palladium Ni over Ni plating

A: Contact area: Au plating over Ni


No. of Contacts: 24 pos.

Board Connection Type

J: 2 row SMT horizontal

Outer Dimensions

On-board




Unit: mm

Part Number	C/H	Dimension A	Dimension B	Dimension C	Dimension D	Mating Length	Rear Shield	Note
DX07S024JJ1	1.57	8.94	8.17	3.14	0.6	4.7	Yes	Shell 2-point contact DIP
DX07S024JJ2								---
DX07S024JA1								Insert mold
DX07S024JJ3								No
DX07S024JJ7								---
DX07S024JJ4								Yes
DX07SD24JJ3								---
DX07SD24JJ3	2.0				0.6	5.1		---

Outer Dimensions

Mid-mount



Unit: mm

Part Number	C/H	Dimension A	Dimension B	Dimension C	Dimension D	Rear Shield	Note
DX07B024JJ1	4.7	8.94	8.17	3.14	0.8	Yes	---
DX07B024JJ2						No	---
DX07B024JJ4						Yes	Insulator White
DX07BG24JJ1							Shell cut
DX07B024JJ3L	-0.07		8.9		0.7	No	---
DX07BN24JA2	-0.64	9.13	11.1	3.45	0.8		---

Technical Documents
---------------------

Part Number	Drawing Number	Specifications	Handling Instructions	Package Quantity
DX07S024JJ1 DX07S024JJ1R1300	SJ115848 SJ115849	JACS-30353	JAHL-30353-1	1,300 pieces/reel
DX07S024JJ2 DX07S024JJ2R1300	SJ115946 SJ115947			
DX07S024JA1 DX07S024JA1R1300	SJ119361 SJ119362	JACS-30353-19	JAHL-30353-5	
DX07S024JJ3 DX07S024JJ3R1300	SJ115994 SJ115995	JACS-30353	JAHL-30353-1	
DX07S024JJ4 DX07S024JJ4R1300	SJ117264 SJ117265			
DX07S024JJ7 DX07S024JJ7R1200	SJ119223 SJ119224	JACS-30353-6	JAHL-30353-5	1,200 pieces/reel
DX07SD24JJ3 DX07SD24JJ3R1200	SJ117525 SJ117526	JACS-30353	JAHL-30353-1	
DX07B024JJ1 DX07B024JJ1R1500	SJ115850 SJ115851			
DX07B024JJ2 DX07B024JJ2R1500	SJ115996 SJ115997			
DX07B024JJ4 DX07B024JJ4R1500	SJ117724 SJ117725			
DX07BG24JJ1 DX07BG24JJ1R1500	SJ117126 SJ117127			
DX07B024JJ3L DX07B024JJ3LR1600	SJ117601 SJ117602			
DX07BN24JA2 DX07BN24JA2R1300	SJ119577 SJ119578			
				1,600 pieces/reel
				1,300 pieces/reel

Note) Please order in reel units.

**Notice:**

1. The values specified in this brochure are only for reference. The products and their specifications are subject to change without notice. Contact our sales staff for further information before considering or ordering any of our products. For purchase, a product specification must be agreed upon.

2. Users are requested to provide protection circuits and redundancy circuits to ensure safety of the equipment, and sufficiently review the suitability of JAE's products to the equipment.

3. The products presented in this brochure are designed for the uses recommended below. We strongly suggest you contact our sales staff when considering use of any of the products in any other way than the recommended applications or for a specific use that requires an extremely high reliability.

(1) Applications that require consultation:

(i) Please contact us if you are considering use involving a quality assurance program that you specify or that is peculiar to the industry, such as:

Automotive electrical components, train control, telecommunications devices (mainline), traffic light control, electric power, combustion control, fire prevention or security systems, disaster prevention equipment, etc.

(ii) We may separately give you our support with a quality assurance program that you specify, when you think of a use such as :

Aviation or space equipment, submarine repeaters, nuclear power control systems, medical equipment for life support, etc.

(2) Recommended applications include:

Computers, office appliances, telecommunications devices (terminals, mobile units), measuring equipment, audiovisual equipment, home electric appliances, factory automation equipment, etc.

**Japan Aviation Electronics Industry, Limited**

Product Marketing Division

Aobadai Building, 3-1-19, Aobadai, Meguro-ku, Tokyo 153-8539

Phone: +81-3-3780-2882 FAX: +81-3-3780-2946

\* The specifications in this brochure are subject to change without notice. Please contact JAE for information.