



德力西电气有限公司

**Product Specification**  
产品规格书  
**Model: DHAFG11025HA2BL**

Factory Address: Delixi High Tech Park, LiuShi Town, Yueqing City,  
Zhejiang Province

工厂地址：浙江省乐清市柳市镇德力西高科技工业园

Tel: +086-400-826-8008

电话: +086-400-826-8008

Website: [www.delixi-electric.com](http://www.delixi-electric.com)

网址: [www.delixi-electric.com](http://www.delixi-electric.com)



|                                |                                   |
|--------------------------------|-----------------------------------|
| 1. 外观尺寸 EXTERNAL DIMENSION     | 110*110*25                        |
| 2. 订货编码                        | DHAFG11025HA2BL                   |
| 3. 产品型号                        | G11025HA2BL                       |
| 4. 重量 WEIGHT                   | 310g                              |
| 5. 轴承 BEARING                  | BALL BEARING                      |
| 6. 额定电压 RATED VOLTAGE          | AC 220V                           |
| 7. 额定电流 RATED CURRENT          | 0.08/0.07A±0.01MAXIMUM            |
| 8. 额定功率 RATED INPUT POWER      | 14/15W±2MAXIMUM                   |
| 9. 转数 RATED SPEED              | 2000/2300 RPM±10%                 |
| 10. 最大风量 MAXIMUM AIR FLOW      | 60/70CFM                          |
| 11. 最大风压 MAXIMUM AIR PRESSURE  | 4.42/4.82mmH2O (AT ZERO AIR FLOW) |
| 12. 启动电压 STARTING VOLTAGE      | AC 110V MINIMUM                   |
| 13. 存储温度 STORAGE HUMIDITY      | -20℃~+80℃                         |
| 14. 运转温度 OPERATING TEMPERATURE | -25℃~+65℃                         |
| 15. 寿命 LIFE EXPECTANCE         | 30000HRS                          |
| 16. 噪音分贝 SOUND LEVEL           | 36dBA/38dBA                       |

## SPECIFICATION 规格参数

