

General Description

The CMN3401ZM uses advanced trench technology to provide excellent RDS(ON), low gate charge and operation with gate voltages as low as 2.5V. This device is suitable for use as a Battery protection or in other Switching application.

Features

- RDS(ON)<50mΩ @ VGS=-10V
- RDS(ON)<60mΩ @ VGS=-4.5V
- Simple drive requirement
- Surface mount package


Product Summary

BVDSS	RDSON	ID
-30V	50mΩ	-4A


Applications

- PWM applications
- Load switch
- Power management
- PA Switch


SOT-23 Pin Configuration



SOT-23-3L



Type	Package	Marking
CMN3401ZM	SOT-23-3L	X1



P-Channel Enhancement Mode Field Effect Transistor

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	-30	V
V_{GS}	Gate-Source Voltage	± 12	V
$I_D@T_C=25^\circ C$	Continuous Drain Current	-4	A
I_{DM}	Pulsed Drain Current	-12	A
$P_D@T_C=25^\circ C$	Total Power Dissipation	1.4	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ C$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ C$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient (Steady State)	---	125	$^\circ C/W$

Electrical Characteristics ($T_J=25^\circ C$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=-250\mu A$	-30	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=-10V, I_D=-4A$	---	---	50	m Ω
		$V_{GS}=-4.5V, I_D=-3.5A$	---	---	60	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=-250\mu A$	-0.5	---	-1.5	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=-24V, V_{GS}=0V$	---	---	-1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 12V, V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=-5V, I_D=-1A$	---	6	---	S
Q_g	Total Gate Charge	$I_D=-4A$ $V_{DS}=-15V$ $V_{GS}=-10V$	---	11	---	nC
Q_{gs}	Gate-Source Charge		---	2	---	
Q_{gd}	Gate-Drain Charge		---	4	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DS}=-15V, R_G=3\Omega$ $R_L=3.75\Omega, V_{GS}=-10V$	---	8	---	ns
T_r	Rise Time		---	6	---	
$T_{d(off)}$	Turn-Off Delay Time		---	45	---	
T_f	Fall Time		---	12	---	
C_{iss}	Input Capacitance	$V_{DS}=-15V, V_{GS}=0V, f=1MHz$	---	800	---	pF
C_{oss}	Output Capacitance		---	50	---	
C_{rss}	Reverse Transfer Capacitance		---	40	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
V_{SD}	Diode Forward Voltage	$V_{GS}=0V, I_S=-1A$	---	---	-1	V

This product has been designed and qualified for the consumer market.
 Cmos assumes no liability for customers' product design or applications.
 Cmos reserves the right to improve product design, functions and reliability without notice.