



**»Features** $V_{DS} = -12V$  $I_D = -5.1A$  $R_{DS(ON)} @ V_{GS} = -4.5V, TYP = 28m\Omega$  $R_{DS(ON)} @ V_{GS} = -2.5V, TYP = 38m\Omega$ **»Pin Configurations****»General Description**

- Advanced trench process technology
- High Density Cell Design For Ultra Low On-Resistance
- SOT-23 for Surface Mount Package.

**»Absolute Maximum Ratings @ $T_A=25^\circ C$  unless otherwise noted**

Characteristic	Symbol	Max	Unit
Drain-Source Voltage	$BV_{DSS}$	-12	V
Gate- Source Voltage	$V_{GS}$	$\pm 8$	V
Drain Current (continuous)	$I_D$	-5.1	A
Drain Current (pulsed)	$I_{DM}$	-20	A
Total Device Dissipation $T_A=25^\circ C$	$P_D$	1250	mW
Junction	$T_J$	150	$^\circ C$
Storage Temperature	$T_{stg}$	-55 to +150	$^\circ C$







**»Electrical Characteristics @ $T_A=25^\circ\text{C}$  unless otherwise noted**


Characteristic	Symbol	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage ( $I_D = -250\mu\text{A}, V_{GS}=0\text{V}$ )	$\text{BV}_{DSS}$	-12	—	—	V
Gate Threshold Voltage ( $I_D = -250\mu\text{A}, V_{GS}= V_{DS}$ )	$V_{GS(\text{th})}$	-0.4	—	-1	V
Diode Forward Voltage Drop ( $I_S= -1 \text{ A}, V_{GS}=0\text{V}$ )	$V_{SD}$	—	—	-1.2	V
Zero Gate Voltage Drain Current ( $V_{GS}=0\text{V}, V_{DS}= -12\text{V}$ )	$I_{DSS}$	—	—	-1	$\mu\text{A}$
Gate Body Leakage ( $V_{GS}=\pm 8\text{V}, V_{DS}=0\text{V}$ )	$I_{GSS}$	—	—	$\pm 100$	nA
Static Drain-Source On-State Resistance ( $I_D= -5.1\text{A}, V_{GS}= -4.5\text{V}$ )	$R_{DS(\text{ON})}$	—	28	35	$\text{m}\Omega$
Static Drain-Source On-State Resistance ( $I_D= -4.5\text{A}, V_{GS}= -2.5\text{V}$ )	$R_{DS(\text{ON})}$	—	38	45	$\text{m}\Omega$
Static Drain-Source On-State Resistance ( $I_D= -2 \text{ A}, V_{GS}= -1.8\text{V}$ )	$R_{DS(\text{ON})}$	—	50	59	$\text{m}\Omega$
Input Capacitance ( $V_{GS}=0\text{V}, V_{DS}= -10\text{V}, f=1\text{MHz}$ )	$C_{ISS}$	—	920	—	pF
Output Capacitance ( $V_{GS}=0\text{V}, V_{DS}= -10\text{V}, f=1\text{MHz}$ )	$C_{OSS}$	—	220	—	pF
Turn-ON Time ( $V_{DS}= -10\text{V}, I_D= -2 \text{ A}, R_{\text{GEN}}=6\Omega$ )	$t_{(\text{on})}$	—	8	—	ns
Turn-OFF Time ( $V_{DS}= -10\text{V}, I_D= -2 \text{ A}, R_{\text{GEN}}=6\Omega$ )	$t_{(\text{off})}$	—	60	—	ns

**Notes :**


 \*Pulse Test : Pulse Width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .

»Typical Performance Characteristics (( $T_J = 25^\circ\text{C}$ , unless otherwise noted))







Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage




Single Pulse Power



Safe Operating Area

## »Package Information

SOT-23



## »Ordering information

Order code	Package	Marking	Base qty	Delivery mode
SI2333	SOT-23	2333	3K	Tape and reel