

Features


- Trench Power LV MOSFET technology
- High Power and current handing capability

Product Summary


V_{DS}	$R_{DS(ON)} \text{ MAX}$	$I_D \text{ MAX}$
20V	65m Ω @4.5V	2.5A
	85m Ω @2.5V	

Application

- PWM application
- Load switch



SOT-23 top view



Schematic diagram

Absolute Maximum Ratings (TA=25°C unless otherwise noted)


Symbol	Parameter	Rating	Unit	
Common Ratings (TC=25°C Unless Otherwise Noted)				
V_{DS}	Drain-Source Breakdown Voltage	20	V	
V_{GS}	Gate-Source Voltage	± 10	V	
T_J	Maximum Junction Temperature	150	°C	
T_{STG}	Storage Temperature Range	-50 to 155	°C	
I_S	Diode Continuous Forward Current	Tc=25°C	2.5	A

Mounted on Large Heat Sink


I_{DM}	Pulse Drain Current Tested	Tc=25°C	14	A
I_D	Continuous Drain Current@GS=10V	Tc=25°C	2.5	A
P_D	Maximum Power Dissipation	Tc=25°C	0.7	W
$R_{θJA}$	Thermal Resistance Junction-to-Ambient @ Steady State		178	°C/W

Electrical Characteristics (TJ=25°C unless otherwise noted)						
Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
$BV_{(BR)DSS}$	Drain-Source Breakdown Voltage	$VGS=0V$, $ID=250\mu A$	20	--	--	V
I_{DSS}	Zero Gate Voltage Drain Current	$VDS=20V$, $VGS=0V$	--	--	1	uA
I_{GSS}	Gate-Body Leakage Current	$VGS=\pm 10V$, $VDS=0V$	--	--	± 100	nA
$V_{GS(th)}$	Gate Threshold Voltage	$VDS=VGS$, $ID=250\mu A$	0.45	0.7	0.9	V
$R_{DS(on)}$	Drain-Source On-State Resistance	$VGS=4.5V$, $ID=2.5A$	--	45	65	$m\Omega$
		$VGS=2.5V$, $ID=2.0A$	--	69	85	$m\Omega$
Dynamic Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
C_{iss}	Input Capacitance	$VDS=10V$, $VGS=0V$, $f=1MHz$	--	120	--	pF
C_{oss}	Output Capacitance		--	30	--	pF
C_{rss}	Reverse Transfer Capacitance		--	25	--	pF
Switching Characteristics						
Q_g	Total Gate Charge	$VDS=10V$, $ID=2.5A$, $VGS=10V$	--	4.5	--	nC
Q_{gs}	Gate Source Charge		--	0.8	--	nC
Q_{gd}	Gate Drain Charge		--	0.5	--	nC
$t_{d(on)}$	Turn-on Delay Time	$VDD=10V$, $ID=2.5A$, $VGS=10V$, $RG=3\Omega$	--	3	--	nS
t_r	Turn-on Rise Time		--	29	--	nS
$t_{d(off)}$	Turn-Off Delay Time		--	6	--	nS
t_f	Turn-Off Fall Time		--	22	--	nS
Source- Drain Diode Characteristics						
V_{SD}	Forward on voltage	$Tj=25^\circ C$, $Is=2.5A$,	--	--	1.2	V


Typical Operating Characteristics




V_{DS}, Drain -Source Voltage (V)
 Fig1. Typical Output Characteristics




Q_g -Total Gate Charge (nC)
 Fig2. Typical Gate Charge Vs.Gate-Source Voltage




T_j - Junction Temperature (°C)
 Fig3. Normalized On-Resistance Vs. Temperature




I_D, Drain-Source Current (A)
 Fig4. On-Resistance Vs. Drain-Source Current



V_{DS}, Drain -Source Voltage (V)
 Fig5. Maximum Safe Operating Area



V_{DS} , Drain-Source Voltage (V)
 Fig6 Typical Capacitance Vs.Drain-Source Voltage

SOT-23 Package information


Symbol	Dimensions in Millimeters(mm)		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950TYP		0.037TYP	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°