




Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40°C-+125°C

温度范围: -40°C ~ $+125^{\circ}\text{C}$

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X1005 W R S - XX A - 6T SW
 (1) (2) (3) (4) (5) (6) (7) (8)

1.Series No

2.Category:W-Wafer

3. Welding Board Angle: R-Straight 90°



4. Welding Way: S-SMT

5.Row No.Pin No:XX-02~30 Pin

6.Special No:A-Short fixed label

7. Material: 6T-PA6T UL94V-0

8.Plating:SW-Matte Tin Plated



Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
02	1.00	5.80	3.10	2.50	17	16.00	20.80	18.10	17.50
03	2.00	6.80	4.10	3.50	18	17.00	21.80	19.10	18.50
04	3.00	7.80	5.10	4.50	19	18.00	22.80	20.10	19.50
05	4.00	8.80	6.10	5.50	20	19.00	23.80	21.10	20.50
06	5.00	9.80	7.10	6.50	21	20.00	24.80	22.10	21.50
07	6.00	10.80	8.10	7.50	22	21.00	25.80	23.10	22.50
08	7.00	11.80	9.10	8.50	23	22.00	26.80	24.10	23.50
09	8.00	12.80	10.10	9.50	24	23.00	27.80	25.10	24.50
10	9.00	13.80	11.10	10.50	25	24.00	28.80	26.10	25.50
11	10.00	14.80	12.10	11.50	26	25.00	29.80	27.10	26.50
12	11.00	15.80	13.10	12.50	27	26.00	30.80	28.10	27.50
13	12.00	16.80	14.10	13.50	28	27.00	31.80	29.10	28.50
14	13.00	17.80	15.10	14.50	29	28.00	32.80	30.10	29.50
15	14.00	18.80	16.10	15.50	30	29.00	32.80	31.10	30.50
16	15.00	19.80	17.10	16.50	/				

X1005WRS-XXA-6TSW	PA6T	Phosphor Bronze	X1005H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X1005WRS-XXA-6TSW
CHKD		UNIT: mm/in	DWG NO.: X-X1005WRS-XXA-6TSW
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						