





**Specifications:**






规格:

- Voltage rating: 50V AC/DC
- 额定电压: 50V AC/DC
- Current rating: 1A AC/DC
- 额定电流: 1A AC/DC
- Withstanding voltage: 500V AC/minute
- 耐受电压: 500V AC/分钟
- Temperature range: -25°C~+85°C
- 温度范围: -25°C~+85°C
- Insulation resistance: 100MΩ min
- 绝缘电阻: 100MΩ Min
- Contact resistance: 30mΩ Max
- 接触电阻: 30mΩ Max



X1010 W R S -XX -LP SN  
 ① ② ③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: R-Stright 90°
4. Welding Way: S-SMT
5. Row No. Pin No: XX-02~15P
6. Material: LP-LCP UL94V-0
7. Plating: SN-Tin Plated  
V01-Gold Flash



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	5.00	09	8.00	11.00
03	2.00	5.00	10	9.00	12.00
04	3.00	6.00	11	10.00	13.00
05	4.00	7.00	12	11.00	14.00
06	5.00	8.00	13	12.00	15.00
07	6.00	9.00	14	13.00	16.00
08	7.00	10.00	15	14.00	17.00

**Recommended P.C.B Layout**

X1010WRS-XX-LPSN	LCP	Brass	X1010H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN		VIEW:	PART NO.: X1010WRS-XX-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X1010WRS-XX-LPSN
APPD		SIZE: A4	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS