




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.31 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Piggyback
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.36 mm[.014 in]
Product Length	15.62 mm[.615 in]
Compatible Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]
Wire Size	.51 – 1.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Agency/Standard	CSA, UL
-----------------	---------

Packaging Features

Packaging Quantity	3500
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 2-2266297-1 OCEAN-2.0-APPLICATOR-S-090F1400	 TE Part # 2-2266297-2 OCEAN-2.0-APPLICATOR-S-090F1400	 TE Part # 2266297-1 OCEAN-2.0-APPLICATOR-S-090F1400
 TE Part # 2266297-2 OCEAN-2.0-APPLICATOR-S-090F1400	 TE Part # 7-2266297-1 OCEAN-2.0-APPLICATOR-S-090F1400	 TE Part # 7-2266297-2 OCEAN-2.0-APPLICATOR-S-090F1400	 TE Part # 7-2266297-7 OCEAN_2.0_SPARE_PART_KIT-090F1400

Also in the Series | FASTON 187

 Crimp Terminal Housings(42)	 Insertion & Extraction Tools(1)	 Joints & Splices(1)	 PCB Terminals(42)
--	--	--	--



Quick Disconnects(209)




Splices(1)

Customers Also Bought




TE Part #2-36151-2
PIDG R 22-16 COMM 22-18MIL 6



TE Part #480054-3
FF 250 REC HSG 1P NYLON NAT



TE Part #61556-1
RING 22-16 AWG .0245 X .435 TPST




TE Part #2-520193-2
ULTRA-FAST 187 ASY REC 22-18 TPBR



TE Part #42743-2
250 FASTON REC 22-18 AWG TPBR




TE Part #40725
RING 190(4.82MM)TERMINAL 18-14 AWG TPBR




TE Part #346027-1
FASTIN FASTON HOUSING RECEPTACLE



TE Part #60196-2
187 FASTON REC 20-16 AWG TPBR



TE Part #1-174355-1
E-J MK-2 CAP HSG 2P NATURAL



TE Part #3-520106-2
ULTRA-FAST 250 ASY TAB 16-14 AWG TPBR

Documents

Product Drawings

187 FASTON REC 20-16 AWG TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_63646-2_G.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_63646-2_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63646-2_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[82004 FASTON Terminals \(Insulated and Uninsulated\) Catalog - FASTON Receptacles Section](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English