


FEATURES

- Low forward voltage drop
- Guard ring construction for transient protection
- Negligible reverse recovery time
- Low reverse capacitance

SOD-123


MARKING: NRVB130T1G S3*

Maximum Ratings and Electrical Characteristics, Single Diode @ $T_A=25^\circ C$

Parameter	Symbol	MBR130T			Unit
Peak Repetitive Peak reverse voltage	V_{RRM}				V
Working Peak Voltage	V_{RWM}	30			
DC Blocking Voltage	V_R				
RMS Reverse Voltage	$V_{R(RMS)}$	28			V
Forward Continuous Current	I_{FM}	1			A
Repetitive Peak Forward Current @$t \leq 1.0s$	I_{FRM}	1.5			A
Power Dissipation	P_d	500			mW
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	250			°C/W
Storage temperature	T_{STG}	-65~+150			°C

Electrical Ratings @ $T_A=25^\circ C$

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Reverse Breakdown Voltage	$V_{(BR)R}$	30			V	$I_R=100\mu A$
Forward voltage	V_F			0.37 0.60	V	$I_F=20mA$ $I_F=200mA$
Reverse current	I_{RM}			5.0	μA	$V_R=30V$
Capacitance between terminals	C_T		50		pF	$V_R=0V, f=1.0MHz$
Reverse Recovery Time	t_{rr}		10		ns	$I_F=I_R=200mA$ $I_{rr}=0.1X I_R, R_L=100\Omega$

Typical Characteristics




Fig. 1 Typical Forward Characteristics




Fig. 2 Typ. Junction Capacitance vs Reverse Voltage