




SOT-23



Features

- For AM/FM Amplifier and Local Oscillator of FM/VHF Tuner Applications

Marking: J8



1. BASE

2. EMITTER

3. COLLECTOR

Absolute Maximum Ratings

Ratings at 25°C ambient temperature unless otherwise specified.

Dimensions in inches and (millimeters)

Parameter	Symbol	Value	Unit
Collector Base Voltage	V_{CBO}	30	V
Collector Emitter Voltage	V_{CEO}	15	V
Emitter Base Voltage	V_{EBO}	5	V
Collector Current	I_C	50	mA
Power Dissipation	P_D	200	mW
Junction Temperature	T_J	150	°C
Storage Temperature Range	T_{STG}	-55 to 150	°C

Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	Min.	Typ.	Max.	Unit
DC Current Gain at $V_{CE} = 5\text{ V}$, $I_C = 1\text{ mA}$ Current Gain Group	H_{FE}	72 97	- -	108 190	
Collector Base Cutoff Current at $V_{CB} = 12\text{ V}$	I_{CBO}	-	-	50	nA
Collector Base Breakdown Voltage at $I_C = 100\text{ }\mu\text{A}$	$V_{(BR)CBO}$	30	-	-	V
Collector Emitter Breakdown Voltage at $I_C = 1\text{ mA}$	$V_{(BR)CEO}$	15	-	-	V
Emitter Base Breakdown Voltage at $I_E = 100\text{ }\mu\text{A}$	$V_{(BR)EBO}$	5	-	-	V
Collector Emitter Saturation Voltage at $I_C = 10\text{ mA}$, $I_B = 1\text{ mA}$	$V_{CE(sat)}$	-	-	0.5	V
Transition Frequency at $V_{CE} = 5\text{ V}$, $I_C = 5\text{ mA}$	f_T	700	1100	-	MHz
Collector Base Capacitance at $V_{CB} = 10\text{ V}$, $f = 1\text{ MHz}$	C_{ob}	-	1.3	1.7	pF

Electrical Characteristics Curves

