



SOT-23
RoHS
COMPLIANT

Pb
Pb-Free

These miniature surface mount MOSFETs reduce power loss conserve energy, making this device ideal for use in small power management circuitry. Typical applications are dc–dc converters, load switching, power management in portable and battery–powered products such as computers, printers, cellular and cordless telephones.

MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Rating	Symbol	Value	Unit
Drain–to–Source Voltage	V_{DS}	50	V _{dc}
Gate–to–Source Voltage – Continuous	V_{GS}	± 20	V _{dc}
Drain Current			mA
– Continuous @ $T_A = 25^\circ\text{C}$	I_D	130	
– Pulsed Drain Current ($t_p \leq 10 \mu\text{s}$)	I_{DM}	520	
Total Power Dissipation @ $T_A = 25^\circ\text{C}$	P_D	225	mW
Operating and Storage Temperature Range	T_J, T_{stg}	– 55 to 150	$^\circ\text{C}$
Thermal Resistance – Junction–to–Ambient	$R_{\theta JA}$	556	$^\circ\text{C/W}$
Maximum Lead Temperature for Soldering Purposes, for 10 seconds	T_L	260	$^\circ\text{C}$

Marking PD


Dimensions in inches and (millimeters)

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
----------------	--------	-----	-----	-----	------

OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage ($V_{GS} = 0\text{ Vdc}$, $I_D = 250\text{ }\mu\text{Adc}$)	$V_{(BR)DSS}$	50	—	—	Vdc
Zero Gate Voltage Drain Current ($V_{DS} = 25\text{ Vdc}$, $V_{GS} = 0\text{ Vdc}$) ($V_{DS} = 50\text{ Vdc}$, $V_{GS} = 0\text{ Vdc}$) ($V_{DS} = 50\text{ Vdc}$, $V_{GS} = 0\text{ Vdc}$, $T_J = 125^\circ\text{C}$)	I_{DSS}	— — —	— — —	0.1 15 60	μAdc
Gate-Body Leakage Current ($V_{GS} = \pm 20\text{ Vdc}$, $V_{DS} = 0\text{ Vdc}$)	I_{GSS}	—	—	± 60	μAdc

ON CHARACTERISTICS (Note 1.)

Gate-Source Threshold Voltage ($V_{DS} = V_{GS}$, $I_D = 1.0\text{ mAdc}$)	$V_{GS(th)}$	0.8	—	2.0	Vdc
Static Drain-to-Source On-Resistance ($V_{GS} = 5.0\text{ Vdc}$, $I_D = 100\text{ mAdc}$)	$r_{DS(on)}$	—	5.0	10	Ohms
Transfer Admittance ($V_{DS} = 25\text{ Vdc}$, $I_D = 100\text{ mAdc}$, $f = 1.0\text{ kHz}$)	$ y_{fs} $	50	—	—	mS

DYNAMIC CHARACTERISTICS

Input Capacitance	($V_{DS} = 5.0\text{ Vdc}$)	C_{iss}	—	30	—	pF
Output Capacitance	($V_{DS} = 5.0\text{ Vdc}$)	C_{oss}	—	10	—	
Transfer Capacitance	($V_{DG} = 5.0\text{ Vdc}$)	C_{rss}	—	5.0	—	



SWITCHING CHARACTERISTICS (Note 2.)






Turn-On Delay Time	$(V_{DD} = -15\text{ Vdc}$, $I_D = -2.5\text{ Adc}$, $R_L = 50\text{ }\Omega$)	$t_{d(on)}$	—	2.5	—	ns
Rise Time		t_r	—	1.0	—	
Turn-Off Delay Time		$t_{d(off)}$	—	16	—	
Fall Time		t_f	—	8.0	—	
Gate Charge		Q_T	—	6000	—	pC

SOURCE-DRAIN DIODE CHARACTERISTICS

Continuous Current	I_S	—	—	0.130	A
Pulsed Current	I_{SM}	—	—	0.520	
Forward Voltage (Note 2.)	V_{SD}	—	2.5	—	V

1. Pulse Test: Pulse Width $\leq 300\text{ }\mu\text{s}$, Duty Cycle $\leq 2\%$.
2. Switching characteristics are independent of operating junction temperature.

TYPICAL ELECTRICAL CHARACTERISTICS

Figure 1. Transfer Characteristics

Figure 2. On-Region Characteristics

TYPICAL ELECTRICAL CHARACTERISTICS

Figure 3. On-Resistance versus Drain Current

Figure 4. On-Resistance versus Drain Current

Figure 5. On-Resistance Variation with Temperature

Figure 6. Gate Charge

Figure 7. Body Diode Forward Voltage