


GENERAL FEATURES

- $R_{DS(ON)} \leq 16 \text{ m}\Omega @ V_{GS}=10\text{V}$
- $R_{DS(ON)} \leq 20 \text{ m}\Omega @ V_{GS}=4.5\text{V}$
- Super high density cell design for extremely low $R_{DS(ON)}$
- Exceptional on-resistance and maximum DC current capability


Application

- Power Management in Note book
- Portable Equipment
- Battery Powered System
- DC/DC Converter
- Load Switch
- DSC
- LCD Display inverter


Package and Pin Configuration



Marking:



Circuit diagram



Schematic diagram

Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter		Symbol	Maximum Ratings	Unit
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	V
Continuous Drain Current	$T_A=25^\circ\text{C}$	I_D	10	A
	$T_A=70^\circ\text{C}$		8.3	
Pulsed Drain Current		I_{DM}	38	A
Maximum Power Dissipation	$T_A=25^\circ\text{C}$	P_D	2	W
	$T_A=70^\circ\text{C}$		1.2	
Operating Junction Temperature		T_J	-55 to 150	$^\circ\text{C}$
Thermal Resistance-Junction to Ambient*		$R_{\theta JA}$	52.0	$^\circ\text{C/W}$


Electrical Characteristics (T_A=25°C Unless Otherwise Specified)

Symbol	Parameter	Limit	Min	Typ	Max	Unit
STATIC						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250 μA	30			V
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250 μA	1		3	V
I _{GSS}	Gate Leakage Current	V _{DS} =0V, V _{GS} =±20V			±100	nA
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =24V, V _{GS} =0V			1	μA
R _{DS(ON)}	Drain-Source On-Resistance ^a	V _{GS} =10V, I _D =10A		11.2	16	mΩ
		V _{GS} =4.5V, I _D =8A		15.6	20	
V _{SD}	Diode Forward Voltage	I _S =8.2A, V _{GS} =0V		0.8	1.2	V
DYNAMIC						
R _g	Gate Resistance	f=1MHz		1		Ω
Q _g	Total Gate Charge	V _{DS} =10V, V _{GS} =4.5V, I _D =8.2A		9.5		nC
Q _{gs}	Post-V _{th} Gate-Source Charge			3.6		
Q _{gd}	Gate-Drain Charge			3.4		
C _{iss}	Input Capacitance	V _{DS} =25V, V _{GS} =0V, f=1MHz		841		pF
C _{oss}	Output Capacitance			250		
C _{rss}	Reverse Transfer Capacitance			71		
t _{d(on)}	Turn-On Delay Time	V _{DD} =15V, R _L =15Ω I _D =1A, V _{GEN} =10V, R _G =6Ω		14		ns
t _r	Turn-On Rise Time			12		
t _{d(off)}	Turn-Off Delay Time			43		
t _f	Turn-Off Fall Time			4		


Notes: a. pulse test: pulse width ≤ 300us, duty cycle ≤ 2%, Guaranteed by design, not subject to production testing.

b. Matsuki Electric/ Force mos reserves the right to improve product design, functions and reliability without notice


On Resistance vs. Junction Temperature




On-Resistance vs. Drain Current




Capacitance




On-Resistance vs. Gate-to-Source Voltage








Threshold Voltage




On-Region Characteristics





SOP-8 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.270(BSC)		0.050(BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°