


SEC: A-A





SEC: B-B

Ordering Information & Specifications

Part No	Wire Range	Insulation O.D.	Material	Finish	Qty/reel
C4255M-TBE	AWG#18-#24	3.10mm(max)	Brass	Tin-plated	5,000pcs
C4255M-GBE	AWG#18-#24	3.10mm(max)	Brass	Gold-flash 1u"	5,000pcs
C4255M-HBE	AWG#18-#24	3.10mm(max)	Brass	Gold-flash 1u"	5,000pcs
C4255M-HBE-G1	AWG#18-#24	3.10mm(max)	Brass	Gold-plated 15u"	5,000pcs

Note: E-Stamping before Tin-plated or Gold-plated

			 燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.		
			UNIT	SCALE	SHEET
			mm	1 : 1	1 of 1
B4	ECN1808230001	2018.09.13	焦秋蘭	DRAWN BY 董正一	APPROVED BY 董正一
B3	REVISE	2009.05.26		2001.02.01	2001.02.01
B2	REVISE	2007.10.18		GENERAL TOLERANCE	
B1	REVISE	2006.11.04		X. X±0.25	ANGLE±
B0	NEW RELEASE	2006.06.07		X. XX±0.15	
REV.	DESCRIPTION	DATE	NAME	X. XXX±0.05	
					TITLE:
					4.20mm PITCH CRIMP TERMINAL-MALE, MINI-FIT
					DRAW NO. :
					C4255M-XX
					REV. B4