



SS32B THRU SS320B

VOLTAGE RANGE 20 to 200 Volts
CURRENT 3.0 Ampere

Features

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- For surface mounted applications
- Metal silicon junction,majority carrier conduction
- Low power loss,high efficiency
- Built-in strain relief,ideal for automated placement
- High forward surge current capability
- High temperature soldering guaranteed: 260 C/10 seconds at terminals



Mechanical Data

- Case: Transfer molded plastic
- Epoxy: UL 94V-0 rate flame retardant
- Lead :Solder plated, solderable per MIL-STD-750 method 2026
- Polarity: Color band denotes cathode end
- Weight: 0.003ounce, 0.093 gram

DO-214AA (SMB J-Bend)

Maximum Ratings and Electrical Characteristics

- Ratings at 25°C ambient temperature unless otherwise specified
- Single phase, half wave, 60Hz, resistive or inductive load
- For capacitive load derate current by 20%

TYPE NUMBER	SYMBOL S	SS 32B	SS 34B	SS 35B	SS 36B	SS 38B	SS 310B	SS 315B	SS 320B	UNIT			
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	20	40	50	60	80	100	150	200	Volts			
Maximum RMS Voltage	V_{RMS}	14	28	35	42	56	70	105	140	Volts			
Maximum DC Blocking Voltage	V_{DC}	20	40	50	60	80	100	150	200	Volts			
Maximum Average Forward Rectified Current at T_L see figure 1 $T_L = 100^\circ\text{C}$	$I_{(AV)}$	3.0								Amps			
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC method)	I_{FSM}	80								Amps			
Maximum Instantaneous Forward Voltage @ 3.0A(Note1)	V_F	0.55		0.70		0.85		0.90		Volts			
Maximum DC Reverse Current at $T_A = 25^\circ\text{C}$ rated DC Blocking Voltage per element	I_R	0.1					0.01		mA				
		20.0			10.0		2.0						
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	50							°C/W				
	$R_{\theta JL}$	12											
Diode junction capacitance (Note 3)	C_J	300		200					pF				
Operating Junction Temperature	T_J	(-55 to +150)					(-65 to +175)		°C				
Storage Temperature Range	T_{STG}	(-55 to +150)							°C				

Notes:

- Pulse test:300μs pulse width,1% duty cycle.
- Thermal resistance from Junction to ambient and from junction to lead mounted on PCB. with $0.3 \times 0.3'' (8.0 \times 8.0\text{mm})$ copper pad areas.
- f=1MHz and applied 4V DC reverse voltage.








SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

SS32B THRU SS320B

VOLTAGE RANGE	20 to 200 Volts
CURRENT	3.0 Ampere

Ratings and Characteristic Curves (TA=25°C unless otherwise noted)





SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

SS32B THRU SS320B

VOLTAGE RANGE


20 to 200 Volts

CURRENT


3.0 Ampere

Package Outline Dimensions in inches (millimeters)

DO-214AA (SMB-J-Bend)



Mounting Pad Layout



Marking

Type number	Marking code
SS32B	SS32
SS34B	SS34
SS35B	SS35
SS36B	SS36
SS38B	SS38
SS310B	SS310
SS315B	SS315
SS320B	SS320



SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

SS32B THRU SS320B


VOLTAGE RANGE

20 to 200 Volts


CURRENT

3.0 Ampere

Package Reel Information




Specifications	Ao	Bo	Ko	Po	W	t1
SMB	3.77±0.10	5.70±0.10	2.67±0.10	4.00±0.1	12.0±0.05	0.23±0.02



DEVICE TYPE	Tape Width	13"Reel			07"Reel			
		Q'TY/REEL(pcs)	BOX/CARTOON	Q'TY/CARTON(pcs)	Q'TY/REEL(pcs)	REEL/BOX	BOX/CARTOON	Q'TY/CARTON(pcs)
SMB	12mm	3000	8	48000	NA	NA	NA	NA



Reflow Profile



Reflow Condition		Pb-Free Assembly
Pre Heat	Temperature Min.	+150°C
	Temperature Max.	+200°C
	Time(Min to Max)	60-180 secs.
Average ramp up rate(Liquidus Temp(T_L) to peak)		3°C/sec. Max.
$T_S(\max)$ to T_L - Ramp-up Rate		3°C/sec. Max.
Reflow	Temperature (T_L)(Liquidus)	+217°C
	Temperature (T_L)	60-150 secs.
Peak Temp (T_P)		+(260+0/-5)°C
Time within 5°C of actual Peak Temp (T_P)		25 secs.
Ramp-down Rate		6°C/sec. Max.
Time 25°C to peak Temp (T_P)		8 min. Max.
Do not exceed		+260°C