

DIMENSION FOR LEFT SIDE HOUSING
COLOR BLACK-POS. 27-52 - ITEM 3

P/N 2209477-1 AS SHOWN

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A3		SHEET2 ADDED	15OCT2020	T.D	I.Y
B		ECR-20-015711	05NOV2020	J.L	J.Z
B1		ECR-20-016644	18NOV2020	S.C	J.Z
B2		ECR-21-003344	16MAR2021	Z.W	J.Z

DIMENSION FOR RIGHT SIDE HOUSING
COLOR GREY-POS. 1-26 - ITEM 4

FOR MISSING DIMENSIONS SEE LEFT SIDE HOUSING DRAWING

NOTES

1) THE PRODUCT IS SUPPLIED WITH LEVER IN CLOSED POSITION

2) INTERFACE DRAWING SEE THE CUSTOMER DRAWONG OF 284972

3) NUMBER 26+26 CAVITIES SUITABLE FOR MICRO QUADLOCK SYSTEM FEMALE CONTACTS
P.N. 928999-1 WIRE RANGE 0.25-0.35 mm²,INSULATOR RANGE Ø1.15-1.6
P.N. 963715-1 WIRE RANGE 0.50-0.75 mm²,INSULATOR RANGE Ø1.7-1.9,FOR SELECTION
MAXIMUM 25% OF ALL CONTACTS

4) SUITABLE MQS SOCKET HOUSING P.N. 1-968326-1 26POS. AND 2-968326-1 26POS.

5) ITEM 1 AND 2 ASSEMBLY TOGETHER, ASSEMBLY PART AND ITEM 3,4 ARE SUPPLIED
IN KIT WITH EQUIVALENT QUANTITY IN A BOX

MECHANICAL CODING DIMENSIONS
P.N. 2209477-1, COLOR - BLACK

MECHANICAL CODING DIMENSIONS
P.N. 2209477-2, COLOR - BLUE

BI

MECHANICAL CODING DIMENSIONS
P.N. 2209477-3, COLOR - GREY

BI

PART LIST

1	1	1	GERY	SOCKET HSG	1	4
1	1	1	BLACK	SOCKET HSG	1	3
1	1	1	RED	LEVER	1	2
1			GREY	COVER		1
	1		BLUE		1	
		1	BLACK		1	
2209477-3	2209477-2	2209477-1	COLOR	DESCRIPTION	QTY.	ITEM NO.
TE ASS'Y NO.						

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
T.DONG
07MAR2013

CHK
A.DANG
07MAR2013

APVD
I.YIN
11MAR2013

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

KIT ASS'Y FOR
52POS. MQS FEMALE CONNECTOR

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2209477

RESTRICTED TO

SCALE
1:1

SHEET
1

OF
2

REV
B2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2020

© COPYRIGHT 2020

TE Connectivity. All Rights Reserved.

ALL RIGHTS RESERVED.

P/N	CODING INFORMATION
6-2209477-1	
6-2209477-2	
6-2209477-3	
6-2209477-4	

1 LEVER IN CLOSED POSITION

LEVER IN OPENED POSITION

NOTES

1 THE PRODUCT IS SUPPLIED WITH LEVER IN CLOSED POSITION

2) THE PRODUCT IS SUITABLE FOR MATING WITH INTERFACE 114-160058:

3 NUMBER 26+26 CAVITIES SUITABLE FOR MICRO QUADLOCK SYSTEM FEMALE CONTACTS
P.N. 928999 WIRE RANGE 0.25-0.35 mm²,INSULATOR RANGE Ø1.15-1.6
P.N. 963715 WIRE RANGE 0.50-0.75 mm²,INSULATOR RANGE Ø1.7-1.9,FOR SELECTION
MAXIMUM 25% OF ALL CONTACTS, REFER TO SHEET 1

4) SUITABLE MQS SOCKET HOUSING P.N. 1-968326-1 26POS. AND 2-968326-1 26POS.
REFER TO SHEET 1

5) ITEM 5 AND 6 ASSEMBLY TOGETHER, ASSEMBLY PART AND ITEM 3,4 ARE SUPPLIED
IN KIT WITH EQUIVALENT QUANTITY IN A BOX

1	1	1	1	GERY	SOCKET HSG	1	4
1	1	1	1	BLACK	SOCKET HSG	1	3
1	1	1	1	RED	LEVER	1	6
1				GREEN	COVER	1	5
	1			GREY		1	
		1		BLUE		1	
			1	BLACK		1	
6-2209477-4	6-2209477-3	6-2209477-2	6-2209477-1	COLOR	DESCRIPTION	QTY.	ITEM NO.

TE ASS'Y NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN T.DONG 15OCT2020

CHK J.ZONG 15OCT2020

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

KIT ASS'Y FOR 52POS. MQS FEMALE CONNECTOR

SIZE A2 CAGE CODE 00779 DRAWING NO C=2209477 RESTRICTED TO -

SCALE 1:1 SHEET 2 OF 2 REV B2

1471-9 (3/13)