



# MUR1010CT THRU MUR1060CT

Reverse Voltage - 100 to 600 Volts Forward Current - 10.0 Ampere

## ULTRAFAST RECOVERY RECTIFIER

### Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Construction utilizes void-free molded plastic technique
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed: 250°C, 0.25"(6.35mm) from case for 10 seconds

### Mechanical Data


**Case :** JEDEC TO-220AB Molded plastic body

**Terminals :** Solder plated, solderable per MIL-STD-750, Method

**2026 Polarity :** As marked

**Mounting Position :** Any

**Weight :** 0.080 ounce, 2.24 grams



Dimensions in inches and (millimeters)

### Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD MUR1010CT	MDD MUR1020CT	MDD MUR1030CT	MDD MUR1040CT	MDD MBUR1050CT	MDD MUR1060CT	UNITS
Marking Code								
Maximum repetitive peak reverse voltage	V <sub>RRM</sub>	100	200	300	400	500	600	V
Maximum RMS voltage	V <sub>RMS</sub>	70	140	210	280	350	420	V
Maximum DC blocking voltage	V <sub>DC</sub>	100	200	300	400	500	600	V
Maximum average forward rectified current (see fig.1)	I <sub>(AV)</sub>				10.0			A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I <sub>FSM</sub>				90			A
Maximum instantaneous forward voltage at 5.0A	V <sub>F</sub>	1.0		1.3		1.7		V
Maximum DC reverse current TA=25°C at rated DC blocking voltage TA=100°C	I <sub>R</sub>				10			uA
					500			
Typical junction capacitance (NOTE 1)	C <sub>J</sub>		170			130		pF
Typical thermal resistance (NOTE 2)	R <sub>θJC</sub>			3.5				°C/W
Maximum Reverse Recovery time (NOTE 3)	T <sub>rr</sub>			35				nS
storage temperature range	T <sub>jT<sub>STG</sub></sub>			-55 to +150				°C

Note:1.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2.Thermal resistance from junction to case.

3..Reverse Recovery Test Conditions: I<sub>F</sub>=0.5A, I<sub>R</sub>=1A, I<sub>rr</sub>=0.25A.



# MUR1010CT THRU MUR1060CT

Reverse Voltage - 100 to 600 Volts   Forward Current - 10.0 Ampere

## Ratings And Characteristic Curves

Fig.1 FORWARD CURRENT DERATING CURVE




Fig.2 TYPICAL JUNCTION CAPACITANCES




Fig.3 FORWARD CHARACTERISTICS




Fig.4 TYPICAL REVERSE CHARACTERISTICS





Fig.5 PEAK FORWARD SURGE CURRENT



The curve above is for reference only.