



SS52 THRU SS520

VOLTAGE RANGE 20 to 200 Volts
CURRENT 5.0 Ampere

Features

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- For surface mounted applications
- Metal silicon junction, majority carrier conduction
- Low power loss, high efficiency
- Built-in strain relief, ideal for automated placement
- High forward surge current capability
- High temperature soldering guaranteed: 260 C/10 seconds at terminals



DO-214AA (SMB J-Bend)

Mechanical Data

- Case: Transfer molded plastic
- Epoxy: UL 94V-0 rate flame retardant
- Lead :Solder plated, solderable per MIL-STD-750 method 2026
- Polarity: Color band denotes cathode end
- Weight: 0.003ounce, 0.093 gram

Maximum Ratings and Electrical Characteristics

- Ratings at 25°C ambient temperature unless otherwise specified
- Single phase, half wave, 60Hz, resistive or inductive load
- For capacitive load derate current by 20%

TYPE NUMBER		SYMBOL S	SS 52	SS 54	SS 55	SS 56	SS 58	SS 510	SS 515	SS 520	UNIT
Maximum Repetitive Peak Reverse Voltage		V _{RRM}	20	40	50	60	80	100	150	200	Volts
Maximum RMS Voltage		V _{RMS}	14	28	35	42	56	70	105	140	Volts
Maximum DC Blocking Voltage		V _{DC}	20	40	50	60	80	100	150	200	Volts
Maximum Average Forward Rectified Current at T _L see figure 1 T _L =100°C		I _(AV)	5.0								Amps
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC method)		I _{FSM}	125								Amps
Maximum Instantaneous Forward Voltage @ 5.0A(Note1)		V _F	0.55		0.70		0.85		0.90		Volts
Maximum DC Reverse Current at rated DC Blocking Voltage per element	T _A = 25°C	I _R	0.1						0.01		mA
	T _A = 100°C		20.0				10.0		2.0		
Typical Thermal Resistance (Note 2)		R _{θJA}	50								°C/W
		R _{θJL}	12								
Diode junction capacitance (Note 3)		C _J	300		200						pF
Operating Junction Temperature		T _J	(-55 to +150)						(-65 to +175)		°C
Storage Temperature Range		T _{STG}	(-55 to +150)								°C

Notes:

1. Pulse test: 300 μs pulse width, 1% duty cycle.
2. Thermal resistance from Junction to ambient and from junction to lead mounted on PCB. with 0.3 $\times$ 0.3"(8.0 $\times$ 8.0mm) copper pad areas.
3. f=1MHz and applied 4V DC reverse voltage.



SS52 THRU SS520

VOLTAGE RANGE 20 to 200 Volts
CURRENT 5.0 Ampere

Ratings and Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

FIG.1-FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.4-TYPICAL REVERSE CHARACTERISTICS





FIG.5-TYPICAL JUNCTION CAPACITANCE






SS52 THRU SS520

VOLTAGE RANGE 20 to 200 Volts
CURRENT 5.0 Ampere

Package Outline Dimensions in inches (millimeters)






SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER


SS52 THRU SS520

VOLTAGE RANGE 20 to 200 Volts
CURRENT 5.0 Ampere

Package Reel Information



Specifications	Ao	Bo	Ko	Po	W	t1
SMB	3.77±0.10	5.70±0.10	2.67±0.10	4.00±0.1	12.0±0.05	0.23±0.02




DEVICE TYPE	Tape Width	13"Reel			07"Reel			
		Q'TY/REEL(pcs)	BOX/CARTON	Q'TY/CARTON(pcs)	Q'TY/REEL(pcs)	REEL/BOX	BOX/CARTON	Q'TY/CARTON(pcs)
SMB	12mm	3000	8	48000	NA	NA	NA	NA



SS52 THRU SS520

VOLTAGE RANGE	20 to 200 Volts
CURRENT	5.0 Ampere

Marking Code




Part Number Code





Reflow Profile



Reflow Condition		Pb-Free Assembly
Pre Heat	Temperature Min.	+150°C
	Temperature Max.	+200°C
	Time(Min to Max)	60-180 secs.
Average ramp up rate(Liquidus Temp(T_L) to peak)		3°C/sec. Max.
$T_{S(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max.
Reflow	Temperature (T_L)(Liquidus)	+217°C
	Temperature (T_L)	60-150 secs.
Peak Temp (T_P)		+(260+0/-5)°C
Time within 5°C of actual Peak Temp (T_P)		25 secs.
Ramp-down Rate		6°C/sec. Max.
Time 25°C to peak Temp (T_P)		8 min. Max.
Do not exceed		+260°C