

PRODUCT-DETAILS

SH201-D10

SH201-D10 Miniature Circuit Breaker - 1P - D - 10 A



General Information

Extended Product Type	SH201-D10
Product ID	2CDS211001R0101
EAN	4016779699099
Catalog Description	SH201-D10 Miniature Circuit Breaker - 1P - D - 10 A
Long Description	SH201-D10 Miniature Circuit Breaker - 1P - D - 10 A

Technical

Standards	IEC/EN 60898-1
Tripping Characteristic	D
Rated Operational Voltage	acc. to IEC 60898-1 230 / 400 V AC
Operational Voltage	Maximum (Incl. Tolerance) 253 V AC Minimum 12 V AC
Rated Insulation Voltage (U _i)	acc. to IEC/EN 60664-1 440 V
Rated Impulse Withstand Voltage (U _{imp})	4 kV at 2000 m 5 kV at Sea Level 6.2 kV
Dielectric Test Voltage	50/60 Hz, 1 min: 2 kV
Input Voltage Type	AC
Rated Current (I _n)	10 A
Rated Short-Circuit Capacity	(AC) 6 kA (230 / 400 V AC) 6 kA

Rated Conditional Short-Circuit Current (I_{nc})	(230 V) 6 kA (400 V) 6 kA
Rated Frequency (f)	50 / 60 Hz
Power Loss	1.6 W at Rated Operating Conditions per Pole 1.6 W
Power Supply Connection	Arbitrary
Contact Position Indication	ON / OFF
Energy Limiting Class	3
Electrical Endurance	20000 AC cycle
Mechanical Endurance	20000 cycle
Number of Poles	1
Number of Protected Poles	1
Overvoltage Category	III
Tightening Torque	2 N·m
Actuator Type	Toggle
Screw Terminal Type	Cage Terminal
Actuator Marking	I / O
Actuator Material	Insulation Group II, Black, Sealable
Housing Material	Insulation Group II, RAL 7035
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Mounting Position	any
Recommended Screw Driver	Pozidriv 2
Accessories Available	No
Connecting Capacity	Conductor 25 / 25 mm ² Flexible with Ferrule 0.75 ... 16 mm ² Flexible 0.75 ... 16 mm ² Rigid 0.75 ... 25 mm ² Stranded 0.75 ... 25 mm ²
Installation Size	acc. to DIN 43880 1
Terminal Type	Screw Terminals

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
Reference Ambient Air Temperature	30 °C
Degree of Protection	IP20 Enclosure with Cover IP40
Pollution Degree	2
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
Resistance to Vibrations acc. to IEC 60068-2-6	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
Resistance to Shock acc. to IEC 60068-2-27	25g 2 shocks 13 ms
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Information	2CDK400030D0201
REACH Declaration	9AKK107492A1906
Environmental Information	2CDK400030D0201

Dimensions

Width in Number of Modular Spacings	1
Product Net Width	17.5 mm
Product Net Height	85 mm
Product Net Depth / Length	69 mm
Product Net Weight	0.125 kg
Pole Net Weight	0.125 kg
Built-In Depth (t ₂)	69 mm

Ordering

Minimum Order Quantity	1 piece
Package Level 1 Units	carton 10 piece
Package Level 1 Gross Weight	1.29 kg

Certificates and Declarations

Certification Agency	EN IEC
Declaration of Conformity - CE	2CDK400607D2703

Installation

Instructions and Manuals	2CDS207105P0001
--------------------------	-----------------

Popular Downloads

Data Sheet, Technical Information	2CSC400030D0202
-----------------------------------	-----------------

Classifications

ETIM 8	EC000042 - Miniature circuit breaker (MCB)
ETIM 9	EC000042 - Miniature circuit breaker (MCB)
EPLAN Catalog Tree	Electrical engineering / Protection devices / General
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	8536 20 10
UNSPSC	39121603
eClass	V11.0 : 27141901
IDEA Granular Category Code (IGCC)	4897 >> Miniature circuit breakers

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs → Miniature Circuit Breakers MCBs

