







RECOMMENDED CABLE SUBASSEMBLY



A-A (FREE)



CABLE TERMINATION FIGURE(FREE)



- NOTES 1. APPLICABLE CABLE: THIN COAXIAL CABLE (AWG#42-AWG#46)
2. THIS CONNECTOR IS NOT HOT PLUGGABLE. MATE AND UNMATE WHILE THE POWER IS OFF.
3. THE ASSEMBLY IS COMPLETED BY COMBINING TWO PARTS "CONNECTOR UNIT AND METAL SHIELDING".
REFER TO THE TABLE FOR EACH ITEM No., PART NAME, PART No. AND CODE No.

ITEM No.	PART NAME	PART No.	CODE No.
1, 2	CONNECTOR UNIT	DF36-30P-0.4SD(51)	CL662-4018-3-51
-	METAL SHIELDING	DF36A-30P-SHL	CL662-4019-6-00

1	PHOSPHOR BRONZE	CONTACT AREA : Au PLATING 0.1μm min TERMINATION AREA : Au PLATING 0.1μm min UNDER PLATING : Ni PLATING 1μm min	5	PS	BLACK
NO.	MATERIAL	FINISH, REMARKS	4	POLYESTER	CLEAR
UNITS	mm	SCALE 5 : 1	3	PS	CLEAR
		COUNT	2	LCP	UL94V-0, BLACK
		DESCRIPTION OF REVISIONS	NO.	MATERIAL	FINISH, REMARKS
		APPROVED : TS. SAKATA 11.10.18			
		CHECKED : IO. DENPOUYA 11.10.18			
		DESIGNED : TP. MATSUMOTO 11.10.17			
		DRAWN : TP. MATSUMOTO 11.10.17			
		DRAWING NO. EDC3-315347-01			
		PART NO. DF36-30P-0.4SD(51)			
		CODE NO. CL662-4018-3-51			

