

General Description

The 25N06 combines advanced trench MOSFET technology with a low resistance package to provide extremely low $R_{DS(ON)}$.

This device is ideal for boost converters and synchronous rectifiers for consumer, telecom, industrial power supplies and LED backlighting.

Features

- N-channel-Enhancement mode
- Lower On-resistance
- 100% Avalanche Tested
- RoHS Compliant

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current	25	A
$I_D@T_C=100^\circ\text{C}$	Continuous Drain Current	16	A
I_{DM}	Pulsed Drain Current	100	A
EAS	Single Pulse Avalanche Energy ¹	30	mJ
$P_D@T_C=25^\circ\text{C}$	Total Power Dissipation	50	W
T_{STG}	Storage Temperature Range	-55 to 175	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 175	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient ²	---	60	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction -Case	---	3	$^\circ\text{C/W}$


Product Summary

BVDSS	$R_{DS(ON)}$	ID
60V	33m Ω	25A

Applications

- DC-DC & DC-AC Converters
- Motor Control, Audio Amplifiers
- High Current, High Speed Switching
- Solenoid And Relay Drivers

TO-252 / 251 Pin Configuration



Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	60	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=10V$, $I_D=20A$	---	29	33	m Ω
		$V_{GS}=4.5V$, $I_D=10A$	---	34	40	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1	---	3	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=60V$, $V_{GS}=0V$, $T_J=25^{\circ}\text{C}$	---	---	1	uA
		$V_{DS}=60V$, $V_{GS}=0V$, $T_J=55^{\circ}\text{C}$	---	---	10	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=20A$	---	7	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	1.2	---	Ω
Q_g	Total Gate Charge	$V_{DS}=30V$, $V_{GS}=10V$, $I_D=25A$	---	26	---	nC
Q_{gs}	Gate-Source Charge		---	8	---	
Q_{gd}	Gate-Drain Charge		---	5	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=30V$, $V_{GEN}=10V$, $R_L=1.2\Omega$ $I_D=25A$, $R_G=7.5\Omega$	---	10	---	ns
T_r	Rise Time		---	10	---	
$T_{d(off)}$	Turn-Off Delay Time		---	30	---	
T_f	Fall Time		---	10	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	1000	---	pF
C_{oss}	Output Capacitance		---	50	---	
C_{rss}	Reverse Transfer Capacitance		---	40	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	25	A
I_{SM}	Pulsed Source Current		---	---	100	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=30A$, $T_J=25^{\circ}\text{C}$	---	0.92	1.3	V

Note :

1. The EAS data shows Max. rating . The test condition is $V_{DS}=30V$, $V_{GS}=10V$, $L=0.5\text{mH}$, $I_{AS}=11A$.
2. Surface mounted on 1" x 1" FR4 Board.

This product has been designed and qualified for the consumer market.
Cmos assumes no liability for customers' product design or applications.
Cmos reserves the right to improve product design ,functions and reliability without notice.

Typical Characteristics

