

规格书
Specification

品名
Model name

HY12-2P 5V

PROPRIETARY
Huayu Electronic co.,Ltd.

CONFIDENTIAL
Huayu Electronic co.,Ltd.

Version #	Spec V1.0
制作日期 Date	2019/12/11
准备 Prepared	yisheng Acoustic specialist,R&D Dept.
承认 Approved	Qianwanjin Executive Manager,R&D Dept.



兴化市华宇电子有限公司

地址：江苏省兴化市陈堡工业区人民路 1 号
电话：13625199874 传真：0523-83723118
邮箱：391245375@qq.com 网址：www.js-huayu.com

*Components Operating Div.
Huayu Electronic co.,Ltd.*

1.基本规格/General specification

项目/Item		规格/Spec	条件/Condition
1	额定电压 Rated voltage	5Vo-p	
2	工作电压 Operation voltage	4-8Vo-p	
3	声压 Sound Pressure Level=SPL	Min 85dB	测试环境：标准状态，标准驱动电路， 额定电压 测试距离：0.1m Standard State,Standard Drive Circuit. Rated voltage,Distance at 0.1m
4	电流 current	Max50mA	
5	振荡频率 Oscillation frequency	2048±300HZ	
6	电阻 Coil Resistance	42±6Ω	
7	工作温度范围 Operating Temperature	-20~+70℃	
8	保存温度范围 Storage temperature	-30~+80℃	
9	外部尺寸 Externals size (mm)	Φ12*H8.5	参阅附图 Refer to the attached drawing
10	重量 Mass	0.8g	
11	材质 Housing Material		



2. 电气和声学测试条件/Electrical And Acoustical Measuring Condition

驱动电路/Recommended Driving Circuit





Resonant frequency, 1/2 duty cycle. Square wave.

Signal amplitude should be large enough to saturate the transistor.

设置 Recommended Setting




3. 可靠性规范/Reliability specification

	项目 ITEM	测试方法 TEST
1	高温试验 High Temperature Test	在+80°C±2°C储存温度下存放 96 小时，恢复 2 小时后测试 After being placed in a chamber with +80±2°C for 96 hours and then being placed in normal condition for 2 hours
2	低温试验 Low Temperature Test	在-20°C±2°C储存温度下存放 96 小时，恢复 2 小时后测试 After being placed in a chamber with -20±2°C for 96 hours and then being placed in normal condition for 2 hours
3	恒定湿热试验 Humidity Test	 <p>The diagram shows a humidity test cycle. It starts with a 5-hour dwell at 25°C and 90-95% RH. This is followed by a 0.5-hour ramp up to 40°C and 90-95% RH. The test then holds at 40°C and 90-95% RH for 6 hours. Finally, there is a 0.5-hour ramp down to 25°C and 90-95% RH. The total cycle duration is 12 hours.</p>
4	温度变化试验 Temperature Cycle Test	 <p>The diagram shows a temperature cycle test. It starts with a 30-minute dwell at -30°C. This is followed by a 15-minute ramp up to +20°C. The test then holds at +20°C for 30 minutes. This is followed by a 15-minute ramp up to +80°C. The test then holds at +80°C for 30 minutes. Finally, there is a 15-minute ramp down to +20°C. The total cycle duration is 150 minutes.</p> <p>Make this test for 5 cycle without applying power, then expose to the room temperature for 2 hours 不加负载，按 5 次循环测试，然后在室温下恢复 2 小时</p>
5	振动试验 Vibration Test	 <p>The diagram shows a vibration test profile. The amplitude starts at 0.3g at 10 Hz and increases linearly to 9.3g at 55 Hz. The test is performed for 1 minute per axis.</p> <p>Amplitude: 1.5mm Time : 1min/axis</p> <p>Make this test for the directions of X, Y, Z for 2 hours each (total 6 hours). 振动频率 10-55Hz, 振幅 1.5mm, 在 X, Y, Z 3 个方向各 2 小时</p>
6	跌落试验 Drop Test	70cm 高自由掉落到 40mm 的木板上，每个方向三次 Drop on a hard wood board of 40mm thick, any directions, three times, at the height of 70cm
7	插针的抗拉强度试验 Terminal Strength Pulling Test	插针承受 1.0kg 拉力，负荷时间 5s The force 5 seconds of 1.0kg is applied to each terminal.
8	可焊性试验 Solder ability Test	焊锡温度 250±5°C，浸润时间为 3±0.5s，试验后目测产品情况 Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of 250±5°C for 3±0.5 seconds.
9	回流焊测试 Soldering Test	 <p>The diagram shows a soldering test profile. It starts with a 4°C/sec Max. ramp up to 180±10°C. This is followed by a 90±30sec dwell at 170-190°C. The test then ramps up to a peak temperature of 250°C max. at 4°C/sec Max. The test then holds at the peak temperature for 10 sec. Max. Finally, there is a cooling by air phase.</p>


4. 尺寸图/Dimension

(UNT: mm)

Tolerance: $\pm 0.5\text{mm}$ Except Specified






5. Frequency Curve 频率图



5Vo-p 50% duty Square wave, 10cm

6.Packing Method/包装图

Item	Drawing	Qty(pcs.)	Material	Specification (m m)
Packing		100 (10×10)	PE	78×78×20
MiddleBox		1000 (10×100)	Paper	780×780×110
OuterBox		10000 (10 1000) ×	Paper	500×420×270



兴化市华宇电子有限公司

Components Operating Div.
Huayu Electronic co.,Ltd.