







© 2021 TE Connectivity. All Rights Reserved.					REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD		
	A	INITIAL RELEASE			13JUN2022	J.Z	W.Z		

D





D

C




C

B



B

A



A

1. MAX.9 TERMINAL MISSING PER REEL PERMITTED
2. 3 LOOSE SPLICES PER REEL PERMITTED

TE LOGO

1.4-1.6	0.5mm ²	TIN	CuNiSi	A	2387544-2
1.2-1.4	0.35mm ²	TIN	CuNiSi	A	2387544-1
INSULATION RANGE	WIRE SIZE	FINISH	MATERIAL	REV.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.ZHANG 13JUN2022		TE Connectivity																	
DIMENSIONS: mm		CHK J.GU 13JUN2022																			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W.ZHANG 13JUN2022		NAME REM 0.64 2 POINT REC. CONTACT															
		0 PLC ±0.1 1 PLC ±0.01 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001		PRODUCT SPEC		- SWS															
				APPLICATION SPEC																	
				114-160148																	
MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO									
-		-		-		A2		00779		C=2387544		-									
-		-		CUSTOMER DRAWING						SCALE		6:1		SHEET		1 OF 1		REV		A	